

Data sheet

# Pressure transmitter for industrial applications

## MBS 4510



The high accuracy flush diaphragm pressure transmitter MBS 4510 is designed for use in non-uniform, high viscous or crystallizing media within industrial applications, and offers a reliable pressure measurement, even under harsh environmental conditions.

The flexible pressure transmitter programme covers a 4 – 20 mA output signal, absolute or gauge (relative) versions, measuring ranges from 0 – 0.25 to 0 – 25 bar zero and span adjustment. A rotatable plug connection and a G1A conic pressure connection with flush mounted diaphragm.

Excellent vibration stability, robust construction, and a high degree of EMC/EMI protection equip the pressure transmitter to meet the most stringent industrial requirements.

### Features

- Designed for use in severe industrial environments
- Enclosure and wetted parts of acid-resistant stainless steel (AISI 316L)
- Pressure ranges in relative (gauge) or absolute up to 25 bar
- Output signal: 4 – 20 mA
- Temperature compensated and laser calibrated
- Accuracy 0.5% FS
- Zero and span adjustment
- USDA-H1 approved oil filling
- For use in Zone 2 explosive atmosphere

**Technical data**
*Performance (EN 60770)*

Accuracy (incl. non-linearity, hysteresis and repeatability)		$\leq \pm 0.2\%$ FS (typ.)
		$\leq \pm 0.5\%$ FS (max.)
Non-linearity BFSL (conformity)		$\leq \pm 0.2\%$ FS
Hysteresis and repeatability		$\leq \pm 0.1\%$ FS
Thermal zero point shift	Measuring range:	0 – 250 mbar $\leq \pm 0.4\%$ FS / 10K
		0 – 400 mbar $\leq \pm 0.3\%$ FS / 10K
		$\geq 0$ – 600 mbar $\leq \pm 0.2\%$ FS / 10K
Thermal sensitivity (span) shift	Measuring range:	0 – 250 mbar $\leq \pm 0.4\%$ FS / 10K
		0 – 400 mbar $\leq \pm 0.35\%$ FS / 10K
		$\geq 0$ – 600 mbar $\leq \pm 0.2\%$ FS / 10K
Response time		< 4 ms
Durability, P: 10 – 90% FS		$> 10 \times 10^6$ cycles
Zero point adjustment	Measuring range:	0 – 0.25 to 0 – 10 bar -5 – 20% FS
		0 – 16 to 0 – 25 bar -5 – 10% FS
Span adjustment	Measuring range:	0 – 0.25 to 0 – 25 bar -5 – 5% FS

*Available measuring ranges*

Pressure range [bar]	Max. Overload pressure [bar]	Burst pressure [bar]
-0.25 – 0.50	2	50
0.00 – 0.25	2	50
0.00 – 0.40	2	50
0.00 – 0.60	2	50
0.00 – 1.00	2	50
0.00 – 1.60	8	50
0.00 – 2.50	8	50
0.00 – 4.00	8	50
0.00 – 6.00	20	50
0.00 – 10.00	20	50
0.00 – 16.00	100	100
0.00 – 25.00	100	100



*Electrical specifications*

Nom. output signal (short-circuit protected)	4 – 20 mA
Supply voltage [ $U_B$ ], polarity protected	10 – 30 V DC
Supply voltage dependency	$\leq \pm 0.1\%$ FS / 10 V
Current limitation (linear output signal up to 1.5 × rated range)	28 mA (typ.)
Load [ $R_L$ ] (load connected to 0 V)	$R_L \leq (U_B - 10 V) / 0.02 A [\Omega]$

**Technical data**  
*(continued)*
**Environmental conditions**

Sensor temperature range	Normal	-40 – 85 °C	
	ATEX Zone 2	-10 – 85 °C	
Media temperature	115 - (0.35 × ambient temperature)		
Ambient temperature range	-10 – 85 °C		
Compensated temperature range	0 – 80 °C		
Transport / Storage temperature range	-25 – 85 °C		
EMC – Emission	EN 61000-6-3		
EMC – Immunity	EN 61000-6-2		
Insulation resistance	> 100 MΩ at 100 V		
Mains frequency test	Based on SEN 361503		
Vibration stability	Sinusoidal	15.9 mm-pp, 5 Hz – 25 Hz	IEC 60068-2-6
		20 g, 25 Hz – 2 kHz	
Shock resistance	Random	7.5 g <sub>rms</sub> , 5 Hz – 1 kHz	IEC 60068-2-64
	Shock	500 g / 1 ms	IEC 60068-2-27
Shock resistance	Free fall	1 m	IEC 60068-2-32
	Enclosure (depending on electrical connection)		
			IP65

**Explosive atmospheres**

Zone 2 applications	  <b>II 3G</b> <b>Ex nA IIA T3 Gc</b> <b>-20C&lt;Ta&lt;85C</b>	EN60079-0; EN60079-15
---------------------	--	-----------------------

When used in ATEX Zone 2 areas at temperatures <-10 °C the cable and plug must be protected against impact

**Mechanical characteristics**

Materials	Wetted parts	EN 10088-1; 1.4404 (AISI 316 L)
	Enclosure	EN 10088-1; 1.4404 (AISI 316 L)
	Electrical connections	Glass filled polyamid PA 6.6
Gasket (above thread)		DIN 3869-33-NBR
Net weight (depending on pressure connection and electrical connection)		0.4 kg

Ordering standard



<b>MBS 4510</b>	1 - A1 C B 1 2	
<b>Measuring range</b>		<b>Pressure connection</b> G1A, ISO 228-1, Flush male
0.25 – 0.5 bar	A 4	<b>Electrical connection</b> Plug Pg 9 (EN 175301-803-A)
0 – 0.25 bar	0 4	
0 – 0.4 bar	0 6	
0 – 0.6 bar	0 8	
0 – 1.0 bar	1 0	
0 – 1.6 bar	1 2	
0 – 2.5 bar	1 4	
0 – 4.0 bar	1 6	
0 – 6.0 bar	1 8	
0 – 10 bar	2 0	
0 – 16 bar	2 2	
0 – 25 bar	2 4	
<b>Pressure reference</b>		
Gauge (relative)	1	
Absolute	2	

Preferred version


Electrical connections

Electrical connection	4 – 20 mA output (2 wire)
<p>EN 175301-803-A, Pg 9</p>	Pin 1: + supply Pin 2: ÷ supply Pin 3: Not used  <p>Earth: Connected to MBS enclosure</p>


Dimensions



### Installation



### Adjustment



### Accessories

<p>Welding nipple for conic metal/metal seal <b>Code no.: 060G2501</b></p>	<p>DIN 11851 (dairy connection), DN40 <b>Code no.: 060G2505</b></p>
<p>DIN 11851 (dairy connection), DN50 <b>Code no.: 060G2506</b></p>	<p>Clamp, ISO 2852, 1½ in. <b>Code no.: 060G2502</b></p>
<p>Clamp, ISO 2852, 2 in. <b>Code no.: 060G2510</b></p>	<p>SMS 1145 connection, 1½ in. <b>Code no.: 060G2503</b></p>

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.