Data sheet

AVDO Automatic By-pass Valve



Application



AVDO self-acting constant flow controls are used to maintain a minimum flow rate (e.g. through a low water content gas boiler) or to control differential pressure in a heating system.

The closing of radiator or zone valves due to reduced heating demand may result in low flow and increased system differential pressure (potentially dead heating pumps). AVDO valves open with a falling system load and allow flow through a bypass line whenever the differential pressure through the valve exceeds set point; ensuring a minimum flow rate or a system differential pressure at minimum system load.

AVDO:

- Opens on rising differential pressure.
- Setting differential pressure range of 0.725 7.25 psi (0.05-0.5 bar).
- Designed for 145 psi (10 bar), max. 248°F (120°C)
- Operates without impulse tubes.
- Can be supplied with NPT or solder tail pieces.

Application Examples:

The placement of the AVDO can be piped between the supply and return or parallel to the circulator as seen in the figures below.






Figure 1: Low water content gas boiler where a min. flow is required through the boiler.





constant circulating system.

Ordering

Code Numbers	Туре	Description	Size/Connection		
AVDO 15	Straight Valve Body	1/2" Union Solder 1/2" Union Male, NPT	003L602001 003L602002		
AVDO 20 AVDO 25		3/4" Union Solder 3/4" Union Male, NPT	003L602501 003L602502		
		1" Union Male, NPT	003L603002		

Technical data


Setting range	0.725 - 7.25 psi (0.05 - 0.5 bar)			
Max. differential pressure	7.25 psi (0.5 bar)			
Operation pressure	145 psi (10 bar)			
Max. flow temperature	248°F (120°C)			
Max. leakage when closed	0.22 gpm (0.05 m ³ /h)			

AVDO

Automatic By-pass Valve



Capacity



Design

Materials of parts in contact with water 1. Setting handle Pom-Plastic 2. Base Ms 58 Polyphenylene sulphide 3. Spring guide (PPS-plastics) 4. Spring Stainless steel Polyphenylene sulphide 5. Valve cone (PPS-plastics) 6. Valve body Ms 58, forged Stainless steel 7. Setting pin **EPDM** rubber 8. O-rings

Installation

The valve body must be mounted with flow in the direction of the cast-in arrow.

Setting

The control is set by turning the adjustment knob. AVDO has a setting scale on which the opening pressure can be set according to the table to the right. The differential pressures stated for a given setting are indicative. The scale gives the differential pressure across the AVDO when it just begins to open.


0.1	-	1	=	1.45	
0.2	-	2	=	2.90	
0.3	-	3	=	4.35	
0.4	-	4	=	5.8	
0.5	-	5	=	7.25	
bar	r	nH²	0	psi	

AVDO

Automatic By-pass Valve



Sizing



Example 1

Bypass control across heating system **Given:**

- System, see fig. 1
- Insignificant pressure loss in pipe from boiler to bypass.
- Pump characteristic, see fig. 2.
- 2.2 psi (0.15 bar) system differential pressure at max. system load.

Required:


- Bypass circulation beginning at 2.2 psi (0.15 bar) pump pressure.
- Min. 8.8 gpm (2.0 m³/h) boiler circulation


Seek

- A constant flow control that opens simultaneously with falling load across the system (closing radiator valves or zone valves)
- A constant flow control that ensures min. 8.8 gpm (2.0 m³/h) boiler circulation at min. system load

Solution:

- An 8.8 gpm (2.0 m³/h) flow corresponds to a 3.6 psi (0.25 bar) pump pressure - see "Capacity".
- On closing radiator valves or zone valves AVDO ensures a minimum of 8.8 gpm (2.0 m³/h) circulation at 3.6 psi (0,25 bar) differential pressure across AVDO.
- Choose AVDO 25 that provides 12 gpm (2.7 m³/h) at 3.6 psi (0.25 bar) differential pressure across valve.
- Set AVDO to #1.5 (2.2 psi, 0.15 bar) opening pressure.





Example 2

Bypass control across circulating pump **Given:**

- System, see fig. 3
- Pump characteristic, see fig. 4

Required:


- Bypass circulation beginning at 1.5 psi (0.1 bar) pump pressure
- Max. system differential pressure with closed radiator valves or zone valves must be limited to 3.6 psi (0.25 bar)

Seek:

- A constant flow control that opens simultaneously with falling load across the system (closing radiator valves or zone valves)
- A constant flow control that ensures max. system differential pressure not to exceed 3.6 psi (0.25 bar) at min. system load

Solution:

- The max. permissible differential pressure 3.6 psi (0.25 bar) across the system corresponds to a 8 gpm (1.8 m³/h) water volume (fig. 4). At min. load AVDO must ensure 8 gpm (1.8 m³/h) in circulation through the bypass. In this example AVDO 20 must be used - see "Capacity".
- As circulation is not to begin before differential pressure across system has exceeded 1.5 psi (0.1 bar), AVDO is set to # 1.0 (1.5 psi, 0.1 bar) - see "Setting.




Data sheet

AVDO Automatic By-pass Valve



Dimensions



DN	Type	Measure	L1	L2	L2	Н		S	а	b
		Unit		Threaded	Solder	Min	Max			ISO 228/1
15	AVDO 15	inch	3.44	5.94	4.76	3.50	4.45	1.18	1/2"	G 3/4 A
		mm	87	151	121	89	113	30		
20	AVDO 20	inch	3.66	6.49	5.39	3.55	4.49	1.46	3/4"	G 1 A
		mm	93	165	137	90	114	37		
25	AVDO 25	inch	4.17	7.00	-	3.74	4.69	4.69	1″	G 1 1/4 A
		mm	106	178	-	95	119	119		

Danfoss can accept no responsibility for possible errors in printed materials and reserves the right to alter its products without notice.

All trademarks in this material are property of the respective companies. Danfoss and Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.



Danfoss

Toronto, ON Toll Free: 866-676-8062 Tel.: 905-285-2050, Fax: 905-285-2055 www.na.heating.danfoss.com

Danfoss

Baltimore, MD Toll Free: 866-375-HVAC (4822) Tel.: 443-512-0266, Fax: 443-512-0270 www.na.heating.danfoss.com