

Data Sheet

EM-PME375-T150

Electric machine, permanent magnet external

FEATURES

- Synchronous Reluctance assisted Permanent Magnet (SRPM) technology
- Extremely compact and robust structure
- Highest efficiency throughout the operation range on the market (~96 %)
- Liquid cooled with plain water or water/glycol mixture
- Low coolant flow required
- Allowed coolant temperature up to +65°C
- Up to IP65 enclosure class to maximize reliability
- Multiple mounting possibilities

GENERATOR SPECIFIC FEATURES

- Standard SAE flange mounting to match the diesel engine connection
- Wide selection of speed ratings allowing the generator to be selected to customer specific applications with various voltage requirements
- Can be also used as starter motor for the ICE

MOTOR SPECIFIC FEATURES

- Extended speed and torque capabilities compared to standard PM motors from Danfoss reluctance assisted permanent magnet motor technology
- Motor structure is designed to be able to produce high starting torques: EM-PME motor can produce instantly full to a non-moving axle
- Optimized speed range to meet the most common gear ratios used in heavy mobile machinery



GENERAL

The machine is developed especially for demanding applications. The design of these machines makes them smaller, lighter and more efficient than conventional products on the market.

The machine is designed to be shorter than normal motors for applications where axial length is crucial parameter. The machine is designed to be connected directly to the ICE flywheel housing with part of the motor being inside the flywheel housing further shortening the length of the motor.

TYPICAL APPLICATIONS

- Generator for diesel-electric/ serial hybrid applications
- Traction/propulsion motor
- Generator/Motor for parallel hybrid applications


SPECIFICATIONS

General electrical properties		Minimum cooling liquid flow	20 l/min
Nominal voltage (line to line)	500 V _{AC}	Pressure loss	0.3 bar with 20 l/min (+25°C coolant)
Voltage stress	IEC 60034-25, Curve A: Without filters for motors up to 500 V _{AC}	Cooling liquid temperature max	+65°C (Derating required if exceeded)
Nominal efficiency	96 %	Temperature rating	
Pole pair number	10	Insulation class (IEC 60034-1)	F (155°C)
Power supply	Inverter fed.	Temperature rise (IEC 60034-1)	85°C
Minimum inverter switching frequency	8 kHz	Maximum winding temperature	150°C
Basic information		Nominal ambient temperature (IEC 60034-1)	65°C
Machine type	Synchronous reluctance assisted permanent magnet	Min. ambient temperature	-40°C
Mounting (IEC 60034-7)	IM 3001 (Flange)	Nominal altitude (IEC 60034-1)	1000 m
Standard Flange D-end (SAE J617)	SAE 3, transmission housing	Connections	
Standard rotation direction	Clockwise (both directions possible)	Coolant connection	2 x G1/2 bores
Protection class (IEC 60034-5)	Up to IP65	HV cables	3 x 50 mm ² max.
Duty type (IEC 60034-1)	S9	HV cable connector	3x AMPHENOL HVBI005R10AMHARD
Standard color	Dark grey RAL7024 powder coating	HV cable mating connector	3 x AMPHENOL HVBI-7-05R10-XFC-XXXX-FG/PC (straight plug) 3x AMPHENOL HVBI-9-05R10-XFC-XXXX-FG/PC (right angle plug) (check the exact codes form connector manufacturer)
Mechanical		HV cable	Recommended H+S Radox screened cable
Total weight	75 kg (no options)	LV connector	12 pin TE HDSCS
Moment of inertia	0.63 kgm ²	LV connector type	TE 1-1564520-1
Rotating mass	23 kg	LV connector pin type	Gold plated
Dimensions		LV mating connector type	TE 1-1703639-1
Length (frame)	66 mm	LV mating connector pin type	TE 1241380-2 (Gold plated)
Diameter (frame)	451 mm	LV connector pin configuration	see table below
Total length (frame + shaft)	195.6 mm		
Cooling			
Cooling liquid	Plain water with appropriate corrosive inhibitor (max. 50 % corrosive inhibitor)		
Cooling liquid corrosive inhibitor type	Ethylene glycol Glysantin G48 recommended		
Cooling method (IEC 60034-6)	IC 9S7Y7 (Liquid cooled, external heat exchanger)		

Table 1 Pin configuration of LV-connector

PIN	Description
1	Resolver, RES_COSN
2	Resolver, RES_SINN
3	Resolver, EXCN
4	Temperature, PT100, Windings
5	Temperature, PT100, Windings
6	Temperature, PT100, Windings
7	Resolver, RES_COSP
8	Resolver, RES_SINP
9	Resolver, EXCP
10	Temperature, PT100, Windings GND
11	Temperature, PT100, Windings GND
12	Temperature, PT100, Windings GND

PRESSURE LOSS VS COOLANT FLOW



Picture 1 Pressure loss vs coolant flow

MOTORS

Type	Coolant temperature +65°C			Coolant temperature +40°C			Coolant temperature +40 / +65°C		
	Cont. Torque [Nm]	Cont. Power [kW]	Nom. Current [A]	Cont. Torque [Nm]	Cont. Power [kW]	Nom. Current [A]	Nom. speed [rpm]	Max. speed [rpm]	Peak torque [Nm]
EM-PME375-T150-1500	160	25	33	191	30	40	1500	3000	600
EM-PME375-T150-1800	167	31	40	179	33	45	1800	3600	600
EM-PME375-T150-2600	147	40	50	164	45	60	2600	4000	600

(* Peak torque achieved with 1 (350A) inverter


(** Peak torque achieved with 2 (350A) inverter

GENERATORS

Type	Coolant temperature +65°C			Coolant temperature +40°C			Coolant temperature +40 / +65°C			
	Apparent power [kVA]	Cont. power [kW]	Nom. Current [A]	Apparent power [kVA]	Cont. Power [kW]	Nom. Current [A]	Nom. speed [rpm]	Nom. Freq. [Hz]	Power factor	Volt/ speed ratio [V/rpm]
EM-PME375-T150-1500	27	26	32	33	32	39	1575	263	0.99	0.319
EM-PME375-T150-1800	34	33	39	38	36	44	1890	315	0.97	0.273
EM-PME375-T150-2600	42	41	49	50	48	59	2730	455	0.99	0.182

(*** Back EMF for cold (20°C) generator

Integrated machine is commonly connected directly to the diesel engine flywheel housing. In such application part of the motor is inside the diesel engine. Exploded view of this kind of application is shown below.



Picture 2 Integrated machine connected to diesel engine flywheel housing

PRODUCT CODE AND OPTIONS

Use product code including all needed options for ordering. Standard options do not need to be listed in the code as they are selected by default if a non-standard option is not selected.

Product code	Description
EM-PME375-T150-1500	Standard unit with standard options
EM-PME375-T150-1500+TEMP4	Standard with additional temperature sensors (6 pcs total)

Table 2 Product code examples

		s = standard o = option		
Variant	code	Description	Standard	
High voltage connector	*	High voltage plug-in connectors for 50 mm ² cables	s	One plug-in connector per phase for 50 mm ² cable
	+HVC1	High voltage plug-in connectors for 35 mm ² cables	o	One plug-in connector per phase for 35 mm ² cable
Rotation sensor	*	None	s	No resolver
	+RES1	Resolver	o	In-built non contacting resolver, 5-pole pair
Winding temperature sensors	*	Temperature surveillance	s	3 x PT100 (two wire) in windings
	+TEMP4	Redundant temperature surveillance	o	6 x PT100 (two wire) in windings

Table 3 Option list

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.