







Installation guide




Thermostatic expansion valve


Type TCBE / TCCE / TCAE

Standard refrigerants: See product label	Max. working pressure: PS / MWP: 45.5 bar / 660 psig	Max. test pressure $P_{test} = 45.5 \text{ bar} / 660 \text{ psig}$
		
		



N, B: 4 °C / 7 °F
N_{MOP}, NM: 4 °C / 7 °F
B_{MOP}: 4 °C / 7 °F



R22/R407C	R134a	R404A/R507	R410A	ΔSS 1 × 
-	N	-	-	1 °C (1.8°F)
N	NM	N,B	N,B	1.5 °C (2.7°F)
NM,B	-	NM	NM	2 °C (3.6°F)

Temperature ranges:

N = -40 - 10 °C / -40 - 60 °F
NM = -40 - 5 °C / -40 - 25 °F
B = -60 - 25 °C / -75 - 15 °F