



Check Valves Technical Information

Poppet Type, Normal Direction


CP102-1

OPERATION

This valve allows free flow from 1 to 2 and blocks flow from 2 to 1.

SPECIFICATIONS

Theoretical performance



Schematic



Specifications


Rated pressure*	315 bar [4570 psi]
Rated flow at 7 bar [100 psi]	210 l/min [55.5 US gal/min]
Leakage	6 drops/min @ Rated pressure
Weight	0.26 kg [0.57 lb]
Cavity	SDC16-2

*Rated pressure based on NFPA fatigue test standard (at 1 million cycles)

DIMENSIONS

mm in

Cross-sectional view



ORDERING INFORMATION

CP102-1-B-0-005		
Check Valve Poppet Type, Normal Direction		
Seal Kit	Seal Option	Crack Pressure
120019	B = Buna-N	005 0.34 bar [5 psi]
120020	V = Viton	015 1.0 bar [15 psi]
		030 2.1 bar [30.4 psi]
		040 2.8 bar [40 psi]
		065 4.5 bar [65 psi]
		100 6.9 bar [100 psi]
Code	Ports & Material	Body Nomenclature
0	0 = Cartridge only	No Body
DG6B	Al, 3/4 BSP	SDC16-2-DG-6B
DG8B	Al, 1 BSP	SDC16-2-DG-8B
12S	Al, #12 SAE	CP16-2-12S
16S	Al, #16 SAE	CP16-2-16S

**Aluminum bodies are to be used for pressures less than 210 bar (3000 psi)

*** Other housings available