

Data Sheet

# Temperature sensor Type **MBT 3270**

Compact industrial temperature sensor.



The flexible temperature sensor MBT 3270 can be used in many industrial applications such as: Air Compressors, Mobile Hydraulics and Exhaust gas return systems. In other words applications where robustness, size and performance are essentials.

The sensor can be equipped with different sensing elements (RTD, NTC and PTC) and is available with different electrical connections (Cable, Delphi Metri Pack, AMP junior power Timer, Deutch DT04).

**Features:**

- OEM Temperature Sensor program
- Various sensor elements available (RTD, NTC, PTC)
- Robust, high protection against moisture
- Fixed measuring insert
- Brass or stainless steel
- Very low response times
- Temperature range up to 300 °C
- Available with cable or integrated plug (Delphi Metri Pack, AMP junior power Timer, Deutsch DT04)

## Product specification

### Technical data

#### Cable version

Figure 1: Cable version




Table 1: General data

Features		Description	
Ambient temperature	Cable	PVC	-40 – 100 °C
		Silicon	-40 – 200 °C
		Teflon	-40 – 200 °C
		Polyolefin (oil resistant)	-40 – 150 °C
	Plug	AMP spade	-40 – 200 °C
		AMP Junior Power Timer	-40 – 125 °C
		Delphi Metri Pack 102	-40 – 125 °C
		Deutsch DT04-3P	-40 – 125 °C
Media temperature	Pt 100	-50 – 300 °C	
	NTC	-50 – 150 °C, Special versions up to 300 °C	
	PTC	-50 – 150 °C	
Max. external pressure	Operating pressure	500 bar	
	Burst pressure	> 900 bar	
Max. tightening torque	M10	17 Nm	
	M14	24 Nm	

Table 2: Performance

Features		Description
Sensor Element		Pt 100, Pt 1000, NTC, PTC
Process Connection		Refer to ordering standard, see page <a href="#">Cable version</a>
Sensor insertion length	Brass	80 mm @ d ≥ 8 mm
		60 mm @ 8 > d > 5 mm 40 mm @ d ≤ 5 mm
	Stainless steel	70 mm @ d ≥ 8 mm
		50 mm @ 8 > d > 5 mm 35 mm @ d ≤ 5 mm
Electrical Connection		Stripped wire ends Cable with AMP spade (6.35) Cable with AMP Junior Power Timer Cable with Delphi Metri Pack 102 Cable with Deutsch DT04-3P-2P Other on request
Connection		2, 3 or 4 wire (depending on electrical connection)

Table 3: Indicative response times

Material protection tube	Protection tube	Indicative response times	
		Water 0,2 m/s	
		t <sub>0,5</sub>	t <sub>0,9</sub>
Stainless steel	ø6 mm	6 s	18 s
	ø4 mm	2 s	6 s
	ø3 mm	1.5 s	3 s

#### NOTE:

Response times can vary very much depending on the design of the sensor and the temperature element chosen.

## Temperature sensor, Type MBT 3270

**Table 4: Mechanical and environmental specifications**


Features	Description	
Sensor tolerances	Pt 1000 / Pt 100	EN 60751 Class B: $\pm (0.3 + 0.005 \times t)$
	NTC	On request
	PTC 2000 (KTY 81 – 210)	$\pm 1\%$ at 25 °C
Vibration stability	Shock	50 g / 6 ms
	Vibrations, x-y-z directions	15.3 g sine, 20 – 2000 Hz, 8 hours
Enclosure	Sensor only	IP67 according to IEC 60529
	Cable with AMP spade	IP00 according to IEC 60529
	Cable with AMP Junior Timer	IP65 according to IEC 60529
	Cable with Delphi Metri Pack 102	IP65 according to IEC 60529
	Cable with Deutsch DT04	IP65 according to IEC 60529

**Table 5: Materials**

Features	Description
Protection tube in contact with media	AISI 316 Brass
Process connection	AISI 316 Brass
Cable	PVC, Silicon, Teflon (other on request)
Gasket	Viton, NBR (other on request)
Plug	PPS (Ryton 4)

## Integrated plug version

**Figure 2: Integrated plug version**



**Table 6: General data**

Features	Description	
Ambient temperature	Plug	-40 – 125 °C
	Pt 1000, Pt 100	-50 – 300 °C
Media temperature	NTC	-50 – 150 °C, Special versions up to 300 °C
	PTC	-50 – 150 °C
	Operating pressure	500 bar
Max. external pressure	Burst pressure	> 900 bar
	Max. tightening torque	M10
M14		24 Nm

**Table 7: Performance**

Features	Description	
Sensor Element	Pt 100, Pt 1000, NTC, PTC	
Process Connection	Refer to ordering standard, see page <a href="#">Integrated plug version</a>	
Sensor insertion length	Brass	80 mm @ $d \geq 8$ mm
		60 mm @ $8 > d > 5$ mm
		40 mm @ $d \leq 5$ mm
	Stainless steel	70 mm @ $d \geq 8$ mm
		50 mm @ $8 > d > 5$ mm
		35 mm @ $d \leq 5$ mm
Electrical Connection	AMP Junior Power Timer Delphi Metri Pack Deutsch DT04 Other on request	
Connection	2 wire	

## Temperature sensor, Type MBT 3270

**Table 8: Indicative response times**

Material protection tube	Protection tube	Indicative response times	
		Water 0,2 m/s	
		$t_{0,5}$	$t_{0,9}$
Stainless Steel	ø6 mm	6 s	18 s
	ø4 mm	2 s	6 s
	ø3 mm	0.5 s	1.5 s

**NOTE:**

Response times can vary very much depending on the design of the sensor and the temperature element chosen.

**Table 9: Mechanical and environmental specifications**

Features	Description	
Sensor tolerances	Pt 1000 / Pt 100 NTC PTC 2000 (KTY 81 – 210)	EN 60751 Class B On request ± 1% at 25 °C
Vibration stability	Shock	50 g / 6 ms
	Vibrations, x-y-z directions	15.3 g sine, 20 – 2000 Hz, 8 hours
Enclosure	AMP Junior Power Timer Delphi Metri Pack Deutsch DT04	IP65 according to IEC 60529






**Table 10: Materials**

Features	Description
Protection tube in contact with media	AISI 316 Brass
Process connection	AISI 316 Brass
Gasket	Viton, NBR (other on request)
Plug	PPS (Ryton 4)

## Electrical connection




### Cable version

**Table 11: Electrical connection of cable version**

AMP spade (6.35)	AMP Junior Power Timer	Deutsch DT04 3 pin	Deutsch DT04 2 pin	Delphi Metri Pack 102
				

### Integrated plug version

**Table 12: Electrical connection of integrated plug version**

Deutsch DT04	AMP Junior Power Timer	Delphi Metri Pack 102
		

## Dimensions

### Cable version

Table 13: Dimensions

-50 – 150 °C	-50 – 150 °C / 300 °C

### Examples:

Insertion length:  $L_i = 21$  to  $xx$  (max. 80 mm)

Cable length:  $L_c = 0.5$  m to  $x.xx$  m

Tube diameter depends on the chosen sensor element and the wanted response time.



### Integrated plug version

Figure 4: Ordering for MBT 3270 - Integrated plug version

Type MBT 3270									
<b>Measuring range</b>									
-50 – 150 °C	0					0		<b>Connection</b>	2-wire
-50 – 200 °C	1					9			Other
-50 – 300 °C	2							<b>Plug</b>	None
Other	9								AMP Junior PowerTimer
<b>Resistance value</b>									Delphi Metri-pack Integrated – 102
1 × Pt 100	0					0			Deutsch Integrated DT04 – 2 pin
1 × Pt 1000	2					3			Other
NTC 2000, B25/85 2880 - 4570	6					4		<b>Insert</b>	Fixed
NTC 2700, B25/85 2880 - 4570	K					0			
NTC 3000, B25/50 3499	A							<b>Process connection</b>	G ¼ A
NTC 5000, B25/100 3988	L								G 3/8 A
Other (e.g. NTC)	9								G ½ A
<b>Tolerance</b>									M10 × 1
EN 60751 Class B	0								M14 × 1.5
± 1%	1								Other
± 2%	2								
± 3%	3								
Other	9								
<b>NTC characteristic</b>									
No NTC	0								
Other	9								
<b>Protection tube</b>									
Brass	0								
Acid-Proof Steel, AISI 316	1								
Other	9								
<b>Insertion length (80 mm max)</b>									
24 mm						0 2 4			
28 mm						0 2 8			
40 mm						0 4 0			
Other (21 – 80)						x x x			

## Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at [danfoss.com](http://danfoss.com) or contact your local Danfoss representative if you have any questions.

**Table 14: MBT 3270**

File name	Document type	Document topic	Approval authority
E494625	Electrical - Safety Certificate	–	UL
DK.C.32.004.A 41461	Measuring - Performance Certificate	–	GOST
097R0004.01	Manufacturers Declaration	RoHS	Danfoss
084R1022.01	Manufacturers Declaration	China RoHS	Danfoss
087R0017.00	Manufacturers Declaration	Simple apparatus	Danfoss
OC.C.32.004.A 75977	Measuring - Performance Certificate	–	GOST



## Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

### The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at [store.danfoss.com](https://store.danfoss.com).

### Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at [www.danfoss.com/en/service-and-support/documentation](https://www.danfoss.com/en/service-and-support/documentation).

### Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at [www.danfoss.com/en/service-and-support/learning](https://www.danfoss.com/en/service-and-support/learning).

### Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: [www.danfoss.com/en/choose-region](https://www.danfoss.com/en/choose-region).

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.