

## Aeroquip Performance Products

# Assembly Instructions


## ProClamp™ Hose Connector and Stainless Steel Overbraid Assembly

## Pro Clamp™




Use PRO CLAMP™ connectors on any rubber or stainless steel braid hose.


Do not be use on brake lines, air conditioning, power steering or other high pressure lines.



**Step 1.** Slide clamp onto hose.




**Step 2.** Push cap (socket) onto hose until it bottoms. Then slide clamp under cap.




**Step 3.** Push assembly onto beaded tube. Position clamp for appearance. Tighten with a screwdriver.


## Overbraid




Stainless Steel Overbraid is used to dress up existing rubber hoses. Simply slip over current radiator hoses and can be clamp with the Aeroquip Performance Products PRO CLAMP™ connectors.



**Step 1.** Disconnect the radiator hose. Slide overbraid over the radiator hose.



**Step 2.** Stretch until snug, mark length and cut with tin snips.



**Step 3.** Reconnect radiator hose and secure hose and overbraid with clamp or ProClamp clamp.

**Products we offer:**

- Cartridge valves
- DCV directional control valves
- Electric converters
- Electric machines
- Electric motors
- Gear motors
- Gear pumps
- Hydraulic integrated circuits (HICs)
- Hydrostatic motors
- Hydrostatic pumps
- Orbital motors
- PLUS+1® controllers
- PLUS+1® displays
- PLUS+1® joysticks and pedals
- PLUS+1® operator interfaces
- PLUS+1® sensors
- PLUS+1® software
- PLUS+1® software services, support and training
- Position controls and sensors
- PVG proportional valves
- Steering components and systems
- Telematics

**Danfoss Power Solutions** is a global manufacturer and supplier of high-quality hydraulic and electric components. We specialize in providing state-of-the-art technology and solutions that excel in the harsh operating conditions of the mobile off-highway market as well as the marine sector. Building on our extensive applications expertise, we work closely with you to ensure exceptional performance for a broad range of applications. We help you and other customers around the world speed up system development, reduce costs and bring vehicles and vessels to market faster.

Danfoss Power Solutions – your strongest partner in mobile hydraulics and mobile electrification.

**Go to [www.danfoss.com](http://www.danfoss.com) for further product information.**

We offer you expert worldwide support for ensuring the best possible solutions for outstanding performance. And with an extensive network of Global Service Partners, we also provide you with comprehensive global service for all of our components.

Local address:

**Hydro-Gear**

[www.hydro-gear.com](http://www.hydro-gear.com)

**Daikin-Sauer-Danfoss**

[www.daikin-sauer-danfoss.com](http://www.daikin-sauer-danfoss.com)

**Danfoss  
Power Solutions (US) Company**  
2800 East 13th Street  
Ames, IA 50010, USA  
Phone: +1 515 239 6000

**Danfoss  
Power Solutions GmbH & Co. OHG**  
Krokamp 35  
D-24539 Neumünster, Germany  
Phone: +49 4321 871 0

**Danfoss  
Power Solutions ApS**  
Nordborgvej 81  
DK-6430 Nordborg, Denmark  
Phone: +45 7488 2222

**Danfoss  
Power Solutions Trading  
(Shanghai) Co., Ltd.**  
Building #22, No. 1000 Jin Hai Rd  
Jin Qiao, Pudong New District  
Shanghai, China 201206  
Phone: +86 21 2080 6201