

Vickers® by Danfoss

Directional Controls




Modular Sequence Valves

DGC-01-*(*)-50
DGC-06-*(*)-50

Model Code Breakdown "10 Series"

DGC - 01 - * (*) - 50



1 Model Series

DGC - Directional control, gasket mounted relief module

3 Pressure Range

B - 125 - 1000 PSI
C - 500 - 2000 PSI
F - 1500 - 3000 PSI


4 Vent

V - High Venting (Omit when not required)

2 Size

01 - 1/8 inch

5 Design Number



△Coat with oil prior to assembly.

◆Not available for sale as individual part.

▲Included in 919654 Seal Kit

■ Included in Cover S/A

Refer to installation drawing 522650 for bolt kit information and module stacking data. The mounting bolt torque should not exceed a maximum of 122 in. lbs.

The following subplates may be used to mount a 10 series directional valve and one or more modular valves:

DGSM-01X-10	(3/8 inch NPT)	Assy. No. 234488
DGSM-01Y-10	(1/2 inch NPT)	Assy. No. 221212
DGRXM-01X-50	(3/8 inch NPT)	Assy. No. 347454
DGRXM-01Y-50	(1/2 inch NPT)	Assy. No. 347455

(DGRXM Subplates have the "Y" Port)


"R" valve modules must be mounted directly to a subplate or manifold for drain through the "Y" port. "X" valve modules must be drained thru the cover (Type "E") or port "B" (Type "L") when not mounted directly to a subplate or manifold with a "Y" drain connection.



CAUTION
This module cannot be used with pressure centered or DG18 air operated valves.

Model Code Breakdown

DGC - 06 - * (*) - 50



1 Model Series

DGC - Directional control, gasket mounted relief module

3 Pressure Range

B - 125 - 1000 PSI
C - 500 - 2000 PSI
F - 1500 - 3000 PSI


4 Vent

V - High Venting (Omit when not required)

2 Size

06 - 3/4 inch

5 Design Number



Refer to installation drawing 522650 for bolt kit information and module stacking data. The mounting bolt torque should not exceed a maximum of 122 in. lbs.

The following subplates may be used to mount a 10 series directional valve and one or more modular valves:

DGSM-06-50	(3/8 inch NPT)	Assy. No. 280497
DGSM-06X-50	(1 inch NPT)	Assy. No. 280498
DGRXM-06Y-50	(1-1/4 inch NPT)	Assy. No. 315213

CAUTION
This module cannot be used with pressure centered or DG18 air operated valves.

For satisfactory service life of these components in industrial applications, use full flow filtration to provide fluid which meets ISO cleanliness code 20/18/15 or cleaner. Selections from Danfoss OFP, OFR, and OFRS series are recommended.

Products we offer:

- Cartridge valves
- DCV directional control valves
- Electric converters
- Electric machines
- Electric motors
- Gear motors
- Gear pumps
- Hydraulic integrated circuits (HICs)
- Hydrostatic motors
- Hydrostatic pumps
- Orbital motors
- PLUS+1® controllers
- PLUS+1® displays
- PLUS+1® joysticks and pedals
- PLUS+1® operator interfaces
- PLUS+1® sensors
- PLUS+1® software
- PLUS+1® software services, support and training
- Position controls and sensors
- PVG proportional valves
- Steering components and systems
- Telematics

Hydro-Gear

www.hydro-gear.com

Daikin-Sauer-Danfoss

www.daikin-sauer-danfoss.com

Danfoss Power Solutions is a global manufacturer and supplier of high-quality hydraulic and electric components. We specialize in providing state-of-the-art technology and solutions that excel in the harsh operating conditions of the mobile off-highway market as well as the marine sector. Building on our extensive applications expertise, we work closely with you to ensure exceptional performance for a broad range of applications. We help you and other customers around the world speed up system development, reduce costs and bring vehicles and vessels to market faster.

Danfoss Power Solutions – your strongest partner in mobile hydraulics and mobile electrification.

Go to www.danfoss.com for further product information.

We offer you expert worldwide support for ensuring the best possible solutions for outstanding performance. And with an extensive network of Global Service Partners, we also provide you with comprehensive global service for all of our components.

Local address:

**Danfoss
Power Solutions (US) Company**
2800 East 13th Street
Ames, IA 50010, USA
Phone: +1 515 239 6000

**Danfoss
Power Solutions GmbH & Co. OHG**
Krokamp 35
D-24539 Neumünster, Germany
Phone: +49 4321 871 0

**Danfoss
Power Solutions ApS**
Nordborgvej 81
DK-6430 Nordborg, Denmark
Phone: +45 7488 2222

**Danfoss
Power Solutions Trading
(Shanghai) Co., Ltd.**
Building #22, No. 1000 Jin Hai Rd
Jin Qiao, Pudong New District
Shanghai, China 201206
Phone: +86 21 2080 6201

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to alter its products without notice. This also applies to products already on order provided that such alterations can be made without subsequent changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. Danfoss and the Danfoss logotype are trademarks of Danfoss A/S. All rights reserved.