


## Royal™ EHW194

Boston by Danfoss Royal EHW194 Water Liquid Cooling



# Engineered to keep you **cool**

Liquid cooling is an innovative technique using water as a cooling medium to help keep computer processor temperatures low in data center applications. Danfoss designed Boston® Royal with this emerging technology in mind.

UL 94 V-0 rated and offering superior flexibility and kink resistance, this hose was designed to maneuver in tight spaces to simplify installation and maintenance. Offered in a variety of sizes and colors, with approved Danfoss fittings—we have made it easy to emerge into this new market.



### Markets/Applications

- Data centers
- Electronic component cooling
- Telemedicine
- Cryptocurrency mining
- IT thermal management



### Sells Against

- Parker Push-Lok® 801
- Parker Push-Lok® 804
- Parker 627
- Parker 7092 GST® II
- Parker 7395 E-Z Form GS
- Contitech FlexAGrip™

### Features

- UL 94 V-0 rated
- Exceeds ASTM E84 Class 1/A Requirements
- Fire resistant cover
- Smooth-finish cover, low CoF
- Multiple color offerings
- Flexible with torsional strain and kink resistance

### Order Fulfillment

- Made to Stock

# Royal EHW194

Liquid cooling, using water as a solution, helps to eliminate the overheating of devices in data center applications

Boston by Danfoss Royal EHW194-08 Water Liquid Cooling 12.7 MM (0.50 IN) DN12 UL94 V-0 16 BAR (232 PSI) with clamp -40°C to 140°C (-40°F to 284°F) YYYY/MM/DD Made in Türkiye //-- XXXXX



Number	Hose I.D.		Hose O.D.		Operating Pressure without clamp		Burst Pressure without clamp		Operating Pressure with clamp		Burst Pressure with clamp		Minimum Bend Radius		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	bar	psi	bar	psi	mm	in	kg/m	lbs/ft	mtr	ft
EHW194-04RD-250R	6.4	0.25	15.0	0.59	5	73	15	218	16	232	48	696	50	2.0	0.21	0.14	76.2	250
EHW194-06RD-250R	9.5	0.37	18.5	0.73	5	73	15	218	16	232	48	696	65	2.5	0.28	0.19	76.2	250
EHW194-08RD-250R	12.7	0.50	22.0	0.87	5	73	15	218	16	232	48	696	75	3.0	0.36	0.24	76.2	250
EHW194-10RD-250R	15.9	0.63	25.2	0.99	5	73	15	218	16	232	48	696	100	4.0	0.43	0.29	76.2	250
EHW194-12RD-250R	19.0	0.75	29.7	1.17	5	73	15	218	16	232	48	696	125	5.0	0.56	0.38	76.2	250
EHW194-16RD-250R	25.4	1.00	36.5	1.44	5	73	15	218	16	232	48	696	150	6.0	0.75	0.50	76.2	250

**EHW194 Thin-wall (TW)** provides a smaller diameter for improved flexibility and lower bending force.

EHW194TW-04RD-250R	6.4	0.25	13.0	0.51	5	73	15	218	16	232	48	696	40	1.6	0.21	0.14	76.2	250
EHW194TW-06RD-250R	9.5	0.37	16.0	0.63	5	73	15	218	16	232	48	696	50	2.0	0.28	0.19	76.2	250

### Construction

**Tube** Peroxide-cured Synthetic EPDM Rubber

### Reinforcement

2 -ply textile

**Cover** Fire retardant Synthetic EPDM Rubber

**Colors** Black (BK), Blue (BU), Grey (GY), Red (RD)

### Operating Temperature

-40°C to +140°C (-40°F to +284°F)

### Certifications

UL 94 V-0 rated

Exceeds ASTM E84 Class 1/A Requirements

### Packaging

250 ft. reels

### Type of couplings

- Danfoss 1G crimp fittings
- Danfoss 100B socketless fittings
- Danfoss UQD hose barb quick disconnect
- Danfoss FD83 hose barb couplings

Contact coupling manufacturer for attachment procedure and other coupling recommendations

ENGINEERING  
TOMORROW



Danfoss Power Solutions, Nordborgvej 81, 6430 Nordborg, Denmark, Tel. +45 74 88 22 22, Fax +45 74 65 25 80  
www.danfoss.com, E-mail: info@danfoss.com

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.