

Table of Contents

Introduction

General Description	3
Features and Benefits	3
Characteristics	3
Typical Side View	3
Model Code	4
Spool Data	5
Functional Symbol	5
Operating Data	6
Performance Data	7
Installation Dimensions	9
Application Data	10

Introduction

General Description

These solenoid operated directional control valves are for directing and stopping flow at any point in a hydraulic system. This series has been specially designed and developed for equipment that has been installed in new applications in potentially explosive atmospheres.

DG4V-3S, X4 option

- ATEX approval
- Hazardous locations - Ex II 2 G; Zone 1 and Zone 2.
- Protection type - EEx me II T4; "increased safety" and "encapsulated"

DG4V-3S and DG4V4, X5 option

- ATEX, UL, and CSA approval; complies to all 3 directives
- ATEX approval; hazardous locations - Ex II 2 G; Zone 1

and Zone 2; protection type EEx d IIB T*, "flameproof"

- UL and CSA approval; hazardous locations - Class 1, Group C/D; Class 2, Group E/F/G; Division 1 & 2

Characteristics

DG4V-3S-X4 & X5-6* Design Mounting interface

ISO 4401 size 03
ANSI/B93.7M size D03
CETOP RP65H, size 3
DIN 24340, NG6

Basic characteristics

Maximum pressure:
350 bar (5075 psi)
Maximum flow:
Up to 40 l/min (10.5 USgpm)

DG4V4-01, X5-10 Design Mounting interface

ISO 4401 size 05
ANSI/B93.7M size D05
CETOP RP65H, size 5
DIN 24340, NG10

Basic characteristics

Maximum pressure
315 bar (4500 psi)
Maximum flow up to 80 L/min
(21 USgpm)

Features and Benefits

New expanded product offering for hazardous environments, opening up new opportunities.

- Multi-fluid capability without need to change seals.
- Higher sustained machine productivity and higher up|time because of proven fatigue life and endurance, tested over 10 million cycles.

Temperature limits

Minimum ambient:
-20°C (-4°F)
Maximum ambient:
+70°C (158°F)

Fluid temperature ▲

For mineral oil
Minimum = -20°C (-4°F)
Maximum = +70°C (158°F)

▲ The temperature limits of these valves are subject to specific operating conditions. Please refer to the Instruction for Use document supplied with each valve.

Functional Symbols

Spools

Available spool options

(illustrated to the right)
Configurations include
3-position and 2-position,
spring centered, spring off-
set and no-spring detented.

The valve function schematics apply to both U.S. and European valves.

DG4V-3-*N(V)




DG4V-3-*A(V)



DG4V-3-*AL(V)








DG4V-3-*C(V)



DG4V-3-*B/F(V)






DG4V-3-*BL/FL(V)



DG4V-3-8C(V)

DG4V-3-8BL(V)

DG4V-3-8B(V)




Solenoids identified to U.S. standards

(specify "A" in model code)

Functional symbols related to solenoid identity "A" and/or "B" according to NFPA/ANSI standards, i.e. energizing solenoid "A" gives flow P to A, solenoid "B" gives flow P to B (as applicable).


Location of solenoid "A" or "B" shown relative to the hydraulic work port.




Solenoid	For Use with Spool Type	Solenoid
B	All except "8"	A
A	"8" only	B

"A" and "B" designations are printed on the name label adjacent to the solenoid indicator lights, illustrated above.


Double solenoid valves, two position, detented




Single solenoid valves, solenoid at port A end



Double solenoid valves, spring centered



Single solenoid valves, solenoid at port B end




▲ Transient condition only

Solenoids identified to European standards

(specify "V" in model code)

Functional symbols related to solenoid identity "A" and/or "B" according to European convention i.e. solenoid "A" adjacent to "A" port, solenoid "B" adjacent to "B" port of valve.


Location of solenoid "A" or "B" shown relative the hydraulic work port.




Solenoid	For Use with Spool Type	Solenoid
B	All spools	A

"A" and "B" designations are printed on the name label adjacent to the solenoid indicator lights, illustrated below.


Double solenoid valves, two position, detented




Single solenoid valves, solenoid at port A end



Double solenoid valves, spring centered



Single solenoid valves, solenoid at port B end



▲ Transient condition only

Operating Data

Data is typical, with fluid at 36 cST (168 SUS) and 50°C (122°F)

Valve size	DG4V-3S		DG4V4-01	
Pressure limits:				
P, A and B ports	350 bar		315 bar	
T port	70 bar for X5, 210 bar for X4		70 bar	
Flow rating	See performance data		See performance data	
Relative duty factor	Continuous rating (ED = 100%)		Continuous rating (ED = 100%)	
Type of protection	IEC 144 class IP66		IEC 144 class IP66	
Permissible Voltage Fluctuation	DC ± 10%		DC ± 10%	
Typical response times at 100% rated volts measured from application/removal of voltage to full spool displacement of "2C" spool at:			DC	AC
Flow Rate at P-A, B-T	20 l/min	20 l/min	40l/min	40l/min
Pressure, P Port	175 bar	175 ms	175 ms	175 ms
Energizing	60 ms	100 ms	60 ms	100 ms
De-energizing	40 ms	100 ms	40 ms	100 ms
Power consumption, solenoids at rated voltage and 20°C (68°F)				
X4 coils				
12V DC solenoid rating - type G	30W		30W	
24V DC solenoid rating - type H	30W		30W	
X5 coils				
24V DC solenoid rating - type H	17W		17W	
48V DC solenoid rating - type OJ	17W		17W	
110V DC solenoid rating - type P	17W		17W	
110V AC, 50Hz, solenoid rating - type A	20W		20W	
120V AC, 60Hz, solenoid rating - type ER	20W		20W	
220V AC, 50Hz, solenoid rating - type C	20W		20W	
240V AC, 60Hz, solenoid rating - type ES	20W		20W	


Performance Data

DG4V-3S, X4 and X5

Maximum flow rates

Typical with mineral oil at 36 cSt (168.6 SUS) and a specific gravity of 0.87. Performance based on full power solenoid coils warm and operating at 90% rated voltage.

Spool/Spring Code	DG4V-3S
0A(L)	2
0B(L) & 0C, 0F	1
2A(L)	2
2B(L) & 2C	2
6B(L) & 6C, 6F	3
8B(L) & 8C	4




DG4V4-01, X5

Maximum flow rates

Typical with mineral oil at 36 cSt (168.6 SUS) and a specific gravity of 0.87. Performance based on full power solenoid coils warm and operating at 90% rated voltage.

Spool/Spring Code	DG4V4-01	
	AC	DC
0A(L)	1	4
0B(L) & 0C, 0F	1	4
2A(L)	1	4
2B(L) & 2C	1	4
6B(L) & 6C, 6F	2	4
8B(L) & 8C	3	4




Performance Data

Flow Curves

DG4V-3S, X4 & X5

Spool/Spring Code	Spool Positions	P to A	P to B	A to T	B to T	P to T	B to A
0A(L)C	Both	5	5	2	2		-
0B(L)C & 0C	De-energized	-	-	-	-	4	-
	Energized	4	4	2	2	-	-
2A(L)	Both	6	6	5	5	-	-
2B(L) & 2C	Energized	5	5	2	2	-	-
6B(L) & 6C	De-energized	-	-	3	3	-	-
	Energized	6	6	1	1	-	-
8B(L) & 8C	All	7	7	5	5	3	-



DG4V4-01, X5

Pressure drops in offset positions except where otherwise indicated.


Spool code	P to A	P to B	A to T	B to T	P to T
0	1	1	1	2	1
2	4	4	2	3	-
6	4	4	1	2	-
8	6	6	4	4	3

For other viscosities, pressure drops approximate to:

Viscosity cSt (SUS)	14 (17.5)	20 (97.8)	43 (200)	54 (251)	65 (302)	76 (352)	85 (399)
% of Δp	81	88	104	111	116	120	124

A change to another specific gravity will yield an approximately proportional change in pressure drop.


The specific gravity of a fluid may be obtained from its producer. Fire resistant fluids usually have higher specific gravities than oil.




Installation Dimensions

In mm


DG4V-3S, X4



DG4V-3S, X5



DG4V4-01, X5



Application Data

Fluid Cleanliness

Proper fluid condition is essential for long and satisfactory life of hydraulic components and systems. Hydraulic fluid must have the correct balance of cleanliness, materials and additives for protection against wear of components, elevated viscosity and inclusion of air.

Recommendations on contamination control methods and the selection of products to control fluid condition are included in publication 9132 or 561, "Vickers® Guide to Systemic Contamination Control". The book also includes information on the concept of "ProActive Maintenance". The following recommendations are based on ISO cleanliness levels at 2 µm, 5 µm and 15 µm.

For products in this catalog the recommended levels are:

0 to 70 bar (1000 psi):

18/16/13

70+ bar (1000+ psi):

17/15/12

Danfoss products, as any components, will operate with apparent satisfaction in fluids with higher cleanliness codes than those described. Other manufacturers will often recommend levels above those specified.

Experience has shown, however, that life of any hydraulic component is shortened in fluids with higher cleanliness codes than those listed above. These codes have been proven to provide a long trouble-free service life for the products shown, regardless of the manufacturer.

Hydraulic Fluids

Materials and seals used in these valves are compatible with antiwear hydraulic oils, and non-alkyl-based phosphate esters. The extreme operating viscosity range is 500 to 13 cSt (2270 to 70 SUS) but the recommended running range is 54 to 13 cSt (245 to 70 SUS).

Installation

The valves in this catalog can be mounted in any attitude, but it may be necessary in certain demanding applications, to ensure that the solenoids are kept full of hydraulic fluid.

Mounting Bolt Kits

If not using recommended bolt kits, bolts used should be to ISO 898, 12.9 or better.

Mass, approx. kg (lb)

DG4V3S-*C = 3.5 kg (7.72 lb)

DG4V3S-A/B = 2.3 kg (5.07 lb)

DG4V4-01-*C = 6 kg (13.2 lb)

DG4V4-01-*A/B = 4.5 kg (10 lb)

Mounting Attitude

No restrictions.

Service Information

It is recommended that, should any mechanical or electronic repair be necessary, valves be returned to the nearest Danfoss repair center.

The products will be refurbished as necessary and retested to specification before return.

This page left intentionally blank.

Products we offer:

- Cartridge valves
- DCV directional control valves
- Electric converters
- Electric machines
- Electric motors
- Gear motors
- Gear pumps
- Hydraulic integrated circuits (HICs)
- Hydrostatic motors
- Hydrostatic pumps
- Orbital motors
- PLUS+1° controllers
- PLUS+1° displays
- PLUS+1° joysticks and pedals
- PLUS+1° operator interfaces
- PLUS+1° sensors
- PLUS+1° software
- PLUS+1° software services, support and training
- Position controls and sensors
- PVG proportional valves
- Steering components and systems
- Telematics

Hydro-Gear

www.hydro-gear.com

Daikin-Sauer-Danfoss

www.daikin-sauer-danfoss.com

Danfoss Power Solutions is a global manufacturer and supplier of high-quality hydraulic and electric components. We specialize in providing state-of-the-art technology and solutions that excel in the harsh operating conditions of the mobile off-highway market as well as the marine sector. Building on our extensive applications expertise, we work closely with you to ensure exceptional performance for a broad range of applications. We help you and other customers around the world speed up system development, reduce costs and bring vehicles and vessels to market faster.

Danfoss Power Solutions – your strongest partner in mobile hydraulics and mobile electrification.

Go to www.danfoss.com for further product information.

We offer you expert worldwide support for ensuring the best possible solutions for outstanding performance. And with an extensive network of Global Service Partners, we also provide you with comprehensive global service for all of our components.

Local address:

Danfoss Power Solutions (US) Company
2800 East 13th Street
Ames, IA 50010, USA
Phone: +1 515 239 6000

Danfoss Power Solutions GmbH & Co. OHG
Krokamp 35
D-24539 Neumünster, Germany
Phone: +49 4321 871 0

Danfoss Power Solutions ApS
Nordborgvej 81
DK-6430 Nordborg, Denmark
Phone: +45 7488 2222

Danfoss Power Solutions Trading (Shanghai) Co., Ltd.
Building #22, No. 1000 Jin Hai Rd
Jin Qiao, Pudong New District
Shanghai, China 201206
Phone: +86 21 2080 6201