

Data Sheet

Pressure transmitter Type **MBS 33M**

For high accuracy marine applications



The high accuracy transmitter MBS 33M is designed for use in almost all marine applications, and offers a reliable pressure measurement, even under harsh environmental conditions.

The flexible pressure transmitter programme covers a 4 – 20 mA output signal, absolute or gauge (relative) versions, measuring ranges from 0 – 1 to 0 – 600 bar. A wide range of pressure and electrical connections.

Excellent vibration stability, robust construction, and a high degree of EMC / EMI protection equip the pressure transmitter to meet the most stringent marine requirements.

Features

- Designed for use in severe maritime environments
- All relevant marine approvals
- Enclosure and wetted parts of acid-resistant stainless steel (AISI 316L)
- Pressure ranges in relative (gauge) or absolute from 0 up to 600 bar
- Standard output signal: 4 – 20 mA
- A wide range of pressure connections
- Fully digitally compensated
- For use in ATEX Zone 2 explosive atmospheres
- UL approved

Product specification

Technical data

Table 1: Performance (EN 60770)

Accuracy (incl. non-linearity, hysteresis and repeatability)		≤ ± 0.3% FS (typ.)
		≤ ± 0.8% FS (max.)
Non-linearity BFSL (conformity)		≤ ± 0.2% FS
Hysteresis and repeatability		≤ ± 0.1% FS
Thermal zero point shift		≤ ± 0.1% FS / 10K (typ.)
		≤ ± 0.2% FS / 10K (max.)
Thermal sensitivity (span) shift		≤ ± 0.1% FS / 10K (typ.)
		≤ ± 0.2% FS / 10K (max.)
Response time:	Liquids with viscosity < 100 cSt	< 4 ms
Overload pressure (static)		6 × FS (max. 1500 bar)
Burst pressure		6 × FS (max. 2000 bar)
Power-up time		< 50 ms
Durability, P: 10 – 90% FS		> 10 × 10 ⁶ cycles
MTTFd - Calculation based on the SN 29500		> 100 years

Table 2: Electrical specifications

Nom. output signal (short-circuit protected)	4 – 20 mA
Supply voltage [U _B] (polarity protected)	9 – 32 V DC (12 / 24 V DC nom.)
Supply voltage dependency	< 0.1% FS / 10 V
Output limitation	22.4 mA
Load	R _L ≤ (U _B - 9 V) / 0.02 A[Ω]

Table 3: Environmental conditions

Sensor operating temperature	Normal	-40 – 85 °C
	ATEX Zone 2	-20 – 85 °C
Media temperature range		-40 – 85 °C
Ambient temperature range (depending on electrical connection)		See Electrical connections
Compensated temperature range		0 – 80 °C
Transport/storage temperature range		-50 – 85 °C
EMC – Emission		EN 61000-6-3
EMC – Immunity		EN 61000-6-2
Insulation resistance		> 100 MΩ at 500 V DC
Vibration stability	Sinusoidal	15.9 mm-pp, 5 Hz – 25 Hz 20 g, 25 Hz – 2 kHz IEC 60068-2-6
	Random	7.5 g _{rms} , 5 Hz – 1 kHz IEC 60068-2-64
Shock resistance	Shock	500 g / 1 ms IEC 60068-2-27
	Free fall	1 m IEC 60068-2-32
Enclosure (depending on electrical connection)		See Electrical connections

Table 4: Explosive atmospheres

Zone 2 applications ⁽¹⁾	II 3G Ex ec IIA T4 Gc -20°C<Ta<+85°C	EN60079-0; EN60079-7
------------------------------------	---	----------------------

⁽¹⁾ The Pressure transmitter must be installed where it cannot be exposed to impact in normal use.

Table 5: Mechanical characteristics

Materials	Wetted parts	EN 10088-1; 1.4404 (AISI 316 L)
	Enclosure	EN 10088-1; 1.4404 (AISI 316 L)
	Electrical connections	See Electrical connections
Net weight (depending on pressure connection and electrical connection)		0.2 – 0.3 kg

Dimensions / Combinations

Table 6: Dimensions / Combinations

Type code	A1	F4	A6	H3	
	EN175301-803-A, Pg9	2 m screened cable	EN 175301-803-A, Pg 11	EN175301-803-A, M20	
	G 1/4 A (EN 837)	G 1/2 A (EN 837)	1/4 – 18 NPT	1/2 – 14 NPT	G 1/4 (DIN 3852-E)
Type code	AB04	AB08	AC04	AC08	GB04
Recommended torque ⁽¹⁾	30 – 35 Nm	30 – 35 Nm	2 – 3 turns after finger tightened	2 – 3 turns after finger tightened	30 – 35 Nm

⁽¹⁾ Depends on different parameters as packing material, mating material, thread lubrication and pressure level

Electrical connections

Type code	A1	F4	A6	H3
	EN 175301-803-A, Pg 9	Cable screened ship 2m	EN 175301-803-A, Pg 11	EN 175301-803-A, M20
Ambient temperature	-40 – 85 °C	-30 – 85 °C	-40 – 85 °C	-40 – 85 °C
Enclosure (IP protection fulfilled together with mating connector)	IP65	IP67	IP65	IP65
Material	Glass filled polyamid, PA 6.6	RTFRO cable with shrinkage tubing	Glass filled polyamid, PA 6.6	Glass filled polyamid, PA 6.6
Electrical connection, 4 – 20 mA output (2 wire)	Pin1: + supply Pin 2: ÷ supply Pin 3: not used Earth: Connected to MBS enclosure	Brown wire: + supply Black wire: ÷ supply Blue wire: Not used Screen connected to MBS enclosure	Pin1: + supply Pin 2: ÷ supply Pin 3: not used Earth: Connected to MBS enclosure	Pin1: + supply Pin 2: ÷ supply Pin 3: not used Earth: Connected to MBS enclosure


NOTE:

Please check [Store.danfoss.com](https://store.danfoss.com) to find the correct variant for your requirements

Ordering

Ordering standard

Figure 1: Ordering standard



NOTE: Non-standard build-up combinations may be selected. However, minimum order quantities may apply. Please contact your local Danfoss office for further information or request on other versions.

Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

Table 7: Certificates and declarations

File name	Document type	Document topic	Approval authority
2008558TA	Marine - Safety Certificate	-	LR
08472-E0 BV	Marine - Safety Certificate	-	BV
18-LD1740756-1-PDA	Marine - Safety Certificate	-	ABS
TAA000025S rev. 1	Marine - Safety Certificate	-	DNV GL
TJ18T00028	Marine - Safety Certificate	-	CCS
TA20389M	Marine - Safety Certificate	-	NKK
SMS.W.II-2179-C.0	Marine - Manufacturing Permission	-	BV
E227388	Explosive - Safety Certificate	Hazardous Locations	UL
E31024	Electrical - Safety Certificate	-	UL
E311982	Electrical - Safety Certificate	-	UL
E494625	Electrical - Safety Certificate	-	UL
064G9615.11	EU-UK Declaration	ATEX / EMC / RoHS	Danfoss
CRN.OF18477.5123467890YTN	Pressure - Safety Certificate	CRN	TSSA
E510763	Electrical Safety Certificate	-	UL
CPH 04967-AE006	Marine Safety Certificate	-	KR
ELE098420XG	Marine Safety Certificate	-	RINA
LLC CDC EURO-TYSK UA.TR.089.1015.05-22	Pressure Certificate	-	LLC CDC EURO-TYSK
Danfoss UA 2023-01-10	UA Declaration	EMC/LVD	Danfoss
Danfoss UA 2023-01-10	UA Declaration	PED	Danfoss
EAC KZ 7500533.13.12.00845	EAC Declaration	EMC	EAC

Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at store.danfoss.com.

Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at www.danfoss.com/en/service-and-support/documentation.

Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at www.danfoss.com/en/service-and-support/learning.

Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: www.danfoss.com/en/choose-region.

Spare Parts



Get access to the Danfoss spare parts and service kit catalog right from your smartphone. The app contains a wide range of components for air conditioning and refrigeration applications, such as valves, strainers, pressure switches, and sensors.

Download the Spare Parts app for free at www.danfoss.com/en/service-and-support/downloads.

Danfoss A/S

Climate Solutions • danfoss.com • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.