



ECfoil Mirror

An effective system for keeping the mirror completely steam free.

Fast and easy installation where the self-adhesive side of the heating foil is placed on the back of the mirror.

Low energy consumption and automatic activation when the light is switched on.

2YEAR
WARRANTY

Product

Product specifications

Benefits • Fast and easy installation • Low energy consumption • Automatic activation Compliance symbols:  Standard compliance • EN 60335-1 + 60335-2-30	Nominal voltage	230 V~
	Output	200 W/m ²
	Max. ambient temperature	80°C
	IP Class	44
	Protection class	Class II - 
	Cold tail length	95 cm

Types

Item no.	Type	Dimensions	Wattage	EAN no.
088L1600	ECfoil Mirror	274 x 358 mm	17,5 W	5703466180853
088L1601	ECfoil Mirror	410 x 524 mm	40 W	5703466180860
088L1602	ECfoil Mirror	708 x 524 mm	70 W	5703466180877