



068R9798



$P_{\text{test}} = \text{max. } 37.5 \text{ bar (540 psig)}$



11-11




Danfoss
68U04.11.11

Max. 100°C
(212°F)

Max. 850°C
(1550°F)






Setting of TUH / TCHE



Lower setting

Factory setting

Higher setting



Valve type	°C / turn				
	R134a	R404A/R507	R407C	R410A	R22
TUH	1.8	1	1.2	0.7	1.1
TCHE	1.4	0.8	1	1.4	1