

Check Valves

FPR11/2

Check Valve, In-line, Female Port
210 bar [3000psi] • 310 l/min [82 US gpm]

DESCRIPTION AND OPERATION


This is an in-line check valve where free flow takes place from port 1 to 2 and is blocked from port 2 to 1.

SCHEMATIC



DIMENSIONS


mm [in]



PERFORMANCE DATA

Rated pressure	210 bar [3000psi]
Rated flow	310 l/min [82 US gpm]
Weight	2.10 kg [4.63 lbs]

PERFORMANCE CURVES



MODEL CODE

FPR11/2 - 0.5 BAR

Crack Pressure

Code	Bar
0.5	0.5
1.0	1.0
2.5	2.5
5.0	5.0
10.0	10.0