Date of issue: 11.07.2024 Revision date: - Version/Replaced version: 1.0/-

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : 160SZ

UFI : PQE0-A040-V00U-WTYC

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Use of the substance/mixture : Refrigeration lubricants

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer/Supplier

Danfoss Commercial Compressors S.A Rue du Pou du Ciel 01600 Reyrieux - France T +33 (0)4 74 00 28 29 contact.cc@danfoss.com

Safety Data Sheet: DLAC Dienstleistungsagentur Chemie GmbH, E-mail: sds@dlac-gmbh.de

1.4. Emergency telephone number

Country	Organisation/Company	Address	Emergency number
Germany	Giftinformationszentrum (GIZ-Nord) Universitätsmedizin Göttingen - Georg-August-Universität	Robert-Koch Straße 40 37075 Göttingen	+49 551 19240

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008 [CLP]

No labelling applicable

2.3. Other hazards

The mixture does not contain substance(s) classified as PBT or vPvB in concentrations above 0.1%. The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605.

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

This mixture does not contain any substances to be mentioned according to the criteria of section 3.2 of REACH Annex II.

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general : Get medical advice/attention if you feel unwell. If possible show him this sheet. Failing this, show him the packaging or label. Never give anything by mouth to an unconscious person. Place the affected person in the recovery position.

First-aid measures after inhalation : Remove victim to fresh air and keep at rest in a position comfortable for breathing.

First-aid measures after skin contact : Remove/Take off immediately all contaminated clothing. Wash with plenty of soap and water.

First-aid measures after eye contact : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

11.07.2024 EN (English) 1/6

Safety Data Sheet

according to Regulation (EU) 2020/878

First-aid measures after ingestion : Rinse mouth. Drink water as a precaution. Do NOT induce vomiting.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/injuries after skin contact : Causes mild skin irritation. Prolonged or repeated contact may cause irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Use extinguishing agents that suit the environment. Carbon dioxide. Extinguishing powder.

Water spray. For a significant fire: Alcohol resistant foam.

Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire

: Carbon dioxide. Carbon monoxide. Toxic gases and vapours.

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Prevent fire-fighting water from entering

environment.

Protection during firefighting : Use a self-contained breathing apparatus and also a protective suit.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Provide adequate ventilation. Do not breathe vapours. Avoid contact with skin and eyes.

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

: Use personal protective equipment as required. In case of inadequate ventilation wear respiratory protection. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Prevent entry to sewers and public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up

Protective equipment

: Wipe up with absorbent material (for example cloth). Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Keep in suitable, closed containers for disposal. Dispose of in accordance with relevant local regulations.

6.4. Reference to other sections

Exposure controls and personal protection, see section 8. Concerning disposal elimination after cleaning, see section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling

: Ensure good ventilation of the work station. Avoid breathing vapours, spray. Avoid contact with skin and eyes. Wear personal protective equipment.

Hygiene measures

: Handle in accordance with good industrial hygiene and safety procedures. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. When using do not eat, drink or smoke.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions

: Store in original container. Keep container tightly closed. Store in a dry, cool and well-ventilated place. Protect from heat and direct sunlight.

Prohibitions on mixed storage : Keep away from food, drink and animal feedingstuffs

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Appropriate engineering controls

: Provide local exhaust or general room ventilation to minimize vapour concentrations.

Hand protection

: Wear suitable gloves (EN 374 or equivalent). Nitrile rubber, neoprene. > 0.35 mm. The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

11.07.2024 EN (English) 2/6

Safety Data Sheet

according to Regulation (EU) 2020/878

Eye protection : Chemical goggles or safety glasses (EN 166).

Skin and body protection : Wear suitable protective clothing.

Respiratory protection : Where exposure through inhalation may occur from use, respiratory protection equipment is

recommended.

Environmental exposure controls : Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Liquid.

Colour : Colourless to yellow

Odour : Mild

Melting point/freezing point : No data available Boiling point or initial boiling point and boiling : No data available

range

Flammability : No data available Lower and upper explosion limit : No data available

Flash point : 270 °C (Tagliabue Open Cup)

Auto-ignition temperature : No data available
Decomposition temperature : No data available
pH : No data available

Kinematic viscosity : 33.7 mm²/s (40 °C); 5.9 mm²/s (100 °C)

Solubility : Water: practically insoluble

Partition coefficient n-octanol/water (log value) : Not applicable

Vapour pressure : No data available

Density and/or relative density : 0.977 (20 °C)

Relative vapour density : No data available

Particle characteristics : Not applicable

9.2. Other information

9.2.1. Information with regard to physical hazard classes

Explosive properties : None
Oxidising properties : None

9.2.2. Other safety characteristics

Pour point : ca. -46 °C

SECTION 10: Stability and reactivity

10.1. Reactivity

No dangerous reactions known.

10.2. Chemical stability

Stable under use and storage conditions as recommended in section 7.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

High temperature. Sources of ignition. Oxidizing agents.

10.5. Incompatible materials

Oxidizing agents. Strong acids. Strong bases.

10.6. Hazardous decomposition products

No hazardous decomposition products known at room temperature. In case of fire: Carbon dioxide. Carbon monoxide. Toxic gases and vapours.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity : Not classified

Based on available data, the classification criteria are not met

Skin corrosion/irritation : Not classified

Based on available data, the classification criteria are not met

Serious eye damage/irritation : Not classified

Based on available data, the classification criteria are not met

11.07.2024 EN (English) 3/6

Safety Data Sheet

according to Regulation (EU) 2020/878

Respiratory or skin sensitisation : Not classified

Based on available data, the classification criteria are not met

Germ cell mutagenicity : Not classified

Based on available data, the classification criteria are not met

Carcinogenicity : Not classified

Based on available data, the classification criteria are not met

Reproductive toxicity : Not classified

Based on available data, the classification criteria are not met

Specific target organ toxicity (single exposure) : Not classified

Based on available data, the classification criteria are not met

Specific target organ toxicity (repeated

exposure)

: Not classified

Based on available data, the classification criteria are not met

Aspiration hazard : Not classified

Based on available data, the classification criteria are not met

11.2. Information on other hazards

11.2.1. Endocrine disrupting properties

Endocrine disruption for human health : The mixture has no endocrine disrupting properties.

11.2.2. Other information

Potential adverse human health effects and

symptoms

: Causes mild skin irritation. Prolonged or repeated contact may cause irritation.

SECTION 12: Ecological information

12.1. Toxicity

Acute aquatic toxicity : Not classified Chronic aquatic toxicity : Not classified

12.2. Persistence and degradability

160SZ		
Persistence and degradability	Readily biodegradable.	
Biodegradation	63.1 %, 28 d (OECD 301 B)	

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Endocrine disrupting properties

Endocrine disruption for the environment : The mixture has no endocrine disrupting properties.

12.7. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Regional legislation (waste) : Dispose in a safe manner in accordance with local/national regulations.

Waste treatment methods : Do not empty into drains.

Waste disposal recommendations : Empty the packaging completely prior to disposal.

Waste code : The valid EWC waste code numbers are source related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC

to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA

14.1. UN number or ID number

UN-No. (ADR) : Not applicable
UN-No. (IMDG) : Not applicable
UN-No. (IATA) : Not applicable

14.2. UN proper shipping name

Proper Shipping Name (ADR) : Not applicable

11.07.2024 EN (English) 4/6

Safety Data Sheet

according to Regulation (EU) 2020/878

Proper Shipping Name (IMDG) : Not applicable
Proper Shipping Name (IATA) : Not applicable

14.3. Transport hazard class(es)

ADR

Transport hazard class(es) (ADR) : Not applicable

IMDG

Transport hazard class(es) (IMDG) : Not applicable

IATA

Transport hazard class(es) (IATA) : Not applicable

14.4. Packing group

Packing group (ADR) : Not applicable
Packing group (IMDG) : Not applicable
Packing group (IATA) : Not applicable

14.5. Environmental hazards

Dangerous for the environment : No Marine pollutant : No

Other information : No supplementary information available.

14.6. Special precautions for user

Overland transport

Not applicable

Transport by sea

Not applicable

Air transport

Not applicable

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on REACH Annex XIV (Authorisation List).

REACH Candidate List (SVHC)

Contains no substance(s) listed on the REACH Candidate List.

PIC Regulation (Prior Informed Consent)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals).

POP Regulation (Persistent Organic Pollutants)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants).

Explosives Precursors Regulation (2019/1148)

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors).

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances).

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

Chemical safety assessments for substances in this mixture were not carried out.

11.07.2024 EN (English) 5/6

Safety Data Sheet according to Regulation (EU) 2020/878

SECTION 16: Other information

Data sources REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE

COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending

Regulation (EC) No 1907/2006.

Changes compared to the previous version

Abbreviations and acronyms:

Appleviations and actoriyms.		
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road	
CLP	Regulation (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures	
DMEL	Derived Minimal Effect Level	
DNEL	Derived No-Effect Level	
EC50	The effective concentration of substance that causes 50% of the maximum response (Median Effective Concentration)	
IATA	International Air Transport Association	
IMDG	"International Maritime Dangerous Goods Code" for the transport of dangerous goods by sea	
LC50	Lethal Concentration to 50 % of a test population (Median Lethal Concentration)	
LD50	Lethal Dose to 50% of a test population (Median Lethal Dose)	
NOEC/L	No Observed Effect Concentration/Level	
OECD	Organisation for Economic Cooperation and Development	
PBT	Persistent, Bioaccumulative and Toxic substance	
PNEC	Predicted No-Effect Concentration	
REACH	Regulation (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals	
SDS	Safety Data Sheet	
STP	Sewage Treatment Plant	
UFI	Unique Formula Identifier	
vPvB	Very Persistent and Very Bioaccumulative	

SDS EU (REACH Annex II)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.

11.07.2024 EN (English) 6/6