Directional Control Valves
MRV6-16

Manual Rotary Valve, 4-Way, Spool Type

210 bar [3000 psi] • 45 l/min [12 US gpm]

DESCRIPTION AND OPERATION

This is a 4-way, spool type, 3 position manually operated semi-rotary directional control valve.
In the center position, ports 1, 3 and 4 are connected to each other and port 2 is blocked. By rotating the manual actuator, the flow path will change from ports 3-2 and 1-4 to ports 3-4 and 1-2.

SCHEMATIC



DIMENSIONS

mm [in]



Installation torque
108-122 Nm [80-90 ft. lbs]

PERFORMANCE DATA

Rated pressure	**210 bar [3000 psi]**
Rated flow	**45 l/min [12 US gpm]**
Weight	0.27 kg [0.59 lb]
Cavity	SDC16-4

PERFORMANCE CURVES



MODEL CODE

MRV6 - 16 - V - D - 6B

Seal Option

Code	Seal Kit
Omit-Buna-N	889625
V-Viton	566080

Actuator Option

O-Cartridge only (no actuator)
D-Lever (3-position detent)

Housing

Code	Ports	Aluminum Standard duty	Aluminum Heavy duty	Steel
0	No housing			
10T	#10 SAE			02-175141
12T	#12 SAE	566411		02-175142
6B	3/4" BSP	02-175468		
10H	#10 SAE		876729	
12H	#12 SAE		876731	
4G	1/2" BSP		876728	02-175143
6G	3/4" BSP		876730	02-175144

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].
* Additional housings available