

Directional Control Valves

CP712-11


Directional Control Valve, 2-Way, Spool Type, Hydraulic Pilot, External Drain

450 bar [6500 psi] • 130 l/min [34 US gpm]


DESCRIPTION AND OPERATION

This is a 2-way, spool type, hydraulically piloted directional control valve with external drain. It is available in normally open or normally closed configurations between ports 2 and 3 that shift when pilot pressure is applied to port 1. Due to the external drain, the pilot pressure required shift the valve is dependent on the pressure in port 4, which would normally be connected to tank. Due to the high pressure rating, this valve is ideal for use in transmission circuits to by-pass flow dividers.

SCHEMATIC




DIMENSIONS



PERFORMANCE DATA

| | |
|-------------------------------------|---|
| Rated pressure | 450 bar [6500 psi] |
| Rated flow @ 7 bar [100 psi] | 130 l/min [34 US gpm] |
| Leakage | 328 ml/min [20 in ³ /min] @ 210 bar [3000 psi] |
| Weight | 0.61 kg [1.34 lb] |
| Cavity | SDC16-4 |

PERFORMANCE CURVES



MODEL CODE

CP712 - 11 - U - 0 - C - 040

Seal Option

| Code | Seal kit |
|------------|----------|
| U-Urethane | 120677 |

Housing

| Code | Ports & Material | Housing Model Code |
|------|------------------|--------------------|
| 0 | No Housing | |
| 6B | AL, 3/4 BSP | CP16-4-6B |
| 8B | AL, 1 BSP | CP16-4-8B |
| 12S | AL, #12 SAE | CP16-4-12S |
| 16S | AL, #16 SAE | CP16-4-16S |
| S16S | Steel, #16SAE | CP16-4-S16S |

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].
* Additional housings available

Shift Pressure

| Code | Bar | [Psi] |
|------|-----|-------|
| 040 | 2.8 | [40] |
| 080 | 5.5 | [80] |

Spool Configuration

0-Normally Open
C-Normally Closed