

# Flow Control Valves

## PFR12-10


Flow Control, Partially Adjustable, Pressure Compensated, Priority Type

350 bar [5000 psi] • 38 l/min [10 US gpm]

### DESCRIPTION AND OPERATION

This is a partially adjustable, priority type, pressure compensated flow control valve, where the flow from port 3 will remain constant regardless of the pressure difference across the valve, while excess flow passes from port 1 to 2. Flow enters at port 1 and passes across a fixed orifice in the spool, which creates a pressure drop. This causes the spool to move back against the spring, which then restricts the outlet flow. Port 1 then opens to port 2 to allow excess flow to pass. The regulated flow will always take priority and remains constant if the working pressure is higher in either port 2 or port 3.

### SCHEMATIC



### PERFORMANCE DATA

Rated pressure	350 bar [5000 psi]
Rated flow	38 l/min [10 US gpm]
Max inlet flow	64 l/min [17 US gpm]
Flow range	0.4-37.8 l/min [0.1-10 US gpm]
Flow accuracy	0.4-1.9 l/min [0.1-0.49 US gpm] ±20%
	1.9-7.5 l/min [0.5-1.99 US gpm] ±15%
	7.6-37.8 l/min [2.0-10.0 US gpm] ±10%
Weight	0.25 kg [0.54 lb]
Cavity	SDC10-3

### MODEL CODE

PFR12 - 10 - V - C - A - 2G - 1.0

#### Seal Option

Code	Seal Kit
Omit-Buna - N	565804
V-Viton	889599

#### Adjustment Option

C - Tamper Resistant  
K - Knob  
S - External

#### Housing Material

Omit - No housing  
A - Aluminum  
S - Steel

#### Flow Setting

Code - Flow in US gpm  
Specify in 0.1 gpm increments within flow range  
Example

Code	l/min	[US gpm]
1.0	4.0	1.0


#### Housing

Code	Ports	Aluminium Heavy duty	Steel
0	No housing		
2G	1/4" BSP	876705	
3G	3/8" BSP	876714	
6H	#6 SAE	876704	
8H	#8 SAE	876711	
2G	1/4" BSP		02-175127
3G	3/8" BSP		02-175128
6T	#6 SAE		02-175124
8T	#8 SAE		02-175125

\* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].  
\* Additional housings available

### DIMENSIONS


mm [in]



Installation torque  
47-54 Nm [35-40 ft. lbs]

### PERFORMANCE CURVES

#### Flow Compensation



A - Port 3, priority (regulated outlet) pressurized.  
B - Port 2, (bypass outlet) pressurized.