

## Data Sheet

Gas detecting sensor  
Type **DGS**

Refrigerant gas detection for safeguarding commercial buildings.



DGS sensors can be used in stand-alone or integrated systems, where continuous real-time, automatic monitoring with Danfoss ADAP-KOOL® Refrigeration Control & Monitoring System and/or Building Management Systems is applied.

DGS supports our customers in complying with environmental F-Gas Regulations and Health & Safety requirements on new or existing systems in:

- supermarkets
- process refrigeration plants
- refrigerated storage and warehousing
- special application areas/zones

Typical refrigerant gas applications include:



- halocarbons: HFCs, HCFCs, CFCs
- carbon dioxide (CO<sub>2</sub>/R744)
- hydrocarbons (e.g. R290)
- other special application gases to customer request

Sensing technology varies to make the best detection for a given gas, in terms of performance and cost. DGS-IR is based on infra-red sensor technology, DGS-SC is based on semi-conductor and DGS-PE is based on pellistor.

## Product specification














### Technical Data

Table 1: Technical data

<b>Power supply</b>	24 V DC $\pm$ 20 % ; reverse polarity protected 24 V AC - 10 % / + 15 %		
<b>Power Consumption (24 V DC)</b>	Max. 250 mA (6 VA)		
<b>Digital output</b>	Alarm acknowledge and test alarm: Potential-free contact Alarm relay /fault relay: 40 V AC/DC, 0.5 A, change-over contact (SPDT) Critical relay: normally closed (SIL II compliant), warning relay: normally open		
<b>Analogue output signal</b>	Proportional, overload and short-circuit proof, load $\leq$ 500 Ohm Measuring range: 0 – 10 V / 2 – 10 V / 0 – 20 mA / 4 – 20 mA		
<b>MODBUS Physical</b>	5 V DC, 250 mA max. overload, short-circuit and reverse-polarity protected		
Enclosure rate	IP 65		
Humidity range	15 – 90 % RH not-condensing		
Burning behaviour	UL 94 V2		
Housing colour	Black		
Dimensions (W x H x D in mm)	94 x 130 x 57		
Installation	Wall mounting		
Cable entry	2 x M12 / 3 x M20		
Wire connection:	Power supply, MODBUS: Screw-type terminals 0.25 – 2.5 mm <sup>2</sup> Analogue output, Digital input: Screw-type terminals 0.25 – 1.3 mm <sup>2</sup> Sensor head: 3-pin plug connector		
<b>Sensor information</b>	DGS-IR (CO <sub>2</sub> )	DGS-SC (HFC)	DGS-PE (Propane)
Temperature range	-35 – 50 °C	-30 – 60 °C	-30 – 60 °C
Response time T90	<90 sec.	$\leq$ 150 sec.	<15 sec.
Recovery time, T0	90 sec.	180 sec.	120 sec.
Maximum calibration interval	60 months	12 months	6 months
Measuring range	0 – 20000 ppm	0 – 2000 ppm	0 – 5000 ppm
Lowest threshold	10% of the measuring range	10% of the measuring range	10% of the measuring range
Default alarm threshold	5000 ppm	500 ppm	800 ppm
<b>Compliance</b>	 EN61010-1  No61010-1 <small>Intertek</small>		
<b>B&amp;L - Buzzer and Light</b> (option by product selection)	Light (LED): Red / yellow /green (alarm - fault - operation - service) Buzzer: >85 dB (A) (0.1 distance ) 2300 Hz $\pm$ 300 Hz		

## Ordering

**Table 2: Ordering**

DGS Sensors			Spares and Accessories		
Product Description	Code no.		Product Description		Code no.
DGS-SC HFC grp 1 <sup>(1)</sup>	080Z2803	     	Spare sensor HFC grp 1 <sup>(1)</sup>	Spare	080Z2815
DGS-SC HFC grp 2 <sup>(1)</sup>	080Z2804		Spare sensor HFC grp 2 <sup>(1)</sup>	Spare	080Z2816
DGS-SC HFC grp 3 <sup>(1)</sup>	080Z2805		Spare sensor HFC grp 3 <sup>(1)</sup>	Spare	080Z2817
DGS-PE propane	080Z2806		Spare sensor propane	Spare	080Z2818
DGS-IR CO <sub>2</sub>	080Z2800		Spare sensor CO <sub>2</sub>	Spare	080Z2813
DGS-IR CO <sub>2</sub> 5 m	080Z2801		Spare sensor CO <sub>2</sub> - 5 m	Spare	080Z2814
DGS-IR 2 CO <sub>2</sub> - 5 m	080Z2802		Hand-held Service Tool	Accessory	080Z2820
DGS-SC HFC grp 1 <sup>(1)</sup> + B&L	080Z2809		Strobe & Horn	Accessory	080Z2819
DGS-SC HFC grp 2 <sup>(1)</sup> + B&L	080Z2810	     	Splash guard	Accessory	148H6226
DGS-SC HFC grp 3 <sup>(1)</sup> + B&L	080Z2811		Duct set	Accessory	148H6236
DGS-PE propane + B&L	080Z2812		Calibration adaptor	Accessory	148H6232
DGS-IR CO <sub>2</sub> + B&L	080Z2807		Remote kit	Accessory	148H6238
DGS-IR CO <sub>2</sub> 5 m + B&L	080Z2808		Power Supply AK-PS075	Accessory	080Z0053

<sup>(1)</sup> HFC grp 1: R1234ze, R454C, **R1234yf**, R452A, R454A, R455A, R454B, R513A  
HFC grp 2: R407F, R416A, R417A, R407A, R422A, R427A, R449A, R437A, **R134A**, R438A, R422D  
HFC grp 3: R448A, R125, R404A, R32, R507A, R434A, R410A, R452B, **R407C**, R143B

**Bold = calibration gas**

**NOTE:**

DGS is also available for alternative refrigerant gases on request. Please contact your local Danfoss Sales Office for details.

## Certificates, declarations, and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

Some approvals may change over time. You can check the most current status at danfoss.com or contact your local Danfoss representative if you have any questions.

**Table 3: Certificates, declarations, and approvals**

File name	Document type	Document topic	Approval authority
Intertek 4000518	Electrical - Safety Certificate	-	Intertek
080R1223.AB	EU Declaration	EMCD/LVD	Danfoss

## Online support

Danfoss offers a wide range of support along with our products, including digital product information, software, mobile apps, and expert guidance. See the possibilities below.

### The Danfoss Product Store



The Danfoss Product Store is your one-stop shop for everything product related—no matter where you are in the world or what area of the cooling industry you work in. Get quick access to essential information like product specs, code numbers, technical documentation, certifications, accessories, and more.

Start browsing at [store.danfoss.com](https://store.danfoss.com).

### Find technical documentation



Find the technical documentation you need to get your project up and running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more.

Start searching now at [www.danfoss.com/en/service-and-support/documentation](https://www.danfoss.com/en/service-and-support/documentation).

### Danfoss Learning



Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications, industry topics, and trends that will help you do your job better.

Create your Danfoss Learning account for free at [www.danfoss.com/en/service-and-support/learning](https://www.danfoss.com/en/service-and-support/learning).

### Get local information and support



Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert—all in your own language.

Find your local Danfoss website here: [www.danfoss.com/en/choose-region](https://www.danfoss.com/en/choose-region).

---

#### Danfoss A/S

Climate Solutions • [danfoss.com](https://danfoss.com) • +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.

All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.