

# Solenoid Valves

## SV15-34-05


Solenoid Valve, 4-way, 3-position, Spool Type  
**230 bar [3300 psi] • 60 l/min [16 US gpm]**



### OPERATION AND DESCRIPTION


This is a 4-way, 3-position, spool type, direct acting solenoid valve. In the center condition, ports 2, 4 and 1 are open while port 3 is blocked. By energizing one coil, port 3 opens to 2 and port 4 to 1. When energizing the other coil, port opens port 3 to 4 and port 2 to 1. This valve provides a directional control function with a neutral de-energized state allowing the work ports to be referenced to tank, removing locked in pressure with the inlet port 3 closed. It can be used in any hydraulic application where an actuator needs to be controlled in both directions. Always check the operating envelope to make sure the valve will work under the required application conditions. Port 1 is not intended for use as inlet (Tank only).

### SCHEMATIC



### DIMENSIONS

mm [in]





### PERFORMANCE DATA

<b>Rated Pressure*</b>	<b>230 bar [3300 psi]**</b>
<b>Flow Capability</b>	<b>60 l/min [16 US gpm]</b>
<b>Coil Options</b>	<b>M19</b>
<b>Weight</b>	<b>1.4 kg [3.09 lb]</b>
<b>Cavity</b>	<b>NCS 12/4</b>

\*Rated Pressure based on NFPA fatigue test standards (at 1 million cycles)

\*\*Valve can operate with an inlet pressure of 315 bar [4600 psi] at port 3 for 300,000 cycles

### PERFORMANCE CURVES



### MODEL CODE

**SV15 - 34 - 05 - 12D - DE - V - F - 8S**

#### Coil Voltage

Code	Coil Voltage
00	No Coil, nut included*
10D	10 VDC
12D	12 VDC
20D	20 VDC
24D	24 VDC
110A	110 VAC**
220A	220 VAC**

\*Standard Coil - Plastic coil nut and o-rings (p/n 173800978)

\*\*DIN only - external rectifier needed

#### Connector Type

Code	Connector Type
00	No Coil
AJ	Amp Junior
AJD	Amp Junior with Diode
DE	Deutsch
DED	Deutsch with Diode
FL	Flying Leads
DN	DIN 43650

#### Housing

Code	Ports & Material	Housing Model Code
00	No Housing	
8S	#8 SAE, AL	NCS12/4-L-8S
12S	#12 SAE, AL	NCS12/4-L-12S
4B	1/2 BSP, AL	NCS12/4-L-1/2
6B	3/4 BSP, AL	NCS12/4-L-3/4

\* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].

\* Additional housings available

#### Filter Option

0mit - No filter  
 F - Filter 300 µm

#### Seal Option

Code	Seal kit
B-Buna - N	11115884
V-Viton	11115885