

ENGINEERING
TOMORROW



Case Story | Sector Coupling

Sector coupling helps **Sønderborg Hospital** reach its decarbonization goals

Sygehus Sønderjylland, a hospital located in Sønderborg, Denmark, has partnered with Danfoss Sector Coupling Solutions and the district heating utility company, Sønderborg Varme, to reduce its CO₂ emissions.

[Sectorcoupling.danfoss.com](https://sectorcoupling.danfoss.com)

The challenge

Since the start of the energy crisis in 2022, companies across Europe have been looking for ways to reduce their reliance on fossil fuels and find more efficient ways of heating and cooling their buildings. Hospitals are no exception. However, unlike corporate entities, hotels or restaurants, hospitals can't simply increase the price of their products to offset energy price increases. They must find a way to improve their buildings' energy efficiency and identify sustainable energy sources.

For Sygehus Sønderjylland, the drive to decarbonize was about more than just financial savings. The hospital aimed to achieve carbon neutrality, and its management recognized the potential of combining heat recovery with district heating to reach that goal. Therefore, the hospital partnered with Danfoss and the local heating utility to explore ways to reduce both their energy bill and carbon emissions simultaneously.

The hospital expects to
reduce the yearly amount
of energy it purchases by

28,300 MWh

The Solution: Unlock the potential of excess heat

The hospital installed two new energy-efficient heat pumps and an updated hydronic heating and cooling system to replace its gas- and oil-based heating system and accompanying boilers. The heat pumps, powered by Energy Machines™, provide the hospital with cooling through an integrated critical equipment and comfort cooling system. Each pump is equipped with four Danfoss oil-free Turbocor® compressors, which provide exceptional efficiency, particularly for cooling applications, and are an ideal fit for cases with high cooling demand, such as hospitals. The hospital expects to reduce the amount of energy it purchases by 28,300 MWh each year.

The hospital uses the heat recovered from the cooling system to meet its process and comfort heat loads. When the system generates more heat than the hospital needs, the heating utility – Sønderborg Varme – transfers the excess heat to the district energy grid for use in heating private homes. In the cold months, where the cooling load is low and the heating demand is high, the hospital can use the bi-directional heat exchanger to supplement the heating delivered to the hospital through the grid. Once the system is fully implemented the hospital expects to sell back 15.800 MWh excess heat to the grid, which could cover the heat consumption of more than 877 average Danish households.

This not only helps the hospital lower its carbon footprint, but it also creates a more comfortable indoor climate for patients, staff, and the surroundings.



The Results: From energy consumer to energy provider

According to **Martin Brander**, Senior Business Development Manager, Sector Coupling Solutions, Danfoss, this case is an excellent example of how communities can create sustainable energy systems.



By capturing heat from the hospital's cooling system and channeling it into the local district heating network, the hospital transforms into an energy provider. It illustrates how we can design energy systems that meet both heating and cooling needs in a sustainable way.



The experiences gained from this project will also benefit other hospitals within the region, as **Jesper Møller Iversen**, Head of Finance and Planning at Sygehus Sønderjylland, points out.



With great pleasure, we wave goodbye to fossil fuels at the hospital in Sønderborg and welcome the green transition. As a large organization, we are pleased to be able to make our contribution to this important transition. We expect to gain a lot of valuable experiences, which can also benefit other hospitals in the region and throughout Europe.



About the installation

- ✓ Two Energy Machines™ heat pumps with a combined **capacity of 2.6 MW**
- ✓ Chilled water loop: **15°C/10-8°C**
- ✓ Cooling load in summer: **2 MW**
- ✓ Hot water loop: **45°C/65-75°C**
- ✓ Cooling load in winter: peak **1MW + 578kW**, **1MW base load**



Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.

About the Danfoss components

Electric expansion valves

- ETS
- ICM Flexline™ motor valves

Sensors & System protection

- Pressure Transmitters
- Pressure switches

Heat exchanger

- Microplate heat exchangers
- Gasketed heat exchangers

Check & Ball valves

- Check valves
- Shut-off ball valves

Solenoid valve

- EVR solenoid valves

Filter Drier / Sight glass

- Filter driers
- Sight glasses

Liquid level sensors

- AKS 4100

Electronic controls

- Electronic temperature controls
- Programmable controllers – MCX

VLT Inverter Drives

- Turbocor® oil-free compressors