

# Proportional Valves

## PRV10-POC


Proportional Relief Valve, Spool Type, Pilot Operated, Normally Closed

250 bar [3600 psi] • 76 l/min [20 US gpm]


### DESCRIPTION AND OPERATION

This is a pilot operated, spool type, normally closed, proportional relief valve. In the de-energized condition, the pressure setting will be at a maximum. As current is applied to the coil, the pressure setting of the valve will decrease proportionally. This valve is ideal for use in cooling circuits to regulate the speed of the fan.

### SCHEMATIC



### DIMENSIONS





### PERFORMANCE DATA

Rated pressure*	250 bar [3600 psi]
Rated flow	76 l/min [20 US gpm]
Recommended PWM frequency	200 Hz
Maximum Hysteresis	10%
Threshold current	0 A [12 VDC coil] 0 A [24 VDC coil]
Maximum control current	1.8 A [12 VDC coil] 0.9 A [24 VDC coil]
Coil Options	M19P
Weight	0.53 kg [1.17 lb]
Cavity	SDC10-2

\*Rated pressure based on NFPA fatigue test standards (at 1 million cycles)

### PERFORMANCE CURVES



### MODEL CODE

**PRV10 - POC - 215 - C - 12D - DE - E - B - 00**

#### Max Pressure Setting

Code - Pressure setting in bar (5 bar increments within specified Pressure Range)  
Example:

Code	Bar	Psi
60	60	[870]

#### Pressure Range

Code	Pressure Range
A	25-65 bar [360-940 psi]
Standard Setting	55 bar [800 psi]
B	55-135 bar [800-1960 psi]
Standard Setting	135 bar [1960 psi]
C	135-215 bar [1960-3100 psi]
Standard Setting	215 bar [3100 psi]

#### Coil Voltage

00 - No coil, nut included\*  
12D - 12 VDC  
24D - 24 VDC

\*Standard Coil - Plastic coil nut and o-rings (p/n 173802188)

#### Connector Type

00 - No coil  
AJ - AMP Junior  
DE - Deutsch  
DN - DIN 43650

#### Housing

Code	Ports & Material	Housing Model Code
00	No housing	
6S	AL, #6 SAE	CP10-2-6S
8S	AL, #8 SAE	CP10-2-8S
DG3B	AL, 3/8 BSP	SDC10-2-DG3B
DG4B	AL, 1/2 BSP	SDC10-2-DG4B

\* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].  
\* Additional housings available

#### Seal Option

Code	Seal kit
B - Buna - N	354000719
V - Viton	354000819

#### Adjustment Option

E - External  
F - Tamper resistant  
H - Hidden