

SEMiX302GAL17E4s



SEMiX® 2s

SEMiX302GAL17E4s

Features


- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability
- UL recognized, file no. E63532

Typical Applications*

- AC inverter drives
- UPS
- Electronic Welding

Remarks

- Case temperature limited to $T_C=125^{\circ}\text{C}$ max.
- Product reliability results are valid for $T_J=150^{\circ}\text{C}$
- Dynamic values apply to the following combination of resistors:
 $R_{Gon,main} = 1,95 \Omega$
 $R_{Goff,main} = 1,95 \Omega$
 $R_{G,X} = 2,2 \Omega$
 $R_{E,X} = 0,5 \Omega$



GAL

Absolute Maximum Ratings				
Symbol	Conditions		Values	Unit
IGBT				
V _{CES}	T _j = 25 °C		1700	V
I _C	T _j = 175 °C	T _c = 25 °C	516	A
		T _c = 80 °C	392	A
I _{Cnom}			300	A
I _{CRM}	I _{CRM} = 3xI _{Cnom}		900	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 1000 V V _{GE} ≤ 15 V V _{CES} ≤ 1700 V	T _j = 150 °C	10	µs
T _j			-40 ... 175	°C
Inverse diode				
V _{RRM}	T _j = 25 °C		1700	V
I _F	T _j = 175 °C	T _c = 25 °C	324	A
		T _c = 80 °C	238	A
I _{Fnom}			300	A
I _{FRM}	I _{FRM} = 2xI _{Fnom}		600	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 25 °C		1710	A
T _j			-40 ... 175	°C
Freewheeling diode				
V _{RRM}	T _j = 25 °C		1700	V
I _F		T _c = 25 °C	324	A
		T _c = 80 °C	238	A
I _{Fnom}			300	A
I _{FRM}	I _{FRM} = 2xI _{Fnom}		600	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 25 °C		1710	A
T _j			-40 ... 175	°C
Module				
I _{t(RMS)}			600	A
T _{stg}			-40 ... 125	°C
V _{isol}	AC sinus 50Hz, t = 1 min		4000	V

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT						
V _{CE(sat)}	I _C = 300 A	T _J = 25 °C		1.90	2.20	V
	V _{GE} = 15 V chipelevel	T _J = 150 °C		2.26	2.45	V
V _{CE0}	chipelevel	T _J = 25 °C		1.1	1.2	V
		T _J = 150 °C		1	1.1	V
r _{CE}	V _{GE} = 15 V	T _J = 25 °C		2.7	3.3	mΩ
	chipelevel	T _J = 150 °C		4.2	4.5	mΩ
V _{GE(th)}	V _{GE} =V _{CE} , I _C = 12 mA		5.2	5.8	6.4	V
I _{CES}	V _{GE} = 0 V	T _J = 25 °C			4	mA
	V _{CE} = 1700 V					mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		24		nF
C _{oes}		f = 1 MHz		1.00		nF
C _{res}		f = 1 MHz		0.76		nF
Q _G	V _{GE} = - 8 V...+ 15 V			2400		nC
R _{Gint}	T _J = 25 °C			2.50		Ω



SEMiX® 2s

SEMiX302GAL17E4s

Features


- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability
- UL recognized, file no. E63532

Typical Applications*

- AC inverter drives
- UPS
- Electronic Welding

Remarks

- Case temperature limited to $T_C=125^\circ\text{C}$ max.
- Product reliability results are valid for $T_J=150^\circ\text{C}$
- Dynamic values apply to the following combination of resistors:
 $R_{Gon,main} = 1,95 \Omega$
 $R_{Goff,main} = 1,95 \Omega$
 $R_{G,X} = 2,2 \Omega$
 $R_{E,X} = 0,5 \Omega$



GAL

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT						
t _{d(on)}	V _{CC} = 1200 V	T _j = 150 °C		380		ns
t _r	I _C = 300 A	T _j = 150 °C		50		ns
E _{on}	V _{GE} = +15/-15 V	T _j = 150 °C		140		mJ
t _{d(off)}	R _{G on} = 3.3 Ω	T _j = 150 °C		840		ns
t _f	R _{G off} = 3.3 Ω	T _j = 150 °C		160		ns
E _{off}	di/dt _{on} = 6600 A/μs du/dt = 1600 A/μs du/dt = 4400 V/μs L _s = 30 nH	T _j = 150 °C		122		mJ
t _{d(on)}	V _{CC} = 900 V	T _j = 150 °C		410		ns
t _r	I _C = 300 A	T _j = 150 °C		90		ns
E _{on}	V _{GE} = +15/-15 V	T _j = 150 °C		73		mJ
t _{d(off)}	R _{G on} = 3.3 Ω	T _j = 150 °C		780		ns
t _f	R _{G off} = 3.3 Ω	T _j = 150 °C		170		ns
E _{off}	di/dt _{on} = 3400 A/μs du/dt = 1400 A/μs du/dt = 4400 V/μs L _s = 80 nH	T _j = 150 °C		100		mJ
R _{th(j-c)}	per IGBT				0.083	K/W

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Inverse diode						
V _F = V _{EC}	I _F = 300 A	T _j = 25 °C		1.98	2.37	V
	V _{GE} = 0 V chipelevel	T _j = 150 °C		2.11	2.52	V
V _{F0}	chipelevel	T _j = 25 °C	1.16	1.32	1.56	V
		T _j = 150 °C		1.08	1.22	V
r _F	chipelevel	T _j = 25 °C	1.7	2.2	2.7	mΩ
		T _j = 150 °C		3.4	4.3	mΩ
I _{RRM}	I _F = 300 A	T _j = 150 °C		310		A
Q _{rr}	di/dt _{off} = 5600 A/μs	T _j = 150 °C		103		μC
E _{rr}	V _{GE} = -15 V V _R = 1200 V	T _j = 150 °C		70		mJ
I _{RRM}	I _F = 300 A	T _j = 150 °C		300		A
Q _{rr}	di/dt _{off} = 3400 A/μs	T _j = 150 °C		100		μC
E _{rr}	V _{GE} = -15 V V _R = 900 V	T _j = 150 °C		61		mJ
R _{th(j-c)}	per diode				0.184	K/W
Freewheeling diode						
V _F = V _{EC}	I _F = 300 A	T _j = 25 °C		1.98	2.37	V
	V _{GE} = 0 V chipelevel	T _j = 150 °C		2.11	2.52	V
V _{F0}	chipelevel	T _j = 25 °C	1.16	1.32	1.56	V
		T _j = 150 °C		1.08	1.22	V
r _F	chipelevel	T _j = 25 °C	1.7	2.2	2.7	mΩ
		T _j = 150 °C		3.4	4.3	mΩ
I _{RRM}	I _F = 300 A	T _j = 150 °C		310		A
Q _{rr}	di/dt _{off} = 5600 A/μs	T _j = 150 °C		103		μC
E _{rr}	V _{GE} = -15 V V _R = 1200 V	T _j = 150 °C		70		mJ
I _{RRM}	I _F = 300 A	T _j = 150 °C		300		A
Q _{rr}	di/dt _{off} = 3400 A/μs	T _j = 150 °C		100		μC
E _{rr}	V _{GE} = -15 V V _R = 900 V	T _j = 150 °C		61		mJ
R _{th(j-c)}	per diode				0.184	K/W

SEMiX302GAL17E4s



SEMiX302GAL17E4s

Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability
- UL recognized, file no. E63532


Typical Applications*

- AC inverter drives
- UPS
- Electronic Welding

Remarks

- Case temperature limited to $T_C=125^{\circ}\text{C}$ max.
- Product reliability results are valid for $T_J=150^{\circ}\text{C}$
- Dynamic values apply to the following combination of resistors:
 $R_{Gon,main} = 1,95\ \Omega$
 $R_{Goff,main} = 1,95\ \Omega$
 $R_{G,X} = 2,2\ \Omega$
 $R_{E,X} = 0,5\ \Omega$

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Module						
L _{CE}			18			nH
R _{CC'+EE'}	res. terminal-chip	T _C = 25 °C	0.7			mΩ
		T _C = 125 °C	1			mΩ
R _{th(c-s)}	per module		0.045			K/W
M _s	to heat sink (M5)		3		5	Nm
M _t		to terminals (M6)	2.5		5	Nm
						Nm
w					250	g
Temperature Sensor						
R ₁₀₀	T _C =100°C (R ₂₅ =5 kΩ)		493 ± 5%			Ω
B _{100/125}	R _(T) =R ₁₀₀ exp[B _{100/125} (1/T-1/T ₁₀₀)]; T[K];		3550 ±2%			K






Fig. 1: Typ. output characteristic, inclusive $R_{CC'} + E_{E'}$




Fig. 2: Rated current vs. temperature $I_C = f(T_C)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic




Fig. 6: Typ. gate charge characteristic




Fig. 7: Typ. switching times vs. I_C




Fig. 8: Typ. switching times vs. gate resistor R_G




Fig. 9: Typ. transient thermal impedance




Fig. 10: Typ. CAL diode forward charact., incl. $R_{CC'}+EE'$




Fig. 11: Typ. CAL diode peak reverse recovery current





Fig. 12: Typ. CAL diode recovery charge



© by SEMIKRON