

January 2024

## Danfoss Position on California Proposition 65

Danfoss supports the objectives of California Proposition 65 (Prop 65), officially known as the Safe Drinking Water and Toxic Enforcement Act of 1986, to protect the public health and the environment against exposure to hazardous substances.

Prop 65 defines warning responsibilities for companies that manufacture, produce, import, supply or distribute products that may expose a California resident to a chemical known to the State of California to cause cancer, birth defects or other reproductive harm. More information may be found here <https://oehha.ca.gov/proposition-65>.

To comply with Prop 65 warning requirements and support our customers in their own Prop 65 compliance efforts, Danfoss is providing annual notification to customers that receive products within the scope of Prop 65. All notified customers are required to confirm receipt of these notices.

Additionally, Danfoss applies a Prop 65 label on all individually boxed products that are within the scope of Prop 65. Danfoss does not label products that are traditionally sold in an industrial pack for OEM use. Here we will simply notify the customer.

Finally, Danfoss displays a Prop 65 label, on specific product webpages and catalogs.

- Climate Solutions and Drives customers may view their products in the Danfoss Product Store at <https://store.danfoss.com>.
- Power Solutions customers may view their products at <https://powersource.danfoss.com/>.

For more information, please contact your sales representative.

All Danfoss manufacturing facilities are required to be ISO 9001 certified and IATF 16949 compliant as well as ISO 14001 certified. Compliance with statutory and regulatory national and international environmental legislation is part of third-party certification procedures.

You are also invited to read more at:

<https://www.danfoss.com/en/about-danfoss/company/sustainability/product-compliance/>

### Danfoss A/S

Senior Director  
Head of Group Regulatory

Povl Schroder