

SEMiX151GD126HDs



SEMiX® 13

Trench IGBT Modules

SEMiX151GD126HDs

Features


- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability
- UL recognised file no. E63532

Typical Applications*

- AC inverter drives
- UPS
- Electronic Welding

Remarks

- Case temperatur limited to $T_C=125^\circ\text{C}$ max.
- Not for new design



GD

Absolute Maximum Ratings				
Symbol	Conditions		Values	Unit
IGBT				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 150 °C	T _c = 25 °C	168	A
		T _c = 80 °C	119	A
I _{Cnom}			100	A
I _{CRM}	I _{CRM} = 2xI _{Cnom}		200	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 600 V V _{GE} ≤ 20 V V _{CES} ≤ 1200 V	T _j = 125 °C	10	µs
T _j			-40 ... 150	°C
Inverse diode				
I _F	T _j = 150 °C	T _c = 25 °C	152	A
		T _c = 80 °C	105	A
I _{Fnom}			100	A
I _{FRM}	I _{FRM} = 2xI _{Fnom}		200	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 25 °C		700	A
T _j			-40 ... 150	°C
Module				
I _{t(RMS)}	T _{terminal} = 80 °C		600	A
T _{stg}			-40 ... 125	°C
V _{isol}	AC sinus 50Hz, t = 1 min		4000	V

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT						
V _{CE(sat)}	I _C = 100 A	T _j = 25 °C		1.7	2.10	V
	V _{GE} = 15 V chipelevel	T _j = 125 °C		2.0	2.45	V
V _{CE0}	chipelevel	T _j = 25 °C		1	1.2	V
		T _j = 125 °C		0.9	1.1	V
r _{CE}	V _{GE} = 15 V chipelevel	T _j = 25 °C		7.0	9.0	mΩ
		T _j = 125 °C		11.0	13.5	mΩ
V _{GE(th)}	V _{GE} =V _{CE} , I _C = 4 mA		5	5.8	6.5	V
I _{CES}	V _{GE} = 0 V	T _j = 25 °C			1	mA
	V _{CE} = 1200 V	T _j = 125 °C				mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		7.2		nF
C _{oes}		f = 1 MHz		0.38		nF
C _{res}		f = 1 MHz		0.33		nF
Q _G	V _{GE} = - 8 V...+ 15 V			800		nC
R _{Gint}	T _j = 25 °C			7.50		Ω
t _{d(on)}	V _{CC} = 600 V	T _j = 125 °C		290		ns
t _r	I _C = 100 A		T _j = 125 °C		50	
E _{on}	V _{GE} = ±15 V	T _j = 125 °C		12		mJ
t _{d(off)}	R _{G on} = 1.7 Ω		T _j = 125 °C		605	
t _f	R _{G off} = 1.7 Ω	T _j = 125 °C		110		ns
E _{off}		T _j = 125 °C		14		mJ
R _{th(j-c)}	per IGBT				0.21	K/W

SEMiX151GD126HDs



SEMiX® 13

Trench IGBT Modules

SEMiX151GD126HDs

Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability
- UL recognised file no. E63532


Typical Applications*

- AC inverter drives
- UPS
- Electronic Welding

Remarks

- Case temperatur limited to $T_C=125^\circ\text{C}$ max.
- Not for new design

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Inverse diode						
V _F = V _{EC}	I _F = 100 A	T _j = 25 °C		1.6	1.80	V
	V _{GE} = 0 V chiplevel	T _j = 125 °C		1.6	1.8	V
V _{F0}	chiplevel	T _j = 25 °C	0.9	1	1.1	V
		T _j = 125 °C	0.7	0.8	0.9	V
r _F	chiplevel	T _j = 25 °C	5.0	6.0	7.0	mΩ
		T _j = 125 °C	7.0	8.0	9.0	mΩ
I _{RRM}	I _F = 100 A	T _j = 125 °C		125		A
Q _{rr}	di/dt _{off} = 2900 A/μs	T _j = 125 °C		26		μC
E _{rr}	V _{GE} = -15 V	T _j = 125 °C		11.5		mJ
	V _{CC} = 600 V					
R _{th(j-c)}	per diode				0.36	K/W
Module						
L _{CE}				20		nH
R _{CC'+EE'}	res., terminal-chip	T _C = 25 °C		0.7		mΩ
		T _C = 125 °C		1		mΩ
R _{th(c-s)}	per module			0.04		K/W
M _s	to heat sink (M5)		3		5	Nm
M _t		to terminals (M6)	2.5		5	Nm
						Nm
w					350	g
Temperature Sensor						
R ₁₀₀	T _C =100°C (R ₂₅ =5 kΩ)			493 ± 5%		Ω
B _{100/125}	R(T)=R ₁₀₀ exp[B _{100/125} (1/T-1/T ₁₀₀)]; T[K];			3550 ±2%		K



GD




Fig. 1: Typ. output characteristic, inclusive $R_{CC}'+EE'$




Fig. 2: Rated current vs. temperature $I_C = f(T_C)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic




Fig. 6: Typ. gate charge characteristic




Fig. 7: Typ. switching times vs. I_C




Fig. 8: Typ. switching times vs. gate resistor R_G




Fig. 9: Typ. transient thermal impedance




Fig. 10: Typ. CAL diode forward charact., incl. $R_{CC'} + EE'$




Fig. 11: Typ. CAL diode peak reverse recovery current




Fig. 12: Typ. CAL diode recovery charge

