

# SEMiX202GB066HDs



SEMiX® 2s

## Trench IGBT Modules

### SEMiX202GB066HDs

#### Features


- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$  with positive temperature coefficient
- UL recognised file no. E63532

#### Typical Applications\*

- Matrix Converter
- Resonant Inverter
- Current Source Inverter

#### Remarks

- Case temperature limited to  $T_C=125^{\circ}\text{C}$  max.
- Product reliability results are valid for  $T_J=150^{\circ}\text{C}$
- For short circuit: Soft  $R_{Goff}$  recommended
- Take care of over-voltage caused by stray inductance



GB

| Absolute Maximum Ratings |                                                                               |                         |             |      |
|--------------------------|-------------------------------------------------------------------------------|-------------------------|-------------|------|
| Symbol                   | Conditions                                                                    |                         | Values      | Unit |
| IGBT                     |                                                                               |                         |             |      |
| V <sub>CES</sub>         | T <sub>j</sub> = 25 °C                                                        |                         | 600         | V    |
| I <sub>C</sub>           | T <sub>j</sub> = 175 °C                                                       | T <sub>c</sub> = 25 °C  | 274         | A    |
|                          |                                                                               | T <sub>c</sub> = 80 °C  | 207         | A    |
| I <sub>Cnom</sub>        |                                                                               |                         | 200         | A    |
| I <sub>CRM</sub>         | I <sub>CRM</sub> = 2xI <sub>Cnom</sub>                                        |                         | 400         | A    |
| V <sub>GES</sub>         |                                                                               |                         | -20 ... 20  | V    |
| t <sub>psc</sub>         | V <sub>CC</sub> = 360 V<br>V <sub>GE</sub> ≤ 15 V<br>V <sub>CES</sub> ≤ 600 V | T <sub>j</sub> = 150 °C | 6           | μs   |
| T <sub>j</sub>           |                                                                               |                         | -40 ... 175 | °C   |
| Inverse diode            |                                                                               |                         |             |      |
| I <sub>F</sub>           | T <sub>j</sub> = 175 °C                                                       | T <sub>c</sub> = 25 °C  | 291         | A    |
|                          |                                                                               | T <sub>c</sub> = 80 °C  | 214         | A    |
| I <sub>Fnom</sub>        |                                                                               |                         | 200         | A    |
| I <sub>FRM</sub>         | I <sub>FRM</sub> = 2xI <sub>Fnom</sub>                                        |                         | 400         | A    |
| I <sub>FSM</sub>         | t <sub>p</sub> = 10 ms, sin 180°, T <sub>j</sub> = 25 °C                      |                         | 1000        | A    |
| T <sub>j</sub>           |                                                                               |                         | -40 ... 175 | °C   |
| Module                   |                                                                               |                         |             |      |
| I <sub>t(RMS)</sub>      | T <sub>terminal</sub> = 80 °C                                                 |                         | 600         | A    |
| T <sub>stg</sub>         |                                                                               |                         | -40 ... 125 | °C   |
| V <sub>isol</sub>        | AC sinus 50Hz, t = 1 min                                                      |                         | 4000        | V    |

| Characteristics      |                                                            |                         |      |      |      |      |
|----------------------|------------------------------------------------------------|-------------------------|------|------|------|------|
| Symbol               | Conditions                                                 |                         | min. | typ. | max. | Unit |
| IGBT                 |                                                            |                         |      |      |      |      |
| V <sub>CE(sat)</sub> | I <sub>C</sub> = 200 A                                     | T <sub>j</sub> = 25 °C  |      | 1.45 | 1.85 | V    |
|                      | V <sub>GE</sub> = 15 V<br>chipelevel                       | T <sub>j</sub> = 150 °C |      | 1.7  | 2.1  | V    |
| V <sub>CE0</sub>     |                                                            | T <sub>j</sub> = 25 °C  |      | 0.9  | 1    | V    |
|                      |                                                            | T <sub>j</sub> = 150 °C |      | 0.85 | 0.9  | V    |
| r <sub>CE</sub>      | V <sub>GE</sub> = 15 V                                     | T <sub>j</sub> = 25 °C  |      | 2.8  | 4.3  | mΩ   |
|                      |                                                            | T <sub>j</sub> = 150 °C |      | 4.3  | 6.0  | mΩ   |
| V <sub>GE(th)</sub>  | V <sub>GE</sub> =V <sub>CE</sub> , I <sub>C</sub> = 3.2 mA |                         | 5    | 5.8  | 6.5  | V    |
| I <sub>CES</sub>     | V <sub>GE</sub> = 0 V                                      | T <sub>j</sub> = 25 °C  |      | 0.15 | 0.45 | mA   |
|                      | V <sub>CE</sub> = 600 V                                    | T <sub>j</sub> = 150 °C |      |      |      | mA   |
| C <sub>ies</sub>     | V <sub>CE</sub> = 25 V<br>V <sub>GE</sub> = 0 V            | f = 1 MHz               |      | 12.3 |      | nF   |
| C <sub>oes</sub>     |                                                            | f = 1 MHz               |      | 0.77 |      | nF   |
| C <sub>res</sub>     |                                                            | f = 1 MHz               |      | 0.37 |      | nF   |
| Q <sub>G</sub>       | V <sub>GE</sub> = - 8 V...+ 15 V                           |                         |      | 1600 |      | nC   |
| R <sub>Gint</sub>    | T <sub>j</sub> = 25 °C                                     |                         |      | 1.00 |      | Ω    |
| t <sub>d(on)</sub>   | V <sub>CC</sub> = 300 V                                    | T <sub>j</sub> = 150 °C |      | 65   |      | ns   |
| t <sub>r</sub>       | I <sub>C</sub> = 200 A                                     | T <sub>j</sub> = 150 °C |      | 80   |      | ns   |
| E <sub>on</sub>      | V <sub>GE</sub> = ±15 V                                    | T <sub>j</sub> = 150 °C |      | 6    |      | mJ   |
| t <sub>d(off)</sub>  | R <sub>G on</sub> = 4.2 Ω                                  | T <sub>j</sub> = 150 °C |      | 545  |      | ns   |
| t <sub>f</sub>       | R <sub>G off</sub> = 4.2 Ω                                 | T <sub>j</sub> = 150 °C |      | 95   |      | ns   |
| E <sub>off</sub>     |                                                            | T <sub>j</sub> = 150 °C |      | 8    |      | mJ   |
| R <sub>th(j-c)</sub> | per IGBT                                                   |                         |      |      | 0.21 | K/W  |



**SEMiX® 2s**

## Trench IGBT Modules

### SEMiX202GB066HDs

#### Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$  with positive temperature coefficient
- UL recognised file no. E63532

#### Typical Applications\*

- Matrix Converter
- Resonant Inverter
- Current Source Inverter

#### Remarks

- Case temperature limited to  $T_C=125^\circ\text{C}$  max.
- Product reliability results are valid for  $T_J=150^\circ\text{C}$
- For short circuit: Soft  $R_{Goff}$  recommended
- Take care of over-voltage caused by stray inductance

| Characteristics                  |                                                                                  |                         |      |             |      |      |
|----------------------------------|----------------------------------------------------------------------------------|-------------------------|------|-------------|------|------|
| Symbol                           | Conditions                                                                       |                         | min. | typ.        | max. | Unit |
| Inverse diode                    |                                                                                  |                         |      |             |      |      |
| V <sub>F</sub> = V <sub>EC</sub> | I <sub>F</sub> = 200 A                                                           | T <sub>j</sub> = 25 °C  |      | 1.4         | 1.60 | V    |
|                                  | V <sub>GE</sub> = 0 V<br>chip                                                    | T <sub>j</sub> = 150 °C |      | 1.4         | 1.6  | V    |
| V <sub>F0</sub>                  |                                                                                  | T <sub>j</sub> = 25 °C  | 0.9  | 1           | 1.1  | V    |
|                                  |                                                                                  | T <sub>j</sub> = 150 °C | 0.75 | 0.85        | 0.95 | V    |
| r <sub>F</sub>                   |                                                                                  | T <sub>j</sub> = 25 °C  | 1.5  | 2.0         | 2.5  | mΩ   |
|                                  |                                                                                  | T <sub>j</sub> = 150 °C | 2.3  | 2.8         | 3.3  | mΩ   |
| I <sub>RRM</sub>                 | I <sub>F</sub> = 200 A                                                           | T <sub>j</sub> = 150 °C |      | 205         |      | A    |
| Q <sub>rr</sub>                  | di/dt <sub>off</sub> = 3900 A/μs                                                 | T <sub>j</sub> = 150 °C |      | 28          |      | μC   |
| E <sub>rr</sub>                  | V <sub>GE</sub> = -8 V                                                           | T <sub>j</sub> = 150 °C |      | 6.5         |      | mJ   |
|                                  | V <sub>CC</sub> = 300 V                                                          |                         |      |             |      |      |
| R <sub>th(j-c)</sub>             | per diode                                                                        |                         |      |             | 0.27 | K/W  |
| Module                           |                                                                                  |                         |      |             |      |      |
| L <sub>CE</sub>                  |                                                                                  |                         |      | 18          |      | nH   |
| R <sub>CC'+EE'</sub>             | res., terminal-chip                                                              | T <sub>C</sub> = 25 °C  |      | 0.7         |      | mΩ   |
|                                  |                                                                                  | T <sub>C</sub> = 125 °C |      | 1           |      | mΩ   |
| R <sub>th(c-s)</sub>             | per module                                                                       |                         |      | 0.045       |      | K/W  |
| M <sub>s</sub>                   | to heat sink (M5)                                                                |                         | 3    |             | 5    | Nm   |
| M <sub>t</sub>                   |                                                                                  | to terminals (M6)       | 2.5  |             | 5    | Nm   |
|                                  |                                                                                  |                         |      |             |      | Nm   |
| w                                |                                                                                  |                         |      |             | 250  | g    |
| Temperatur Sensor                |                                                                                  |                         |      |             |      |      |
| R <sub>100</sub>                 | T <sub>c</sub> =100°C (R <sub>25</sub> =5 kΩ)                                    |                         |      | 493 ± 5%    |      | Ω    |
| B <sub>100/125</sub>             | R(T)=R <sub>100</sub> exp[B <sub>100/125</sub> (1/T-1/T <sub>100</sub> )]; T[K]; |                         |      | 3550<br>±2% |      | K    |



**GB**




Fig. 1: Typ. output characteristic, inclusive  $R_{CC} + EE'$




Fig. 2: Rated current vs. temperature  $I_C = f(T_C)$




Fig. 3: Typ. turn-on /-off energy =  $f(I_C)$




Fig. 4: Typ. turn-on /-off energy =  $f(R_G)$




Fig. 5: Typ. transfer characteristic











Fig. 6: Typ. gate charge characteristic




# SEMiX202GB066HDs

Case: SEMiX 2s


guide pin left  
F-F (1 : 1)




screw duct (4x)  
spring duct (12x):  
G-G (1 : 1)



marking of terminals



screw duct  
top view (4x):  
J (2 : 1)



\*guide pin left with

|                    |   |   |   |
|--------------------|---|---|---|
| $\varnothing$ 0,25 | A | B | C |
| $\varnothing$ 0,5  | A | D | C |

\*\*screw ducts / spring ducts / guide pin right with


|                    |   |   |   |
|--------------------|---|---|---|
| $\varnothing$ 0,25 | A | B | C |
| $\varnothing$ 0,5  | A | D | C |

Rules for the contact PCB:


- holes guidepins =  $\varnothing 4 \pm 0,1$  / position tolerance  $\pm 0,1$
- holes for screws =  $\varnothing 3,3 \pm 0,1$  / position tolerance  $\pm 0,1$
- spring contact pad =  $\varnothing 3,6 \pm 0,1$  / position tolerance  $\pm 0,1$

general tolerance:  
ISO 2768-m  
ISO 8015

All measures in Z-direction  
valid when mounted to heat sink



SEMiX 2s



spring configuration

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX

\* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our staff.