

SEMiX453GB17E4s



SEMiX® 3s

SEMiX453GB17E4s

Features


- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability
- UL recognized, file no. E63532

Typical Applications*

- AC inverter drives
- UPS
- Electronic Welding

Remarks

- Case temperature limited to $T_C=125^\circ\text{C}$ max.
- Product reliability results are valid for $T_J=150^\circ\text{C}$
- Dynamic values apply to the following combination of resistors:
 $R_{Gon,main} = 2,4 \Omega$
 $R_{Goff,main} = 2,4 \Omega$
 $R_{G,X} = 2,2 \Omega$
 $R_{E,X} = 0,5 \Omega$



GB

Absolute Maximum Ratings				
Symbol	Conditions		Values	Unit
IGBT				
V _{CES}	T _j = 25 °C		1700	V
I _c	T _j = 175 °C	T _c = 25 °C	762	A
		T _c = 80 °C	579	A
I _{Cnom}			450	A
I _{CRM}	I _{CRM} = 3xI _{Cnom}		1350	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 1000 V V _{GE} ≤ 15 V V _{CES} ≤ 1700 V	T _j = 150 °C	10	μs
T _j			-40 ... 175	°C
Inverse diode				
V _{RRM}	T _j = 25 °C		1700	V
I _F	T _j = 175 °C	T _c = 25 °C	482	A
		T _c = 80 °C	354	A
I _{Fnom}			450	A
I _{FRM}	I _{FRM} = 2xI _{Fnom}		900	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 25 °C		2565	A
T _j			-40 ... 175	°C
Module				
I _{t(RMS)}			600	A
T _{stg}			-40 ... 125	°C
V _{isol}	AC sinus 50Hz, t = 1 min		4000	V

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT						
V _{CE(sat)}	I _C = 450 A	T _J = 25 °C		1.90	2.20	V
	V _{GE} = 15 V chiplevel	T _J = 150 °C		2.26	2.45	V
V _{CE0}	chiplevel	T _J = 25 °C		1.1	1.2	V
		T _J = 150 °C		1	1.1	V
r _{CE}	V _{GE} = 15 V chiplevel	T _J = 25 °C		1.8	2.2	mΩ
		T _J = 150 °C		2.8	3	mΩ
V _{GE(th)}	V _{GE} =V _{CE} , I _C = 18 mA		5.2	5.8	6.4	V
I _{CES}	V _{GE} = 0 V	T _J = 25 °C			5	mA
	V _{CE} = 1700 V					mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		36		nF
C _{oes}		f = 1 MHz		1.50		nF
C _{res}		f = 1 MHz		1.14		nF
Q _G	V _{GE} = - 8 V...+ 15 V			3600		nC
R _{Gint}	T _J = 25 °C			1.67		Ω
t _{d(on)}	V _{CC} = 1200 V	T _J = 150 °C		455		ns
t _r	I _C = 450 A			65		ns
E _{on}	V _{GE} = +15/-15 V	T _J = 150 °C		250		mJ
t _{d(off)}	R _{G on} = 3.3 Ω	T _J = 150 °C		960		ns
t _f	R _{G off} = 3.3 Ω	T _J = 150 °C		170		ns
E _{off}	di/dt _{on} = 7000 A/μs	T _J = 150 °C		190		mJ
	di/dt _{off} = 2220 A/μs					
	du/dt = 5160 V/μs L _s = 30 nH					



SEMiX® 3s

SEMiX453GB17E4s

Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability
- UL recognized, file no. E63532

Typical Applications*


- AC inverter drives
- UPS
- Electronic Welding

Remarks

- Case temperature limited to $T_C=125^\circ\text{C}$ max.
- Product reliability results are valid for $T_J=150^\circ\text{C}$
- Dynamic values apply to the following combination of resistors:
 $R_{Gon,main} = 2,4 \Omega$
 $R_{Goff,main} = 2,4 \Omega$
 $R_{G,X} = 2,2 \Omega$
 $R_{E,X} = 0,5 \Omega$

Characteristics					
Symbol	Conditions		min.	typ.	max. Unit
$t_{d(on)}$	$V_{CC} = 900 \text{ V}$	$T_J = 150^\circ\text{C}$		490	ns
t_r	$I_C = 450 \text{ A}$	$T_J = 150^\circ\text{C}$		120	ns
E_{on}	$V_{GE} = +15/-15 \text{ V}$	$T_J = 150^\circ\text{C}$		118	mJ
$t_{d(off)}$	$R_{G on} = 3.3 \Omega$	$T_J = 150^\circ\text{C}$		900	ns
t_f	$R_{G off} = 3.3 \Omega$	$T_J = 150^\circ\text{C}$		200	ns
E_{off}	$di/dt_{on} = 4000 \text{ A}/\mu\text{s}$ $di/dt_{off} = 2050 \text{ A}/\mu\text{s}$ $du/dt = 4600 \text{ V}/\mu\text{s}$ $L_s = 80 \text{ nH}$	$T_J = 150^\circ\text{C}$		154	mJ
$R_{th(j-c)}$	per IGBT			0.056	K/W

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Inverse diode						
V _F = V _{EC}	I _F = 450 A	T _j = 25 °C		1.98	2.37	V
	V _{GE} = 0 V chiplevel	T _j = 150 °C		2.11	2.52	V
V _{F0}	chiplevel	T _j = 25 °C	1.16	1.32	1.56	V
		T _j = 150 °C		1.08	1.22	V
r _F	chiplevel	T _j = 25 °C	1.2	1.5	1.8	mΩ
		T _j = 150 °C		2.3	2.9	mΩ
I _{RRM}	I _F = 450 A	T _j = 150 °C		440		A
Q _{rr}	di/dt _{off} = 6240 A/μs	T _j = 150 °C		150		μC
E _{rr}	V _{GE} = -15 V V _R = 1200 V	T _j = 150 °C		100		mJ
I _{RRM}	I _F = 450 A	T _j = 150 °C		400		A
Q _{rr}	di/dt _{off} = 3700 A/μs	T _j = 150 °C		150		μC
E _{rr}	V _{GE} = -15 V V _R = 900 V	T _j = 150 °C		87		mJ
R _{th(j-c)}	per diode				0.125	K/W
Module						
L _{CE}				20		nH
R _{CC'+EE'}	res. terminal-chip	T _C = 25 °C		0.85		mΩ
		T _C = 150 °C		1.2		mΩ
R _{th(c-s)}	per module			0.04		K/W
M _s	to heat sink (M5)		3		5	Nm
M _t		to terminals (M6)	2.5		5	Nm
						Nm
w					300	g
Temperature Sensor						
R ₁₀₀	T _C =100°C (R ₂₅ =5 kΩ)			493 ± 5%		Ω
B _{100/125}	R _(T) =R ₁₀₀ exp[B _{100/125} (1/T-1/T ₁₀₀)]; T[K];			3550 ±2%		K



GB




Fig. 1: Typ. output characteristic, inclusive $R_{CC} + EE'$




Fig. 2: Rated current vs. temperature $I_C = f(T_C)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic




Fig. 6: Typ. gate charge characteristic




Fig. 7: Typ. switching times vs. I_C




Fig. 8: Typ. switching times vs. gate resistor R_G




Fig. 9: Typ. transient thermal impedance




Fig. 10: Typ. CAL diode forward charact., incl. $R_{CC'} + EE'$




Fig. 11: Typ. CAL diode peak reverse recovery current






Fig. 12: Typ. CAL diode recovery charge

Case: SEMiX 3s

guide pin left
F-F (1 : 1)





screw duct
(1x centre):
H-H (1 : 1)





$\square$ 0,3	connector 1-2 / 3-4
$\parallel$ 0,2	each connector A

general tolerance:
ISO 2768-m
ISO 8015

screw duct (6x)
spring duct (16x):
G-G (1 : 1)



All measures in Z-direction
valid when mounted to heat sink



*guide pin left with

$\oplus$ Ø 0,25	A	B	C
-----------------	---	---	---


**screw ducts / spring ducts / guide pin right with

$\oplus$ Ø 0,5	A	B	D
----------------	---	---	---

Rules for the contact PCB:

- holes guidepins = $\phi 4 \pm 0,1$ / position tolerance $\pm 0,1$
- holes for screws = $\phi 3,3 \pm 0,1$ / position tolerance $\pm 0,1$
- spring contact pad = $\phi 3,6 \pm 0,1$ / position tolerance $\pm 0,1$

SEMiX 3s



spring configuration

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our staff.