

SK15DGDL12T4ETE1



SEMITOP®E1

3-phase bridge rectifier +
brake chopper + 3-phase
bridge inverter

SK15DGDL12T4ETE1

Features*

- Low inductive design
- Press-Fit contact technology
- Rugged mounting due to integrated mounting clamps
- Heat transfer and insulation through direct copper bonded aluminium oxide ceramic (DBC)
- Trench4 IGBT technology
- Robust and soft switching CAL4F diode technology
- Integrated NTC temperature sensor
- UL recognized file no. E 63 532

Typical Applications

- Motor drives
- Air conditioning
- Auxiliary Inverters


Remarks

- IGBT1: inverter IGBT
- IGBT2: brake IGBT
- Diode1: rectifier diode
- Diode2: APD inverter
- Diode3: FWD brake

Absolute Maximum Ratings				
Symbol	Conditions		Values	Unit
IGBT 1				
V _{CES}	T _j = 25 °C		1200	V
I _C	λ _{paste} =0.8 W/(mK)	T _s = 25 °C	26	A
	T _j = 175 °C	T _s = 70 °C	21	A
I _C	λ _{paste} =2.5 W/(mK)	T _s = 25 °C	30	A
	T _j = 175 °C	T _s = 70 °C	25	A
I _{Cnom}			15	A
I _{CRM}	I _{CRM} = 3 x I _{Cnom}		45	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V V _{GE} ≤ 15 V V _{CES} ≤ 1200 V	T _j = 150 °C	10	μs
T _j			-40 ... 175	°C

Absolute Maximum Ratings				
Symbol	Conditions		Values	Unit
IGBT 2				
V _{CES}	T _j = 25 °C		1200	V
I _C	λ _{paste} =0.8 W/(mK)	T _s = 25 °C	26	A
	T _j = 175 °C	T _s = 70 °C	21	A
I _C	λ _{paste} =2.5 W/(mK)	T _s = 25 °C	30	A
	T _j = 175 °C	T _s = 70 °C	25	A
I _{Cnom}			15	A
I _{CRM}	I _{CRM} = 3 x I _{Cnom}		45	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V V _{GE} ≤ 15 V V _{CES} ≤ 1200 V	T _j = 150 °C	10	μs
T _j			-40 ... 175	°C

Absolute Maximum Ratings				
Symbol	Conditions		Values	Unit
Diode 1				
V _{RRM}	T _j = 25 °C		1600	V
I _F	λ _{paste} =0.8 W/(mK)	T _s = 25 °C	34	A
		T _j = 150 °C	25	A
I _F	λ _{paste} =2.5 W/(mK)	T _s = 25 °C	38	A
		T _j = 150 °C	29	A
I _{Fnom}			8	A
I _{FSM}	10 ms, sin 180°, T _j = 150 °C		200	A
i ² t	10 ms, sin 180°, T _j = 150 °C		200	A ² s
T _j			-40 ... 150	°C



DGDL-ET

SK15DGDL12T4ETE1



SEMITOP®E1

3-phase bridge rectifier +
brake chopper + 3-phase
bridge inverter

SK15DGDL12T4ETE1

Features*

- Low inductive design
- Press-Fit contact technology
- Rugged mounting due to integrated mounting clamps
- Heat transfer and insulation through direct copper bonded aluminium oxide ceramic (DBC)
- Trench4 IGBT technology
- Robust and soft switching CAL4F diode technology
- Integrated NTC temperature sensor
- UL recognized file no. E 63 532

Typical Applications

- Motor drives
- Air conditioning
- Auxiliary Inverters

Remarks

- IGBT1: inverter IGBT
- IGBT2: brake IGBT
- Diode1: rectifier diode
- Diode2: APD inverter
- Diode3: FWD brake

Absolute Maximum Ratings


Symbol	Conditions	Values	Unit
Diode 2			
V_{RRM}	$T_j = 25\text{ °C}$	1200	V
I_F	$\lambda_{paste}=0.8\text{ W/(mK)}$	$T_s = 25\text{ °C}$	A
	$T_j = 175\text{ °C}$	$T_s = 70\text{ °C}$	A
I_F	$\lambda_{paste}=2.5\text{ W/(mK)}$	$T_s = 25\text{ °C}$	A
	$T_j = 175\text{ °C}$	$T_s = 70\text{ °C}$	A
I_{Fnom}		15	A
I_{FRM}	$I_{FRM} = 2 \times I_{Fnom}$	30	A
I_{FSM}	10 ms	$T_j = 25\text{ °C}$	A
	sin 180°	$T_j = 150\text{ °C}$	A
T_j		-40 ... 175	°C

Absolute Maximum Ratings

Symbol	Conditions	Values	Unit
Diode 3			
V_{RRM}	$T_j = 25\text{ °C}$	1200	V
I_F	$\lambda_{paste}=0.8\text{ W/(mK)}$	$T_s = 25\text{ °C}$	A
	$T_j = 175\text{ °C}$	$T_s = 70\text{ °C}$	A
I_F	$\lambda_{paste}=2.5\text{ W/(mK)}$	$T_s = 25\text{ °C}$	A
	$T_j = 175\text{ °C}$	$T_s = 70\text{ °C}$	A
I_{Fnom}		8	A
I_{FRM}	$I_{FRM} = 3 \times I_{Fnom}$	24	A
I_{FSM}	10 ms	$T_j = 25\text{ °C}$	A
	sin 180°	$T_j = 150\text{ °C}$	A
T_j		-40 ... 175	°C

Absolute Maximum Ratings

Symbol	Conditions	Values	Unit
Module			
$I_{t(RMS)}$	$\Delta T_{terminal}$ at PCB joint = 30 K, per pin	30	A
T_{stg}		-40 ... 125	°C
V_{isol}	AC, sinusoidal, t = 1 min	2500	V



DGDL-ET

SK15DGD12T4ETE1



SEMITOP®E1

3-phase bridge rectifier +
brake chopper + 3-phase
bridge inverter

SK15DGD12T4ETE1

Features*


- Low inductive design
- Press-Fit contact technology
- Rugged mounting due to integrated mounting clamps
- Heat transfer and insulation through direct copper bonded aluminium oxide ceramic (DBC)
- Trench4 IGBT technology
- Robust and soft switching CAL4F diode technology
- Integrated NTC temperature sensor
- UL recognized file no. E 63 532

Typical Applications

- Motor drives
- Air conditioning
- Auxiliary Inverters

Remarks

- IGBT1: inverter IGBT
- IGBT2: brake IGBT
- Diode1: rectifier diode
- Diode2: APD inverter
- Diode3: FWD brake



DGDL-ET

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT 1						
V _{CE(sat)}	I _C = 15 A	T _j = 25 °C		1.85	2.10	V
	V _{GE} = 15 V chiplevel	T _j = 150 °C		2.25	2.45	V
V _{CE0}	chiplevel	T _j = 25 °C		0.80	0.90	V
		T _j = 150 °C		0.70	0.80	V
r _{CE}	V _{GE} = 15 V	T _j = 25 °C		70	80	mΩ
	chiplevel	T _j = 150 °C		103	110	mΩ
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 0.5 mA		5	5.8	6.5	V
I _{CES}	V _{GE} = 0 V, V _{CE} = 1200 V, T _j = 25 °C				1	mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		0.9		nF
C _{oes}		f = 1 MHz		0.08		nF
C _{res}		f = 1 MHz		0.055		nF
Q _G	V _{GE} = -15V ... +15V			111		nC
R _{Gint}	T _j = 25 °C			0		Ω
t _{d(on)}	V _{CC} = 600 V	T _j = 150 °C		12		ns
t _r	I _C = 15 A	T _j = 150 °C		17		ns
E _{on}	V _{GE} = +15/-15 V	T _j = 150 °C		1.09		mJ
t _{d(off)}	R _{G on} = 8.2 Ω	T _j = 150 °C		120		ns
	R _{G off} = 8.2 Ω	T _j = 150 °C		30		ns
t _f	di/dt _{on} = 893 A/μs	T _j = 150 °C				
E _{off}	di/dt _{off} = 170 A/μs	T _j = 150 °C		0.93		mJ
	dv/dt = 7114 V/μs					
R _{th(j-s)}	per IGBT, λ _{paste} =0.8 W/(mK)			1.53		K/W
R _{th(j-s)}	per IGBT, λ _{paste} =2.5 W/(mK)			1.17		K/W

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT 2						
V _{CE(sat)}	I _C = 15 A	T _j = 25 °C		1.85	2.10	V
	V _{GE} = 15 V chipllevel	T _j = 150 °C		2.25	2.45	V
V _{CE0}	chipllevel	T _j = 25 °C		0.80	0.90	V
		T _j = 150 °C		0.70	0.80	V
r _{CE}	V _{GE} = 15 V	T _j = 25 °C		70	80	mΩ
	chipllevel	T _j = 150 °C		103	110	mΩ
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 0.5 mA		5	5.8	6.5	V
I _{CES}	V _{GE} = 0 V, V _{CE} = 1200 V, T _j = 25 °C			-	1	mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		0.9		nF
C _{oes}		f = 1 MHz		0.08		nF
C _{res}		f = 1 MHz		0.055		nF
Q _G	V _{GE} = -15V ... +15V			111		nC
R _{Gint}	T _j = 25 °C			0		Ω
t _{d(on)}	V _{CC} = 600 V	T _j = 150 °C		24		ns
t _r	I _C = 15 A	T _j = 150 °C		32		ns
E _{on}	V _{GE} = +15/-15 V R _{G on} = 16 Ω	T _j = 150 °C		1.22		mJ
t _{d(off)}	R _{G off} = 16 Ω	T _j = 150 °C		164		ns
t _f	di/dt _{on} = 595 A/μs	T _j = 150 °C		44		ns
E _{off}	di/dt _{off} = 116 A/μs	T _j = 150 °C		0.98		mJ
R _{th(j-s)}	per IGBT, λ _{paste} =0.8 W/(mK)			1.53		K/W
R _{th(j-s)}	per IGBT, λ _{paste} =2.5 W/(mK)			1.17		K/W

SK15DGDL12T4ETE1



SEMITOP®E1

3-phase bridge rectifier +
brake chopper + 3-phase
bridge inverter

SK15DGDL12T4ETE1

Features*

- Low inductive design
- Press-Fit contact technology
- Rugged mounting due to integrated mounting clamps
- Heat transfer and insulation through direct copper bonded aluminium oxide ceramic (DBC)
- Trench4 IGBT technology
- Robust and soft switching CAL4F diode technology
- Integrated NTC temperature sensor
- UL recognized file no. E 63 532

Typical Applications

- Motor drives
- Air conditioning
- Auxiliary Inverters


Remarks

- IGBT1: inverter IGBT
- IGBT2: brake IGBT
- Diode1: rectifier diode
- Diode2: APD inverter
- Diode3: FWD brake

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Diode 1						
V _F	I _F = 8 A	T _j = 25 °C		1.00	1.21	V
	chiplevel	T _j = 125 °C		0.90	1.10	V
V _{F0}		T _j = 25 °C		0.88	0.98	V
	chiplevel	T _j = 125 °C		0.73	0.83	V
r _F		T _j = 25 °C		15	29	mΩ
	chiplevel	T _j = 125 °C		21	34	mΩ
I _R		T _j = 145 °C, V _{RRM}			2	mA
R _{th(j-s)}	per Diode, λ _{paste} =0.8 W/(mK)			1.89		K/W
R _{th(l-s)}	per Diode, λ _{paste} =2.5 W/(mK)			1.52		K/W

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Diode 2						
V _F	I _F = 15 A	T _j = 25 °C		2.38	2.71	V
	chiplevel	T _j = 150 °C		2.44	2.77	V
V _{F0}	chiplevel	T _j = 25 °C		1.30	1.50	V
		T _j = 150 °C		0.90	1.10	V
r _F	chiplevel	T _j = 25 °C		72	81	mΩ
		T _j = 150 °C		103	111	mΩ
I _{RRM}	I _F = 15 A	T _j = 150 °C		16		A
Q _{rr}	di/dt _{off} = 893 A/μs	T _j = 150 °C		2.3		μC
E _{rr}	V _{GE} = -15 V V _{CC} = 600 V	T _j = 150 °C		0.97		mJ
R _{th(j-s)}	per Diode, λ _{paste} =0.8 W/(mK)			2.13		K/W
R _{th(j-s)}	per Diode, λ _{paste} =2.5 W/(mK)			1.74		K/W

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Diode 3						
V _F	I _F = 8 A	T _j = 25 °C		2.33	2.65	V
	chiplevel	T _j = 150 °C		2.35	2.68	V
V _{F0}	chiplevel	T _j = 25 °C		1.30	1.50	V
		T _j = 150 °C		0.90	1.10	V
r _F	chiplevel	T _j = 25 °C		129	144	mΩ
		T _j = 150 °C		181	198	mΩ
I _{RRM}	I _F = 10 A	T _j = 150 °C		12		A
Q _{rr}	di/dt _{off} = 595 A/μs	T _j = 150 °C		1.1		μC
E _{rr}	V _{GE} = -15 V V _{CC} = 600 V	T _j = 150 °C		0.49		mJ
R _{th(j-s)}	per Diode, λ _{paste} =0.8 W/(mK)			2.64		K/W
R _{th(j-s)}	per Diode, λ _{paste} =2.5 W/(mK)			2.24		K/W



DGDLE-T

SK15DGD12T4ETE1



SEMITOP®E1

3-phase bridge rectifier +
brake chopper + 3-phase
bridge inverter

SK15DGD12T4ETE1

Features*

- Low inductive design
- Press-Fit contact technology
- Rugged mounting due to integrated mounting clamps
- Heat transfer and insulation through direct copper bonded aluminium oxide ceramic (DBC)
- Trench4 IGBT technology
- Robust and soft switching CAL4F diode technology
- Integrated NTC temperature sensor
- UL recognized file no. E 63 532

Typical Applications


- Motor drives
- Air conditioning
- Auxiliary Inverters

Remarks

- IGBT1: inverter IGBT
- IGBT2: brake IGBT
- Diode1: rectifier diode
- Diode2: APD inverter
- Diode3: FWD brake

Characteristics					
Symbol	Conditions	min.	typ.	max.	Unit
Module					
M_s	to heatsink	1.6		2.3	Nm
w	weight		25		g

Characteristics					
Symbol	Conditions	min.	typ.	max.	Unit
Temperature Sensor					
R_{100}	$T_r = 100\text{ °C}$		$493 \pm 5\%$		Ω
$B_{100/125}$	$R(T) = R_{100} \exp[B_{100/125}(1/T - 1/T_{100})]$; $T[K]$		$3550 \pm 2\%$		K



DGD1-ET




Fig. 1: Typ. IGBT output characteristic, incl. $R_{CC'+EE'}$




Fig. 2: IGBT rated current vs. temperature $I_C=f(T_s)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. IGBT transfer characteristic




Fig. 6: Typ. IGBT gate charge characteristic




Fig. 7: Typ. switching times = f (I_C)




Fig. 8: Typ. switching times = f (R_G)




Fig. 9: Typ. transient thermal impedance




Fig. 10: Typ. Diode2 forward characteristic, incl. R_{CC'+EE'}




Fig. 11: Typ. Diode2 peak reverse recovery current




Fig. 12: Typ. Diode2 reverse recovery charge




Fig. 13: IGBT Reverse Bias Safe Operating Area (RBSOA)








Fig. 14: Typ. Diode1 forward characteristic, incl. $R_{CC'+EE'}$



- Pin-Grid 3.2 mm
- Tolerance of PCB hole pattern ± 0.025
- Diameters of drill $\varnothing 1.15\text{mm}$
- Copper thickness in hole 25 - 50 μm
- Hole specification for contacts: refer to SEMITOP E1, E2 mounting instructions



SEMITOP®E1



DGDLE-T

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, chapter IX.

***IMPORTANT INFORMATION AND WARNINGS**

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.