

SK50DGDL12T4T



SEMITOP®4


3-phase bridge rectifier +
brake chopper + 3-phase
bridge inverter

SK 50 DGDL 12T4 T

Features

- One screw mounting module
- Fully compatible with SEMITOP®1,2,3
- Improved thermal performances by aluminium oxide substrate
- Trench4 IGBT technology
- CAL4 technology free-wheeling diode
- Integrated NTC temperature sensor






1) $V_{CE,sat}$, V_F = chip level value








DGDL - T

Absolute Maximum Ratings		Ts = 25 °C, unless otherwise specified	
Symbol	Conditions	Values	Units
IGBT - Inverter. For IGBT chopper maximum ratings, please refer to SK35DGDL12T4T			
V_{CES}		1200	V
I_C	$T_s = 25 (70) ^\circ C$	75 (60)	A
I_{CRM}	$I_{CRM} = 3 \times I_{Cnom}$, $t_p = 1 \text{ ms}$	150	A
V_{GES}		± 20	V
T_j		-40 ... +175	$^\circ C$
Diode - Inverter, Chopper			
I_F	$T_s = 25 (70) ^\circ C$	60 (45)	A
I_{FRM}	$I_{FRM} = 2 \times I_{Fnom}$, $t_p = 1 \text{ ms}$	150	A
T_j		-40 ... +150	$^\circ C$
Rectifier			
V_{RRM}		1600	V
I_F	$T_s = 70 ^\circ C$	61	A
I_{FSM} / I_{TSM}	$t_p = 10 \text{ ms}$, $\sin 180 ^\circ$, $T_j = 25 ^\circ C$	700	A
I_t^2	$t_p = 10 \text{ ms}$, $\sin 180 ^\circ$, $T_j = 25 ^\circ C$	2400	A ² s
T_j		-40 ... +175	$^\circ C$
T_{sol}	Terminals, 10 s	260	$^\circ C$
T_{stg}		-40 ... +125	$^\circ C$
V_{isol}	AC, 1 min. / 1 s	2500 / 3000	V


Characteristics		Ts = 25 °C, unless otherwise specified		
Symbol	Conditions	min.	typ.	max.
IGBT - Inverter. For IGBT chopper electrical characteristics, please refer to SK35DGDL12T4T				
V_{CEsat}	$I_C = 50 \text{ A}$, $T_j = 25 (150) ^\circ C$		1,85 (2,2)	2,05 (2,45)
$V_{GE(th)}$	$V_{GE} = V_{CE}$, $I_C = 1,7 \text{ mA}$	5	5,8	6,5
$V_{CE(TO)}$	$T_j = 25 ^\circ C (150) ^\circ C$		1,1 (1)	1,3 (1,2)
r_T	$T_j = 25 ^\circ C (150) ^\circ C$		15 (24)	
C_{ies}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1 \text{ MHz}$		2,77	
C_{oes}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1 \text{ MHz}$		0,2	
C_{res}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1 \text{ MHz}$		0,16	
$R_{th(j-s)}$	per IGBT		0,65	
$t_{d(on)}$	under following conditions		63	
t_r	$V_{CC} = 600 \text{ V}$, $V_{GE} = \pm 15 \text{ V}$		65	
$t_{d(off)}$	$I_C = 50 \text{ A}$, $T_j = 150 ^\circ C$		521	
t_f	$R_{Gon} = R_{Goff} = 32 \Omega$		80	
E_{on}	inductive load		8,3	
E_{off}			5	
Diode - Inverter, Chopper				
$V_F = V_{EC}$	$I_F = 50 \text{ A}$, $T_j = 25(150) ^\circ C$		2,22 (2,18)	2,54 (2,5)
$V_{(TO)}$	$T_j = 25 ^\circ C (150) ^\circ C$		1,3 (0,9)	1,5 (1,1)
r_T	$T_j = 25 ^\circ C (150) ^\circ C$		18,4 (25,6)	20,8 (28)
$R_{th(j-s)}$	per diode		0,97	
I_{RRM}	under following conditions		30	
Q_{rr}	$I_F = 50 \text{ A}$, $V_R = 300 \text{ V}$		7,2	
E_{rr}	$V_{GE} = 0 \text{ V}$, $T_j = 150 ^\circ C$		2,15	
	$di_F/dt = 920 \text{ A}/\mu s$			
Diode - Rectifier				
V_F	$I_F = 50 \text{ A}$, $T_j = 25(150) ^\circ C$		1,1	
$V_{(TO)}$	$T_j = 150 ^\circ C$		0,8	
r_T	$T_j = 150 ^\circ C$		6	
$R_{th(j-s)}$	per diode		0,9	
Temperatur sensor				
R_{ts}	5 %, $T_r = 25 (100) ^\circ C$		5000(493)	Ω
Mechanical data				
w			60	g
M_s	Mounting torque		2,6	Nm







Case T 75 (Suggested hole diameter for the solder pins in the circuit board: 2mm. Suggested hole diameter for the mounting pins in the circuit board: 3,6mm)



Case T 75 (pin without letter refers to row "a", unless otherwise specified)

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, chapter IX.

*IMPORTANT INFORMATION AND WARNINGS

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffungsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.