




SEMITOP® 2

Bridge Rectifier

SK 70 D

Preliminary Data

Features


- Compact design
- One screw mounting
- Heat transfer and insulation through direct copper bonded aluminium oxide ceramic (DCB)
- Up to 1600V reverse voltage
- High surge currents
- Glass passivated diodes chips
- UL recognized, file no. E 63 532

Typical Applications*

- Input rectifier for power supplies
- Rectifier

V_{RSM} V	V_{RRM}, V_{DRM} V	$I_D = 70$ A (full conduction) ($T_s = 80$ °C)
800	800	SK 70 D 08
1200	1200	SK 70 D 12
1600	1600	SK 70 D 16

Symbol	Conditions	Values	Units
I_D	$T_s = 80$ °C	70	A
I_{FSM}	$T_{vj} = 25$ °C; 10 ms $T_{vj} = 150$ °C; 10 ms	370 270	A A
i^2t	$T_{vj} = 25$ °C; 8,3...10 ms $T_{vj} = 150$ °C; 8,3...10 ms	685 365	A²s A²s
V_F $V_{(TO)}$ r_T I_{RD}	$T_{vj} = 25$ °C; $I_F = 25$ A $T_{vj} = 150$ °C $T_{vj} = 150$ °C $T_{vj} = 150$ °C; $V_{DD} = V_{DRM}$; $V_{RD} = V_{RRM}$	max. 1,25 max. 0,8 max. 13 max. 4	V V mΩ mA mA
$R_{th(f-s)}$	per diode per module	1,7 0,28	K/W K/W
T_{solder} T_{vj} T_{stg}	terminals, 10s	260 -40...+150 -40...+125	°C °C °C
V_{isol} M_s M_t m	a. c. 50 Hz; r.m.s.; 1 s / 1 min. mounting torque to heatsink approx. weight	3000 (2500) 2 19	V Nm g
Case	SEMITOP® 2	T 7	



D




Fig. 1 Power dissipation vs. Output current




Fig. 2 Surge overload current vs. time




Fig. 3 Forward characteristics of single diode






Fig. 4 Thermal transient impedance vs. time



* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.