


SKiiP 12HEB066V1



MiniSKiiP®1

1-phase half controlled
bridge rectifier + brake
chopper + 3-phase bridge
inverter


SKiiP 12HEB066V1

Features

- Trench IGBTs
- Robust and soft freewheeling diode in CAL technology
- Highly reliable spring contacts for electrical connection
- UL recognised file no. E63532

Remarks

- Case temperature limited to $T_C = 125^\circ\text{C}$ max.
- Product reliability results are valid for $T_j = 150^\circ\text{C}$
- SC data: $t_p \leq 6 \text{ s}$; $V_{GE} \leq 15 \text{ V}$; $T_j = 150^\circ\text{C}$; $V_{CC} = 360 \text{ V}$
- V_{CEsat} , V_F , V_T = chip level value














HEB



Absolute Maximum Ratings		$T_S = 25^\circ\text{C}$, unless otherwise specified	
Symbol	Conditions	Values	Units
IGBT - Inverter, Chopper			
V_{CES}		600	V
I_C	$T_S = 25 (70)^\circ\text{C}$, $T_j = 150^\circ\text{C}$	30 (21)	A
I_C	$T_S = 25 (70)^\circ\text{C}$, $T_j = 175^\circ\text{C}$	33 (25)	A
I_{CRM}	$t_p = 1 \text{ ms}$	40	A
V_{GES}		± 20	V
T_j		$-40 \dots +175$	$^\circ\text{C}$
Diode - Inverter, Chopper			
I_F	$T_S = 25 (70)^\circ\text{C}$, $T_j = 150^\circ\text{C}$	33 (22)	A
I_F	$T_S = 25 (70)^\circ\text{C}$, $T_j = 175^\circ\text{C}$	39 (29)	A
I_{FRM}	$t_p = 1 \text{ ms}$	40	A
T_j		$-40 \dots +175$	$^\circ\text{C}$
Diode / Thyristor - Rectifier			
V_{RRM}		800	V
I_F / I_T	$T_S = 70$	46 / 45	A
I_{FSM} / I_{TSM}	$t_p = 10 \text{ ms}$, $\sin 180^\circ$, $T_j = 25^\circ\text{C}$	370 / 340	A
i^2t	$t_p = 10 \text{ ms}$, $\sin 180^\circ$, $T_j = 25^\circ\text{C}$	575	A^2s
T_j	Diode	$-40 \dots +150$	$^\circ\text{C}$
T_j	Thyristor	$-40 \dots +125$	$^\circ\text{C}$
I_{TRMS}	per power terminal (20 A / spring)	20	A
T_{stg}	$T_{op} \leq T_{stg}$	$-40 \dots +125$	$^\circ\text{C}$
V_{isol}	AC, 1 min.	2500	V

Characteristics		$T_S = 25^\circ\text{C}$, unless otherwise specified			
Symbol	Conditions	min.	typ.	max.	Units
IGBT - Inverter, Chopper					
V_{CEsat}	$I_{Cnom} = 20 \text{ A}$, $T_j = 25 (150)^\circ\text{C}$	1,1	1,45 (1,65)	1,85 (2,05)	V
$V_{GE(th)}$	$V_{GE} = V_{CE}$, $I_C = 1 \text{ mA}$		5,8		V
$V_{CE(TO)}$	$T_j = 25 (150)^\circ\text{C}$		0,9 (0,85)	1 (0,9)	V
r_T	$T_j = 25 (150)^\circ\text{C}$		30 (42,5)	45 (60)	m Ω
C_{ies}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1 \text{ MHz}$		1,13		nF
C_{oes}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1 \text{ MHz}$		0,25		nF
C_{res}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 1 \text{ MHz}$		0,18		nF
$R_{CC+EE'}$	spring contact-chip $T_S = 25 (150)^\circ\text{C}$				m Ω
$R_{th(j-s)}$	per IGBT		1,6		K/W
$t_{d(on)}$	under following conditions		30		ns
t_r	$V_{CC} = 300 \text{ V}$, $V_{GE} = -8\text{V}/+15\text{V}$		25		ns
$t_{d(off)}$	$I_{Cnom} = 20 \text{ A}$, $T_j = 150^\circ\text{C}$		265		ns
t_f	$R_{Gon} = R_{Goff} = 27 \Omega$		50		ns
$E_{on} (E_{off})$	inductive load		0,8 (0,7)		mJ
Diode - Inverter, Chopper					
$V_F = V_{EC}$	$I_{Fnom} = 30 \text{ A}$, $T_j = 25 (150)^\circ\text{C}$		1,5 (1,5)	1,7 (1,7)	V
$V_{(TO)}$	$T_j = 25 (150)^\circ\text{C}$		1 (0,9)	1,1 (1)	V
r_T	$T_j = 25 (150)^\circ\text{C}$		16,7 (20)	20 (23,3)	m Ω
$R_{th(j-s)}$	per diode		2,1		K/W
I_{RRM}	under following conditions		25,1		A
Q_{rr}	$I_{Fnom} = 20 \text{ A}$, $V_R = 300 \text{ V}$		2,6		C
E_{rr}	$V_{GE} = 0 \text{ V}$, $T_j = 150^\circ\text{C}$		0,6		mJ
	$di_F/dt = 980 \text{ A/s}$				

Characteristics		$T_S = 25^\circ\text{C}$, unless otherwise specified			
Symbol	Conditions	min.	typ.	max.	Units
Diode - Rectifier					
V_F	$I_{Fnom} = 25\text{ A}$, $T_J = 25^\circ\text{C}$		1,1		V
$V_{(TO)}$	$T_J = 150^\circ\text{C}$		0,8		V
r_T	$T_J = 150^\circ\text{C}$		13		m Ω
$R_{th(j-s)}$	per diode		1,25		K/W
Thyristor - Rectifier					
V_T	$I_{Fnom} = 25\text{ A}$, $T_J = 25\text{ (125)}^\circ\text{C}$			(1,6)	V
$V_{T(TO)}$	$T_J = 125^\circ\text{C}$			1,1	V
r_T	$T_J = 125^\circ\text{C}$			20	m Ω
V_{GT}	$T_J = 25^\circ\text{C}$			2	V
I_{GT}	$T_J = 25^\circ\text{C}$			100	mA
I_H	$T_J = 25^\circ\text{C}$		80	150	mA
I_L	$T_J = 25^\circ\text{C}$		150	300	mA
$dv/dt_{(cr)}$	$T_J = 125^\circ\text{C}$	500			V/ s
$di/dt_{(cr)}$	$T_J = 125^\circ\text{C}$			100	A/ s
$R_{th(j-s)}$	per thyristor		1,25		K/W
Temperature Sensor					
R_{ts}	3 %, $T_r = 25\text{ (100)}^\circ\text{C}$		1000(1670)		Ω
Mechanical Data					
w			35		g
M_s	Mounting torque	2		2,5	Nm







This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.