


SKiP 29TMLI12F4V1



MiniSKiP® 2

3-Level TNPC IGBT-Module


SKiP 29TMLI12F4V1

Features*

- Fast Trench 4 IGBTs
- Trench IGBTs
- Robust and soft diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised: File no. E63532

Remarks*


- Case temperature limited to $T_C=125^{\circ}\text{C}$ max.; $T_C = T_S$ (for baseplateless modules)
- Product reliability results valid for $T_j \leq 150^{\circ}\text{C}$ (recommended $T_{jop} = -40 \dots +150^{\circ}\text{C}$)
- IGBT 1: outer IGBTs T1&T4
- IGBT 2: inner IGBTs T2&T3
- Diode 1: outer diodes D1&D4
- Diode 2: inner diodes D2&D3



TMLI

Absolute Maximum Ratings				
Symbol	Conditions		Values	Unit
IGBT1				
V _{CES}	T _j = 25 °C		1200	V
I _C	λ _{paste} =0.8 W/(mK)	T _s = 25 °C	144	A
	T _j = 175 °C	T _s = 70 °C	115	A
I _C	λ _{paste} =2.5 W/(mK)	T _s = 25 °C	173	A
	T _j = 175 °C	T _s = 70 °C	139	A
I _{Cnom}			150	A
I _{CRM}			450	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V, V _{GE} ≤ 15 V, T _j = 150 °C, V _{CES} ≤ 1200 V		6	µs
T _j			-40 ... 175	°C
IGBT2				
V _{CES}	T _j = 25 °C		650	V
I _C	λ _{paste} =0.8 W/(mK)	T _s = 25 °C	131	A
	T _j = 175 °C	T _s = 70 °C	104	A
I _C	λ _{paste} =2.5 W/(mK)	T _s = 25 °C	150	A
	T _j = 175 °C	T _s = 70 °C	120	A
I _{Cnom}			150	A
I _{CRM}			450	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 360 V, V _{GE} ≤ 15 V, T _j = 150 °C, V _{CES} ≤ 650 V		6	µs
T _j			-40 ... 175	°C
Diode1				
V _{RRM}	T _j = 25 °C		1200	V
I _F	λ _{paste} =0.8 W/(mK)	T _s = 25 °C	148	A
	T _j = 175 °C	T _s = 70 °C	117	A
I _F	λ _{paste} =2.5 W/(mK)	T _s = 25 °C	170	A
	T _j = 175 °C	T _s = 70 °C	136	A
I _{FRM}			450	A
I _{FSM}	10 ms, sin 180°, T _j = 25 °C		774	A
T _j			-40 ... 175	°C
Diode2				
V _{RRM}	T _j = 25 °C		650	V
I _F	λ _{paste} =0.8 W/(mK)	T _s = 25 °C	129	A
	T _j = 175 °C	T _s = 70 °C	99	A
I _F	λ _{paste} =2.5 W/(mK)	T _s = 25 °C	155	A
	T _j = 175 °C	T _s = 70 °C	121	A
I _{FRM}			300	A
I _{FSM}	10 ms, sin 180°, T _j = 25 °C		1200	A
T _j			-40 ... 175	°C
Module				
I _{t(RMS)}	20 A per spring		100	A
T _{stg}	module without TIM		-40 ... 125	°C
V _{isol}	AC sinus 50 Hz, t = 1 min		2500	V

SKiiP 29TMLI12F4V1



MiniSKiiP® 2

3-Level TNPC IGBT-Module


SKiiP 29TMLI12F4V1

Features*

- Fast Trench 4 IGBTs
- Trench IGBTs
- Robust and soft diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised: File no. E63532

Remarks*


- Case temperature limited to $T_C=125^\circ\text{C}$ max.; $T_C = T_S$ (for baseplateless modules)
- Product reliability results valid for $T_j \leq 150^\circ\text{C}$ (recommended $T_{jop} = -40 \dots +150^\circ\text{C}$)
- IGBT 1: outer IGBTs T1&T4
- IGBT 2: inner IGBTs T2&T3
- Diode 1: outer diodes D1&D4
- Diode 2: inner diodes D2&D3



TMLI

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT1						
V _{CE(sat)}	I _C = 150 A	T _j = 25 °C		2.05	2.42	V
	V _{GE} = 15 V chiplevel	T _j = 150 °C		2.59	2.96	V
V _{CE0}	chiplevel	T _j = 25 °C		1.10	1.28	V
		T _j = 150 °C		0.95	1.13	V
r _{CE}	V _{GE} = 15 V	T _j = 25 °C		6.3	7.6	mΩ
	chiplevel	T _j = 150 °C		11	12	mΩ
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 5.2 mA		5.2	5.8	6.4	V
I _{CES}	V _{GE} = 0 V, V _{CE} = 1200 V, T _j = 25 °C				1.5	mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		8.80		nF
C _{oes}		f = 1 MHz		0.58		nF
C _{res}		f = 1 MHz		0.47		nF
Q _G	V _{GE} = - 8 V...+ 15 V			850		nC
R _{Gint}	T _j = 25 °C			5.0		Ω
t _{d(on)}	V _{CE} = 300 V	T _j = 150 °C		155		ns
t _r	I _C = 150 A	T _j = 150 °C		54		ns
E _{on}	V _{GE} = +15/-15 V	T _j = 150 °C		5.2		mJ
t _{d(off)}	R _{G on} = 1.6 Ω	T _j = 150 °C		323		ns
t _f	R _{G off} = 1.6 Ω	T _j = 150 °C		66		ns
E _{off}	di/dt _{on} = 2550 A/μs di/dt _{off} = 1850 A/μs	T _j = 150 °C		6.1		mJ
R _{th(j-s)}	per IGBT, λ _{paste} =0.8 W/(mK)			0.35		K/W
R _{th(j-s)}	per IGBT, λ _{paste} =2.5 W/(mK)			0.26		K/W
IGBT2						
V _{CE(sat)}	I _C = 150 A	T _j = 25 °C		1.45	1.77	V
	V _{GE} = 15 V chiplevel	T _j = 150 °C		1.70	2.10	V
V _{CE0}	chiplevel	T _j = 25 °C		0.90	1.00	V
		T _j = 150 °C		0.82	0.90	V
r _{CE}	V _{GE} = 15 V	T _j = 25 °C		3.7	5.1	mΩ
	chiplevel	T _j = 150 °C		5.9	8.0	mΩ
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 2.4 mA		5.1	5.8	6.4	V
I _{CES}	V _{GE} = 0 V, V _{CE} = 650 V, T _j = 25 °C				1.5	mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		9.24		nF
C _{oes}		f = 1 MHz		0.60		nF
C _{res}		f = 1 MHz		0.27		nF
Q _G	V _{GE} = - 8 V...+ 15 V			1360		nC
R _{Gint}	T _j = 25 °C			2.0		Ω
t _{d(on)}	V _{CE} = 300 V	T _j = 150 °C		118		ns
t _r	I _C = 150 A	T _j = 150 °C		40		ns
E _{on}	V _{GE} = +15/-15 V	T _j = 150 °C		1.6		mJ
t _{d(off)}	R _{G on} = 1.6 Ω	T _j = 150 °C		276		ns
t _f	R _{G off} = 1.6 Ω	T _j = 150 °C		79		ns
E _{off}	di/dt _{on} = 3900 A/μs di/dt _{off} = 1650 A/μs	T _j = 150 °C		6.1		mJ
R _{th(j-s)}	per IGBT, λ _{paste} =0.8 W/(mK)			0.57		K/W
R _{th(j-s)}	per IGBT, λ _{paste} =2.5 W/(mK)			0.46		K/W

SKiiP 29TMLI12F4V1



MiniSKiiP® 2

3-Level TNPC IGBT-Module

SKiiP 29TMLI12F4V1


Features*

- Fast Trench 4 IGBTs
- Trench IGBTs
- Robust and soft diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised: File no. E63532

Remarks*

- Case temperature limited to $T_C=125^\circ\text{C}$ max.; $T_C = T_S$ (for baseplateless modules)
- Product reliability results valid for $T_j \leq 150^\circ\text{C}$ (recommended $T_{jop} = -40 \dots +150^\circ\text{C}$)
- IGBT 1: outer IGBTs T1&T4
- IGBT 2: inner IGBTs T2&T3
- Diode 1: outer diodes D1&D4
- Diode 2: inner diodes D2&D3

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Diode1						
V _F = V _{EC}	I _F = 150 A	T _j = 25 °C		2.17	2.49	V
	V _{GE} = 0 V chiplevel	T _j = 150 °C		2.11	2.42	V
V _{F0}	chiplevel	T _j = 25 °C		1.30	1.50	V
		T _j = 150 °C		0.90	1.10	V
r _F	chiplevel	T _j = 25 °C		5.8	6.6	mΩ
		T _j = 150 °C		8.1	8.8	mΩ
I _{RRM}	I _F = 150 A	T _j = 150 °C		191.3		A
Q _{rr}	di/dt _{off} = 3760 A/μs V _R = 300 V	T _j = 150 °C		26		μC
E _{rr}	V _{GE} = +15/-15 V	T _j = 150 °C		6.5		mJ
R _{th(j-s)}	per Diode, λ _{paste} =0.8 W/(mK)			0.45		K/W
R _{th(j-s)}	per Diode, λ _{paste} =2.5 W/(mK)			0.36		K/W
Diode2						
V _F = V _{EC}	I _F = 150 A	T _j = 25 °C		1.40	1.76	V
	V _{GE} = 0 V chiplevel	T _j = 150 °C		1.39	1.77	V
V _{F0}	chiplevel	T _j = 25 °C		1.04	1.24	V
		T _j = 150 °C		0.85	0.99	V
r _F	chiplevel	T _j = 25 °C		2.4	3.5	mΩ
		T _j = 150 °C		3.6	5.2	mΩ
I _{RRM}	I _F = 150 A	T _j = 150 °C		131.4		A
Q _{rr}	di/dt _{off} = 2640 A/μs V _R = 300 V	T _j = 150 °C		13.5		μC
E _{rr}	V _{GE} = +15/-15 V	T _j = 150 °C		2.4		mJ
R _{th(j-s)}	per Diode, λ _{paste} =0.8 W/(mK)			0.73		K/W
R _{th(j-s)}	per Diode, λ _{paste} =2.5 W/(mK)			0.56		K/W
Module						
L _{sCE1}				-		nH
L _{CE}				-		nH
R _{CC'+EE'}		T _s = 25 °C		-		mΩ
		T _s = 125 °C		-		mΩ
M _s	to heat sink		2		2.5	Nm
M _t				-		Nm
						Nm
w				55		g
Temperature Sensor						
R ₁₀₀	T _r =100°C (R ₂₅ =1000Ω)			1670 ± 3%		Ω
R _(T)	R _(T) =1000Ω[1+A(T-25°C)+B(T-25°C) ²] , A = 7.635*10 ⁻³ °C ⁻¹ , B = 1.731*10 ⁻⁵ °C ⁻²					



TMLI




Fig. 1: Typ. IGBT1 output characteristic, incl. $R_{CC'+EE'}$




Fig. 2: IGBT1 rated current vs. Temperature $I_C=f(T_s)$




Fig. 3: Typ. IGBT1 & Diode2 turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. IGBT1 & Diode2 turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. IGBT1 transfer characteristic




Fig. 6: Typ. IGBT1 gate charge characteristic




Fig. 7: Typ. IGBT1 switching times vs. I_C




Fig. 8: Typ. IGBT1 switching times vs. gate resistor R_G




Fig. 9: Typ. Transient thermal impedance of IGBT1 & Diode2




Fig. 10: Typ. Diode2 forward characteristic, incl. $R_{CC'}+EE'$




Fig. 11: Typ. Diode2 peak reverse recovery current




Fig. 12: Typ. Diode2 recovery charge




Fig. 13: Typ. IGBT2 output characteristic, incl. $R_{CC'+EE'}$




Fig. 14: IGBT2 Rated current vs. Temperature $I_C = f(T_s)$




Fig. 15: Typ. IGBT2 & Diode1 turn-on /-off energy = $f(I_C)$




Fig. 16: Typ. IGBT2 & Diode1 turn-on /-off energy = $f(R_G)$




Fig. 17: Typ. IGBT2 transfer characteristic




Fig. 18: Typ. IGBT2 gate charge characteristic




Fig. 19: Typ. IGBT2 switching times vs. I_C




Fig. 20: Typ. IGBT2 switching times vs. gate resistor R_G




Fig. 21: Transient thermal impedance of IGBT2 & Diode1




Fig. 22: Typ. Diode1 forward characteristic, incl. $R_{CC'+EE'}$




Fig. 23: Typ. Diode1 peak reverse recovery current






Fig. 24: Typ. Diode1 recovery charge

Pin out											
Pin	X	Y	Function	Pin	X	Y	Function	Pin	X	Y	Function
1	24,38	-21,80	C	23	8,38	5,80		45	-12,23	-5,80	
2	24,38	-18,60		24	8,38	12,20		46	-12,23	0,70	
3	24,38	-15,40		25	8,38	15,40		47	-12,23	3,90	E1
4	24,38	-12,20		26	8,38	18,60	N	48	-12,23	7,10	g1
5	24,38	-9,00	T+	27	8,38	21,80	N	49	-12,23	10,30	
6	24,38	-5,80		28	2,46	-21,80	DC-	50	-12,23	15,40	DC+
7	24,38	-2,60	T-	29	2,46	-18,60	g4	51	-12,23	18,60	DC+
8	24,38	12,20	g3	30	2,46	-15,40		52	-12,23	21,80	DC+
9	24,38	15,40	E3	31	2,46	-12,20		53	-24,38	-21,80	DC-
10	24,38	18,60	N	32	2,46	-9,00	g2	54	-24,38	-18,60	DC-
11	24,38	21,80	N	33	2,46	-5,80	E2	55	-24,38	-15,40	DC-
12	16,58	12,20		34	0,03	5,80		56	-24,38	-12,20	
13	16,58	15,40		35	0,03	9,00		57	-24,38	-9,00	
14	16,58	18,60	N	36	0,03	12,20		58	-24,38	-5,80	AC
15	16,58	21,80	N	37	0,03	15,40		59	-24,38	-2,50	AC
16	13,42	-21,80		38	0,03	18,60		60	-24,38	0,70	AC
17	13,42	-18,60		39	0,03	21,80		61	-24,38	3,90	AC
18	13,42	-15,40		40	-8,51	-21,80	DC-	62	-24,38	7,10	AC
19	13,42	-12,20		41	-8,51	-18,60	E4	63	-24,38	15,40	DC+
20	13,42	-9,00		42	-8,51	-15,40		64	-24,38	18,60	DC+
21	13,42	-5,80		43	-8,51	-12,20		65	-24,38	21,80	DC+
22	8,38	2,60		44	-12,23	-9,00					

all values in mm



Pinout and Dimensions



Pinout

This is an electrostatic discharge sensitive device (ESDS) due to international standard IEC 61340.

***IMPORTANT INFORMATION AND WARNINGS**

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.