SKiiP 36NAB126V10

CONVERTER, INVERTER, BRAKE



MiniSKiiP® 3

3-phase bridge rectifier + brake chopper + 3-phase bridge inverter

SKiiP 36NAB126V10

Features

- Fast Trench IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised file no. E63532

Typical Applications*

- Inverter up to 36 kVA
- Typical motor power 18,5 kW

Remarks

- V_{CEsat} , V_F = chip level value



NAB

Absolute Maximum Ratings		T_s = 25 °C, unless otherwise specified	
Symbol	**Conditions**	**Values**	**Units**
IGBT - Inverter, Chopper			
V_{CES}		1200	V
I_C	T_s = 25 (70) °C	88 (66)	A
I_{CRM}		140	A
V_{GES}		± 20	V
T_j		- 40 ... + 150	°C
Diode - Inverter, Chopper			
I_F	T_s = 25 (70) °C	91 (68)	A
I_{FRM}		140	A
T_j		- 40 ... + 150	°C
Diode - Rectifier			
V_{RRM}		1600	V
I_F	T_s = 70 °C	67	A
I_{FSM}	t_p = 10 ms, sin 180 °, T_j = 25 °C	850	A
i^2t	t_p = 10 ms, sin 180 °, T_j = 25 °C	3600	A^2s
T_j		- 40 ... + 150	°C
Module			
I_{tRMS}	per power terminal (20 A / spring)	80	A
T_{stg}		- 40 ... + 125	°C
V_{isol}	AC, 1 min.	2500	V

Characteristics		T_s = 25 °C, unless otherwise specified			
Symbol	**Conditions**	**min.**	**typ.**	**max.**	**Units**
IGBT - Inverter, Chopper					
V_{CEsat}	I_{Cnom} = 70 A, T_j = 25 (125) °C		1,7 (2)	2,1 (2,4)	V
$V_{GE(th)}$	V_{GE} = V_{CE}, I_C = 3 mA	5	5,8	6,5	V
$V_{CE(TO)}$	T_j = 25 (125) °C		1 (0,9)	1,2 (1,1)	V
r_T	T_j = 25 (125) °C		10 (16)	13 (19)	mΩ
C_{ies}	V_{CE} = 25 V, V_{GE} = 0 V, f = 1 MHz		4,8		nF
C_{oes}	V_{CE} = 25 V, V_{GE} = 0 V, f = 1 MHz		1		nF
C_{res}	V_{CE} = 25 V, V_{GE} = 0 V, f = 1 MHz		0,6		nF
$R_{th(j-s)}$	per IGBT		0,5		K/W
$t_{d(on)}$	under following conditions		80		ns
t_r	V_{CC} = 600 V, V_{GE} = ± 15 V		25		ns
$t_{d(off)}$	I_{Cnom} = 70 A, T_j = 125°C		390		ns
t_f	R_{Gon} = R_{Goff} = 9 Ω		90		ns
E_{on}	inductive load		9		mJ
E_{off}			7,7		mJ
Diode - Inverter, Chopper					
$V_F = V_{EC}$	I_{Fnom} = 70 A, T_j = 25 (125) °C		1,5 (1,5)	1,7 (1,7)	V
$V_{(TO)}$	T_j = 25 (125) °C		1 (0,8)	1,1 (0,9)	V
r_T	T_j = 25 (125) °C		7,1 (10)	8,6 (11)	mΩ
$R_{th(j-s)}$	per diode		0,7		K/W
I_{RRM}	under following conditions		77		A
Q_{rr}	I_{Fnom} = 70 A, V_R = 600 V		18		µC
E_{rr}	V_{GE} = 0 V, T_j = 125 °C		7,5		mJ
	di_F/dt = 2000 A/µs				
Diode - Rectifier					
V_F	I_{Fnom} = 40 A, T_j = 25 °C		1,1		V
$V_{(TO)}$	T_j = 125 °C		0,8		V
r_T	T_j = 125 °C		9		mΩ
$R_{th(j-s)}$	per diode		0,85		K/W
Temperature Sensor					
R_{ts}	3 %, T_r = 25 (100) °C		1000(1670)		Ω
Mechanical Data					
w			95		g
M_s	Mounting torque	2		2,5	Nm

 © by SEMIKRON



Fig. 1 Typ. output characteristic



Fig. 2 Typ. rated current vs. temperature



Fig. 3 Typ. transfer characteristic



Fig. 4 Reverse bias safe operating area



Fig. 5 Typ. Turn-on /-off energy = f (I_C)



Fig. 6 Typ. Turn-on /-off energy = f (R_G)

 © by SEMIKRON



Fig. 7 Typ. gate charge characteristic



Fig. 8 Typ. thermal impedance



Fig. 9 Typ. freewheeling diode forward characteristic



Fig. 10 Typ. input bridge forward characteristic

 © by SEMIKRON





This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.