

SKiM® 4

Trench IGBT Modules

SKiM201MLI12E4

Features


- IGBT 4 Trench Gate Technology
- Solder technology
- $V_{CE(sat)}$ with positive temperature coefficient
- Low inductance case
- Insulated by Al_2O_3 DCB (Direct Copper Bonded) ceramic substrate
- Pressure contact technology for thermal contacts
- Spring contact system to attach driver PCB to the control terminals
- High short circuit capability, self limiting to $6 \times I_C$
- Integrated temperature sensor

Typical Applications

- Automotive inverter
- High reliability AC inverter wind
- High reliability AC inverter drives

Remarks*


- Case temperature limited to $T_s = 125^\circ C$ max; $T_c = T_s$ (for baseplateless modules)
- Recommended $T_{jop} = -40 \dots +150^\circ C$
- IGBT1 : outer IGBTs T1 & T4
- IGBT2 : inner IGBTs T2 & T3
- Diode1 : outer diodes D1 & D4
- Diode2 : inner diodes D2 & D3
- Diode5 : clamping diodes D5 & D6



MLI

Absolute Maximum Ratings

Symbol	Conditions		Values	Unit
IGBT1				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 175 °C	T _s = 25 °C	206	A
		T _s = 70 °C	166	A
I _{Cnom}			200	A
I _{CRM}	I _{CRM} = 3 x I _{Cnom}		600	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V, V _{GE} ≤ 15 V, T _j = 150 °C, V _{CES} ≤ 1200 V		10	μs
T _j			-40 ... 175	°C
IGBT2				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 175 °C	T _s = 25 °C	206	A
		T _s = 70 °C	166	A
I _{Cnom}			200	A
I _{CRM}	I _{CRM} = 3 x I _{Cnom}		600	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V, V _{GE} ≤ 15 V, T _j = 150 °C, V _{CES} ≤ 1200 V		10	μs
T _j			-40 ... 175	°C
Diode1				
V _{RRM}	T _j = 25 °C		1200	V
I _F	T _j = 175 °C	T _s = 25 °C	187	A
		T _s = 70 °C	148	A
I _{Fnom}			200	A
I _{FRM}	I _{FRM} = 2 x I _{Fnom}		400	A
I _{FSM}	10 ms, sin 180°, T _j = 25 °C		990	A
T _j			-40 ... 175	°C
Diode2				
V _{RRM}	T _j = 25 °C		1200	V
I _F	T _j = 175 °C	T _s = 25 °C	187	A
		T _s = 70 °C	148	A
I _{Fnom}			200	A
I _{FRM}	I _{FRM} = 2 x I _{Fnom}		400	A
I _{FSM}	10 ms, sin 180°, T _j = 25 °C		990	A
T _j			-40 ... 175	°C
Diode5				
V _{RRM}	T _j = 25 °C		1200	V
I _F	T _j = 175 °C	T _s = 25 °C	141	A
		T _s = 70 °C	111	A
I _{Fnom}			200	A
I _{FRM}	I _{FRM} = 2 x I _{Fnom}		400	A
I _{FSM}	10 ms, sin 180°, T _j = 25 °C		990	A
T _j			-40 ... 175	°C
Module				
I _{t(RMS)}			400	A
T _{stg}			-40 ... 125	°C
V _{isol}	AC sinus 50 Hz, t = 1 min		2500	V



SKiM® 4

Trench IGBT Modules

SKiM201MLI12E4

Features

- IGBT 4 Trench Gate Technology
- Solder technology
- $V_{CE(sat)}$ with positive temperature coefficient
- Low inductance case
- Insulated by Al_2O_3 DCB (Direct Copper Bonded) ceramic substrate
- Pressure contact technology for thermal contacts
- Spring contact system to attach driver PCB to the control terminals
- High short circuit capability, self limiting to $6 \times I_C$
- Integrated temperature sensor


Typical Applications

- Automotive inverter
- High reliability AC inverter wind
- High reliability AC inverter drives


Remarks*

- Case temperature limited to $T_s = 125^\circ C$ max; $T_c = T_s$ (for baseplateless modules)
- Recommended $T_{jop} = -40 \dots +150^\circ C$
- IGBT1 : outer IGBTs T1 & T4
- IGBT2 : inner IGBTs T2 & T3
- Diode1 : outer diodes D1 & D4
- Diode2 : inner diodes D2 & D3
- Diode5 : clamping diodes D5 & D6

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
IGBT1						
V _{CE(sat)}	I _C = 200 A	T _J = 25 °C		1.80	2.05	V
	V _{GE} = 15 V chipelevel	T _J = 150 °C		2.20	2.40	V
V _{CE0}	chipelevel	T _J = 25 °C		0.80	0.90	V
		T _J = 150 °C		0.70	0.80	V
r _{CE}	V _{GE} = 15 V	T _J = 25 °C		5.0	5.8	mΩ
	chipelevel	T _J = 150 °C		7.5	8.0	mΩ
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 7.6 mA		5	5.8	6.5	V
I _{CES}	V _{GE} = 0 V, V _{CE} = 1200 V, T _J = 25 °C				2.7	mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		12.3		nF
C _{oes}		f = 1 MHz		0.81		nF
C _{res}		f = 1 MHz		0.69		nF
Q _G	V _{GE} = - 15 V...+ 15 V			1600		nC
R _{Gint}	T _J = 25 °C			3.8		Ω
t _{d(on)}	V _{CE} = 600 V	T _J = 150 °C		182		ns
t _r	I _C = 200 A	T _J = 150 °C		52		ns
E _{on}	V _{GE} = +15/-15 V R _{G on} = 1.5 Ω	T _J = 150 °C		14.81		mJ
t _{d(off)}	R _{G off} = 1.5 Ω	T _J = 150 °C		446		ns
t _f	di/dt _{on} = 5700 A/μs di/dt _{off} = 2600 A/μs	T _J = 150 °C		98		ns
E _{off}		T _J = 150 °C		22.6		mJ
R _{th(j-s)}	per IGBT			0.29		K/W
IGBT2						
V _{CE(sat)}	I _C = 200 A	T _J = 25 °C		1.80	2.05	V
	V _{GE} = 15 V chipelevel	T _J = 150 °C		2.20	2.40	V
V _{CE0}	chipelevel	T _J = 25 °C		0.80	0.90	V
		T _J = 150 °C		0.70	0.80	V
r _{CE}	V _{GE} = 15 V	T _J = 25 °C		5.0	5.8	mΩ
	chipelevel	T _J = 150 °C		7.5	8.0	mΩ
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 7.6 mA		5	5.8	6.5	V
I _{CES}	V _{GE} = 0 V, V _{CE} = 1200 V, T _J = 25 °C				2.7	mA
C _{ies}	V _{CE} = 25 V V _{GE} = 0 V	f = 1 MHz		12.3		nF
C _{oes}		f = 1 MHz		0.81		nF
C _{res}		f = 1 MHz		0.69		nF
Q _G	V _{GE} = - 15 V...+ 15 V			1600		nC
R _{Gint}	T _J = 25 °C			3.8		Ω
t _{d(on)}	V _{CE} = 600 V	T _J = 150 °C		184		ns
t _r	I _C = 200 A	T _J = 150 °C		59		ns
E _{on}	V _{GE} = +15/-15 V R _{G on} = 1.5 Ω	T _J = 150 °C		7.33		mJ
t _{d(off)}	R _{G off} = 1.5 Ω	T _J = 150 °C		457		ns
t _f	di/dt _{on} = 4960 A/μs di/dt _{off} = 1840 A/μs	T _J = 150 °C		73		ns
E _{off}		T _J = 150 °C		23.87		mJ
R _{th(j-s)}	per IGBT			0.29		K/W



MLI



SKiM® 4

Trench IGBT Modules

SKiM201MLI12E4

Features

- IGBT 4 Trench Gate Technology
- Solder technology
- $V_{CE(sat)}$ with positive temperature coefficient
- Low inductance case
- Insulated by Al_2O_3 DCB (Direct Copper Bonded) ceramic substrate
- Pressure contact technology for thermal contacts
- Spring contact system to attach driver PCB to the control terminals
- High short circuit capability, self limiting to $6 \times I_C$
- Integrated temperature sensor


Typical Applications

- Automotive inverter
- High reliability AC inverter wind
- High reliability AC inverter drives


Remarks*

- Case temperature limited to $T_s = 125^\circ\text{C}$ max; $T_c = T_s$ (for baseplateless modules)
- Recommended $T_{jop} = -40 \dots +150^\circ\text{C}$
- IGBT1 : outer IGBTs T1 & T4
- IGBT2 : inner IGBTs T2 & T3
- Diode1 : outer diodes D1 & D4
- Diode2 : inner diodes D2 & D3
- Diode5 : clamping diodes D5 & D6

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Diode1						
V _F = V _{EC}	I _F = 200 A	T _j = 25 °C		2.20	2.52	V
	chiplevel	T _j = 150 °C		2.15	2.47	V
V _{F0}	chiplevel	T _j = 25 °C		1.30	1.50	V
		T _j = 150 °C		0.90	1.10	V
r _F	chiplevel	T _j = 25 °C		4.5	5.1	mΩ
		T _j = 150 °C		6.3	6.9	mΩ
I _{RRM}	I _F = 200 A	T _j = 150 °C		211		A
Q _{rr}	di/dt _{off} = 5000 A/μs V _R = 600 V	T _j = 150 °C		36.47		μC
E _{rr}	V _{GE} = +15/-15 V	T _j = 150 °C		14.53		mJ
R _{th(j-s)}				0.36		K/W
Diode2						
V _F = V _{EC}	I _F = 200 A	T _j = 25 °C		2.20	2.52	V
	chiplevel	T _j = 150 °C		2.15	2.47	V
V _{F0}	chiplevel	T _j = 25 °C		1.30	1.50	V
		T _j = 150 °C		0.90	1.10	V
r _F	chiplevel	T _j = 25 °C		4.5	5.1	mΩ
		T _j = 150 °C		6.3	6.9	mΩ
I _{RRM}	I _F = 200 A	T _j = 150 °C		212		A
Q _{rr}	di/dt _{off} = 5000 A/μs V _R = 600 V	T _j = 150 °C		36.47		μC
E _{rr}	V _{GE} = +15/-15 V	T _j = 150 °C		-		mJ
R _{th(j-s)}				0.36		K/W
Diode5						
V _F = V _{EC}	I _F = 200 A	T _j = 25 °C		2.20	2.52	V
	chiplevel	T _j = 150 °C		2.15	2.47	V
V _{F0}	chiplevel	T _j = 25 °C		1.30	1.50	V
		T _j = 150 °C		0.90	1.10	V
r _F	chiplevel	T _j = 25 °C		4.5	5.1	mΩ
		T _j = 150 °C		6.3	6.9	mΩ
I _{RRM}	I _F = 200 A	T _j = 150 °C		212		A
Q _{rr}	di/dt _{off} = 5700 A/μs V _R = 600 V	T _j = 150 °C		34.87		μC
E _{rr}	V _{GE} = +15/-15 V	T _j = 150 °C		15.79		mJ
R _{th(i-s)}				0.55		K/W



MLI



SKiM® 4

Trench IGBT Modules

SKiM201MLI12E4

Features

- IGBT 4 Trench Gate Technology
- Solder technology
- $V_{CE(sat)}$ with positive temperature coefficient
- Low inductance case
- Insulated by Al_2O_3 DCB (Direct Copper Bonded) ceramic substrate
- Pressure contact technology for thermal contacts
- Spring contact system to attach driver PCB to the control terminals
- High short circuit capability, self limiting to $6 \times I_C$
- Integrated temperature sensor


Typical Applications

- Automotive inverter
- High reliability AC inverter wind
- High reliability AC inverter drives

Remarks*

- Case temperature limited to $T_s = 125^\circ\text{C}$ max; $T_c = T_s$ (for baseplateless modules)
- Recommended $T_{jop} = -40 \dots +150^\circ\text{C}$
- IGBT1 : outer IGBTs T1 & T4
- IGBT2 : inner IGBTs T2 & T3
- Diode1 : outer diodes D1 & D4
- Diode2 : inner diodes D2 & D3
- Diode5 : clamping diodes D5 & D6

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Module						
L _{sCE1}			25			nH
L _{sCE2}			32			nH
R _{CC'+EE'}	measured between terminal 4 and 24	T _s = 25 °C	0.4			mΩ
		T _s = 125 °C	0.6			mΩ
M _s	to heat sink M5		2	3		Nm
M _t		to terminals M6	4	5		Nm
						Nm
w			317			g
Temperature Sensor						
R ₁₀₀	T _c =100°C (R ₂₅ =5 kΩ)		493 ± 5%			Ω
B _{100/125}	R _(T) =R ₁₀₀ exp[B _{100/125} (1/T-1/T ₁₀₀)]; T[K];		3550 ±2%			K



MLI




Fig. 1: Typ. IGBT1 output characteristic, incl. $R_{CC'+EE'}$




Fig. 2: IGBT1 rated current vs. Temperature $I_C=f(T_s)$




Fig. 3: Typ. IGBT1 & Diode5 turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. IGBT1 & Diode5 turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. IGBT1 transfer characteristic










Fig. 6: Typ. IGBT1 gate charge characteristic






Fig. 15: Typ. IGBT2 & Diode1 turn-on /-off energy = $f(I_C)$




Fig. 16: Typ. IGBT2 & Diode1 turn-on / -off energy = $f(R_G)$




Fig. 17: Typ. IGBT2 transfer characteristic




Fig. 18: Typ. IGBT2 gate charge characteristic




Fig. 19: Typ. IGBT2 switching times vs. I_C




Fig. 20: Typ. IGBT2 switching times vs. gate resistor R_G




Fig. 21: Transient thermal impedance of IGBT2, Diode1 & Diode2






Fig. 22: Typ. Diode1 & Diode2 forward characteristic, incl. $R_{CC'+EE'}$



SKiM 4



MLI

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, chapter IX.

***IMPORTANT INFORMATION AND WARNINGS**

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.