


SKiiP 39AC12T4V21



MiniSKiiP® 3

Sixpack

SKiiP 39AC12T4V21

Features*


- Trench 4 IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised: File no. E63532
- Insulated by Si₃N₄ (Silicon Nitride) AMB (Active Metal Brazed) ceramic substrate for optimized thermal performance

Typical Applications

- Inverter up to 50 kVA
- Typical motor power 30 kW

Remarks

- Max. case temperature limited to T_C=125°C
- Product reliability results valid for T_j≤150°C (recommended T_{j,op}=-40...+150°C)
- For short circuit: Soft R_{Goff} recommended
- MiniSKiiP "Technical Explanations" and "Mounting Instructions" are part of the data sheet. Please refer to both documents for further information.



AC


Absolute Maximum Ratings

Symbol	Conditions	Values	Unit
Inverter - IGBT			
V _{CES}	T _j = 25 °C	1200	V
I _C	λ _{paste} =0.8 W/(mK) T _j = 175 °C	189	A
I _C	λ _{paste} =2.5 W/(mK) T _j = 175 °C	249	A
I _C	T _s = 25 °C T _s = 70 °C	154	A
I _C	T _s = 25 °C T _s = 70 °C	204	A
I _{Cnom}		150	A
I _{CRM}		450	A
V _{GES}		-20 ... 20	V
t _{psc}	V _{CC} = 800 V V _{GE} ≤ 15 V V _{CES} ≤ 1200 V T _j = 150 °C	10	μs
T _j		-40 ... 175	°C
Inverse - Diode			
V _{RRM}	T _j = 25 °C	1200	V
I _F	λ _{paste} =0.8 W/(mK) T _j = 175 °C	149	A
I _F	λ _{paste} =2.5 W/(mK) T _j = 175 °C	221	A
I _F	T _s = 25 °C T _s = 70 °C	118	A
I _F	T _s = 25 °C T _s = 70 °C	177	A
I _{FRM}		450	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 150 °C	900	A
T _j		-40 ... 175	°C
Module			
I _{t(RMS)}	T _{terminal} = 80 °C, 20 A per spring	160	A
T _{stg}	module without TIM	-40 ... 125	°C
V _{isol}	AC sinus 50 Hz, t = 1 min	2500	V

Characteristics

Symbol	Conditions	min.	typ.	max.	Unit
Inverter - IGBT					
V _{CE(sat)}	I _C = 150 A V _{GE} = 15 V chipelevel		1.85	2.10	V
	T _j = 25 °C T _j = 150 °C		2.25	2.45	V
V _{CE0}	chipelevel		0.80	0.90	V
	T _j = 25 °C T _j = 150 °C		0.70	0.80	V
r _{CE}	V _{GE} = 15 V chipelevel		7.0	8.0	mΩ
	T _j = 25 °C T _j = 150 °C		10	11	mΩ
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 6 mA	5	5.8	6.5	V
I _{CES}	V _{GE} = 0 V, V _{CE} = 1200 V, T _j = 25 °C			1.5	mA
C _{ies}	V _{CE} = 25 V f = 1 MHz		8.80		nF
C _{oes}	V _{GE} = 0 V f = 1 MHz		0.58		nF
C _{res}	f = 1 MHz		0.47		nF
Q _G	V _{GE} = - 8 V...+ 15 V		850		nC
R _{Gint}	T _j = 25 °C		5.0		Ω
t _{d(on)}	V _{CC} = 600 V T _j = 150 °C		165		ns
t _r	I _C = 150 A T _j = 150 °C		50		ns
E _{on}	R _{G on} = 1 Ω T _j = 150 °C		22.5		mJ
t _{d(off)}	R _{G off} = 1 Ω T _j = 150 °C		390		ns
t _f	di/dt _{on} = 2840 A/μs di/dt _{off} = 1880 A/μs T _j = 150 °C		80		ns
E _{off}	V _{GE} = +15/-15 V T _j = 150 °C		14		mJ
R _{th(j-s)}	per IGBT, λ _{paste} =0.8 W/(mK)		0.26		K/W
R _{th(j-s)}	per IGBT, λ _{paste} =2.5 W/(mK)		0.16		K/W

SKiiP 39AC12T4V21



MiniSKiiP® 3

Sixpack

SKiiP 39AC12T4V21

Features*

- Trench 4 IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised: File no. E63532
- Insulated by Si₃N₄ (Silicon Nitride) AMB (Active Metal Brazed) ceramic substrate for optimized thermal performance


Typical Applications

- Inverter up to 50 kVA
- Typical motor power 30 kW

Remarks

- Max. case temperature limited to $T_C=125^{\circ}\text{C}$
- Product reliability results valid for $T_j \leq 150^{\circ}\text{C}$ (recommended $T_{j,op} = -40 \dots +150^{\circ}\text{C}$)
- For short circuit: Soft R_{Goff} recommended
- MiniSKiiP "Technical Explanations" and "Mounting Instructions" are part of the data sheet. Please refer to both documents for further information.

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Inverse - Diode						
V _F = V _{EC}	I _F = 150 A	T _j = 25 °C		2.14	2.46	V
	V _{GE} = 0 V	T _j = 150 °C		2.07	2.38	V
	chiplevel					
V _{F0}		T _j = 25 °C		1.30	1.50	V
	chiplevel	T _j = 150 °C		0.90	1.10	V
r _F		T _j = 25 °C		5.6	6.4	mΩ
	chiplevel	T _j = 150 °C		7.8	8.5	mΩ
I _{RRM}	I _F = 150 A	T _j = 150 °C		188		A
Q _{rr}	di/dt _{off} = 4020 A/μs	T _j = 150 °C		27		μC
E _{rr}	V _{GE} = +15/-15 V	T _j = 150 °C		11.4		mJ
	V _{CC} = 600 V					
R _{th(j-s)}	per Diode, λ _{paste} =0.8 W/(mK)			0.45		K/W
R _{th(j-s)}	per Diode, λ _{paste} =2.5 W/(mK)			0.24		K/W
Module						
L _{CE}				-		nH
M _s	to heat sink		2		2.5	Nm
w				82		g
Temperature Sensor						
R ₁₀₀	T _r =100°C (R ₂₅ =1000Ω)			1670 ± 3%		Ω
R _(T)	R _(T) =1000Ω[1+A(T-25°C)+B(T-25°C) ²] , A = 7.635*10 ⁻³ °C ⁻¹ , B = 1.731*10 ⁻⁵ °C ⁻²					



AC




Fig. 1: Typ. output characteristic




Fig. 2: Rated current vs. temperature $I_C = f(T_S)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic




Fig. 6: Typ. gate charge characteristic




Fig. 7: Typ. switching times vs. I_C




Fig. 8: Typ. switching times vs. gate resistor R_G




Fig. 9: Typ. transient thermal impedance




Fig. 10: Typ. CAL diode forward characteristic




Fig. 11: Typ. CAL diode peak reverse recovery current






Fig. 12: Typ. CAL diode recovery charge

Pin out											
Pin	X	Y	Function	Pin	X	Y	Function	Pin	X	Y	Function
1	15,83	-25,30	g5	31	-16,05	-15,02	V	61	-39,33	25,30	DC-
2	15,83	-6,40	E5	32	-16,05	-11,82	V	62	-40,23	-25,30	DC+
3	15,83	-3,20		33	-16,05	-8,62	V	63	-40,23	-22,10	
4	15,83	0		34	-16,05	-5,42	V	64	-40,23	-15,70	U
5	15,83	3,20		35	-19,23	-25,30		65	-40,23	-12,50	U
6	15,83	6,40	T-	36	-19,70	-15,02	V	66	-40,23	-9,30	U
7	15,83	15,70	T+	37	-19,70	-11,82	V	67	-40,23	-6,10	U
8	15,83	18,90		38	-19,70	-8,62	V	68	-50,18	-25,30	DC+
9	15,83	22,10		39	-19,70	-5,42	V	69	-50,18	-22,10	DC+
10	15,83	25,30		40	-22,26	-1,00	g3	70	-50,18	-18,90	DC+
11	8,13	-25,30		41	-22,26	2,20	E3	71	-50,18	-15,70	
12	8,13	-22,10		42	-22,68	22,10	E4	72	-50,18	-9,50	
13	8,13	22,10		43	-22,68	25,30	g2	73	-50,18	-6,30	
14	8,13	25,30	g6	44	-25,91	-1,00		74	-50,18	6,30	
15	1,83	-15,39	W	45	-25,91	2,20		75	-50,18	9,50	
16	1,83	-12,19	W	46	-29,18	8,74		76	-50,18	22,10	DC-
17	1,83	-8,99	W	47	-29,18	11,94		77	-50,18	25,30	DC-
18	1,83	-5,79	W	48	-32,83	8,74		78	-53,83	-25,30	DC+
19	0,43	22,10		49	-32,83	11,94		79	-53,83	-22,10	DC+
20	0,43	25,30		50	-35,68	22,10	DC-	80	-53,83	-18,90	DC+
21	-1,08	-25,30		51	-35,68	25,30	DC-	81	-53,83	-15,70	
22	-1,83	-15,39	W	52	-36,58	-25,30	DC+	82	-53,83	-9,50	
23	-1,83	-12,19	W	53	-36,58	-22,10		83	-53,83	-6,30	
24	-1,83	-8,99	W	54	-36,58	-15,70	U	84	-53,83	3,10	g1
25	-1,83	-5,79	W	55	-36,58	-12,50	U	85	-53,83	6,30	E1
26	-5,83	3,95		56	-36,58	-9,30	U	86	-53,83	9,50	
27	-7,28	22,10	E6	57	-36,58	-6,10	U	87	-53,83	22,10	DC-
28	-7,28	25,30	g4	58	-39,33	15,70		88	-53,83	25,30	DC-
29	-14,98	22,10		59	-39,33	18,90	E2				
30	-14,98	25,30		60	-39,33	22,10	DC-				

all values in mm



Pinout and Dimensions



Pinout

This is an electrostatic discharge sensitive device (ESDS) due to international standard IEC 61340.

***IMPORTANT INFORMATION AND WARNINGS**

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.