


SKM 100GB176D



SEMITRANS® 2

Trench IGBT Modules

SKM 100GB176D

Features


- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability, self limiting to $6 \times I_C$

Typical Applications*

- AC inverter drives mains 575 - 750 V AC
- Public transport (auxiliary syst.


Absolute Maximum Ratings		T _{case} = 25°C, unless otherwise specified		
Symbol	Conditions		Values	Units
IGBT				
V _{CES}	T _j = 25 °C		1700	V
I _C	T _j = 150 °C	T _c = 25 °C	125	A
		T _c = 80 °C	90	A
I _{CRM}	I _{CRM} =2xI _{Cnom}		150	A
V _{GES}			± 20	V
t _{psc}	V _{CC} = 1200 V; V _{GE} ≤ 20 V; T _j = 125 °C V _{CES} < 1700 V		10	µs
Inverse Diode				
I _F	T _j = 150 °C	T _c = 25 °C	100	A
		T _c = 80 °C	70	A
I _{FRM}	I _{FRM} =2xI _{Fnom}		150	A
I _{FSM}	t _p = 10 ms; sin.	T _j = 150 °C	720	A
Module				
I _{t(RMS)}			200	A
T _{vj}			- 40 ... +150	°C
T _{stg}			- 40 ... +125	°C
V _{isol}	AC, 1 min.		4000	V

Characteristics		$T_{case} = 25^\circ\text{C}$, unless otherwise specified			
Symbol	Conditions	min.	typ.	max.	Units
IGBT					
$V_{GE(th)}$	$V_{GE} = V_{CE}, I_C = 3\text{ mA}$	5,2	5,8	6,4	V
I_{CES}	$V_{GE} = 0\text{ V}, V_{CE} = V_{CES}$			3	mA
V_{CE0}			$T_J = 25^\circ\text{C}$	1	V
			$T_J = 125^\circ\text{C}$	0,9	V
r_{CE}	$V_{GE} = 15\text{ V}$		$T_J = 25^\circ\text{C}$	13	m Ω
			$T_J = 125^\circ\text{C}$	20	m Ω
$V_{CE(sat)}$	$I_{Cnom} = 75\text{ A}, V_{GE} = 15\text{ V}$		$T_J = 25^\circ\text{C}_{chiplev.}$	2	V
			$T_J = 125^\circ\text{C}_{chiplev.}$	2,4	V
C_{ies}	$V_{CE} = 25, V_{GE} = 0\text{ V}$	$f = 1\text{ MHz}$		5,7	nF
C_{oes}				0,28	nF
C_{res}				0,22	nF
Q_G	$V_{GE} = -8\text{V}/+15\text{V}$			620	nC
R_{Gint}	$T_J = 25^\circ\text{C}$			8,5	Ω
$t_{d(on)}$	$R_{Gon} = 4,2\ \Omega$ $di/dt = 1680\text{ A}/\mu\text{s}$	$V_{CC} = 1200\text{V}$ $I_C = 75\text{A}$		280	ns
t_r				40	ns
E_{on}				44	mJ
$t_{d(off)}$	$R_{Goff} = 4,2\ \Omega$ $di/dt = 490\text{ A}/\mu\text{s}$	$T_J = 125^\circ\text{C}$ $V_{GE} = -15\text{V}$ $L_s = 20\text{ nH}$		680	ns
t_f				140	ns
E_{off}				28,5	mJ
$R_{th(j-c)}$	per IGBT			0,24	K/W



GB

SKM 100GB176D



SEMITRANS® 2

Trench IGBT Modules

SKM 100GB176D

Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability, self limiting to $6 \times I_C$


Typical Applications*

- AC inverter drives mains 575 - 750 V AC
- Public transport (auxiliary syst.

Characteristics		min.	typ.	max.	Units
Symbol	Conditions				
Inverse Diode					
$V_F = V_{EC}$	$I_{Fnom} = 75 \text{ A}; V_{GE} = 0 \text{ V}$				
	$T_j = 25 \text{ }^\circ\text{C}_{chiplev.}$		1,6	1,9	V
	$T_j = 125 \text{ }^\circ\text{C}_{chiplev.}$		1,6	1,9	V
V_{F0}					
	$T_j = 25 \text{ }^\circ\text{C}$		1,1	1,3	V
	$T_j = 125 \text{ }^\circ\text{C}$		0,9	1,1	V
r_F					
	$T_j = 25 \text{ }^\circ\text{C}$		6,7	8	mΩ
	$T_j = 125 \text{ }^\circ\text{C}$		9,3	11	mΩ
I_{RRM}	$I_F = 75 \text{ A}$		78,5		A
Q_{rr}	$di/dt = 1650 \text{ A}/\mu\text{s}$		29,6		μC
E_{rr}	$V_{GE} = -15 \text{ V}; V_{CC} = 1200 \text{ V}$		21,4		mJ
$R_{th(j-c)D}$	per diode			0,45	K/W
Module					
L_{CE}				30	nH
$R_{CC'+EE'}$	res., terminal-chip	$T_{case} = 25 \text{ }^\circ\text{C}$	0,75		mΩ
		$T_{case} = 125 \text{ }^\circ\text{C}$	1		mΩ
$R_{th(c-s)}$	per module			0,05	K/W
M_s	to heat sink M6		3	5	Nm
M_t	to terminals M5		2,5	5	Nm
w				160	g

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.



GB

SKM 100GB176D



SEMITRANS® 2

Trench IGBT Modules

SKM 100GB176D

Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability, self limiting to $6 \times I_C$







Typical Applications*







- AC inverter drives mains 575 - 750 V AC
- Public transport (auxiliary syst.


Z_{th}			
Symbol	Conditions	Values	Units
$Z_{th(j-c)I}$			
R_i	$i = 1$	160	mk/W
R_i	$i = 2$	60	mk/W
R_i	$i = 3$	16,5	mk/W
R_i	$i = 4$	3,5	mk/W
τ_{u_i}	$i = 1$	0,1056	s
τ_{u_i}	$i = 2$	0,009	s
τ_{u_i}	$i = 3$	0,0011	s
τ_{u_i}	$i = 4$	0,0005	s
$Z_{th(j-c)D}$			
R_i	$i = 1$	270	mk/W
R_i	$i = 2$	139	mk/W
R_i	$i = 3$	37	mk/W
R_i	$i = 4$	4	mk/W
τ_{u_i}	$i = 1$	0,0475	s
τ_{u_i}	$i = 2$	0,0104	s
τ_{u_i}	$i = 3$	0,0011	s
τ_{u_i}	$i = 4$	0,0003	s




GB







Case D 61



GB

Case D 61