


SKM 400GB125D



SEMITRANS® 3

Ultra Fast IGBT Modules

SKM 400GB125D

SKM 400GAL125D


SKM 400GAR125D

Features

- Low inductance case
- Short tail current with low temperature dependence
- High short circuit capability, self limiting to $6 \times I_{Cnom}$
- Fast & soft inverse CAL diodes
- Isolated copper baseplate using DBC Direct Copper Bonding Technology
- Large clearance (13 mm) and creepage distances (20 mm)

Typical Applications*

- Switched mode power supplies at $f_{sw} > 20\text{kHz}$
- Resonant inverters up to 100 kHz
- Inductive heating
- Electronic welders at $f_{sw} > 20\text{ kHz}$




GB

GAL

GAR

Absolute Maximum Ratings				$T_c = 25^\circ\text{C}$, unless otherwise specified	
Symbol	Conditions			Values	Units
IGBT					
V_{CES}	$T_j = 25^\circ\text{C}$			1200	V
I_C	$T_j = 150^\circ\text{C}$	$T_{case} = 25^\circ\text{C}$		400	A
		$T_{case} = 80^\circ\text{C}$		300	A
I_{CRM}	$I_{CRM} = 2 \times I_{Cnom}$			600	A
V_{GES}				± 20	V
t_{psc}	$V_{CC} = 600\text{ V}; V_{GE} \leq 20\text{ V}; T_j = 125^\circ\text{C}$ $V_{CES} < 1200\text{ V}$			10	μs
Inverse Diode					
I_F	$T_j = 150^\circ\text{C}$	$T_{case} = 25^\circ\text{C}$		390	A
		$T_{case} = 80^\circ\text{C}$		260	A
I_{FRM}	$I_{FRM} = 2 \times I_{Fnom}$			600	A
I_{FSM}	$t_p = 10\text{ ms; sin.}$	$T_j = 150^\circ\text{C}$		2880	A
Freewheeling Diode					
I_F	$T_j = 150^\circ\text{C}$	$T_{case} = 25^\circ\text{C}$		390	A
		$T_{case} = 80^\circ\text{C}$		260	A
I_{FRM}	$I_{FRM} = 2 \times I_{Fnom}$			600	A
I_{FSM}	$t_p = 10\text{ ms; sin.}$	$T_j = 150^\circ\text{C}$		2880	A
Module					
$I_{t(RMS)}$				500	A
T_{vj}				- 40...+ 150	$^\circ\text{C}$
T_{stg}				- 40...+ 125	$^\circ\text{C}$
V_{isol}	AC, 1 min.			4000	V

Characteristics			T _c = 25 °C, unless otherwise specified			
Symbol	Conditions		min.	typ.	max.	Units
IGBT						
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 12 mA		4,5	5,5	6,5	V
I _{CES}	V _{GE} = 0 V, V _{CE} = V _{CES}	T _j = 25 °C		0,15	0,45	mA
V _{CE0}		T _j = 25 °C		1,4		V
		T _j = 125 °C		1,7		V
r _{CE}	V _{GE} = 15 V	T _j = 25°C		6,3		mΩ
		T _j = 125°C		7,6		mΩ
V _{CE(sat)}	I _{Cnom} = 300 A, V _{GE} = 15 V	T _j = 25°C _{chiplev.}		3,3	3,85	V
		T _j = 125°C _{chiplev.}		4	4,55	V
C _{ies}	V _{CE} = 25, V _{GE} = 0 V	f = 1 MHz		22	30	nF
C _{oes}				3,3	4	nF
C _{res}				1,2	1,6	nF
Q _G	V _{GE} = 0V - +20V			2650		nC
R _{Gint}	T _j = °C			1,25		Ω
t _{d(on)}	R _{Gon} = 2 Ω	V _{CC} = 600V I _C = 300A T _j = 125 °C V _{GE} = ±15V		70		ns
t _r				50		ns
E _{on}				17		mJ
t _{d(off)}	R _{Goff} = 2 Ω			500		ns
t _f				32		ns
E _{off}				18		mJ
R _{th(j-c)}	per IGBT				0,05	K/W



SEMITRANS® 3

Ultra Fast IGBT Modules

SKM 400GB125D

SKM 400GAL125D

SKM 400GAR125D

Features

- Low inductance case
- Short tail current with low temperature dependence
- High short circuit capability, self limiting to $6 \times I_{cnom}$
- Fast & soft inverse CAL diodes
- Isolated copper baseplate using DBC Direct Copper Bonding Technology
- Large clearance (13 mm) and creepage distances (20 mm)


Typical Applications*

- Switched mode power supplies at $f_{sw} > 20\text{kHz}$
- Resonant inverters up to 100 kHz
- Inductive heating
- Electronic welders at $f_{sw} > 20\text{ kHz}$

Characteristics					
Symbol	Conditions	min.	typ.	max.	Units
Inverse Diode					
$V_F = V_{EC}$	$I_{Fnom} = 300\text{ A}; V_{GE} = 0\text{ V}$ $T_j = 25\text{ °C}_{chiplev.}$ $T_j = 125\text{ °C}_{chiplev.}$		2 1,8	2,5	V V
V_{F0}	$T_j = 25\text{ °C}$ $T_j = 125\text{ °C}$		1,1	1,2	V V
r_F	$T_j = 25\text{ °C}$ $T_j = 125\text{ °C}$		3	4,3	mΩ mΩ
I_{RRM} Q_{rr} E_{rr}	$I_F = 300\text{ A}$ $di/dt = 8300\text{ A/μs}$ $V_{GE} = 0\text{ V}; V_{CC} = 600\text{ V}$		350 45 16		A μC mJ
$R_{th(j-c)D}$	per diode			0,125	K/W
Freewheeling Diode					
$V_F = V_{EC}$	$I_{Fnom} = 300\text{ A}; V_{GE} = 0\text{ V}$ $T_j = 25\text{ °C}_{chiplev.}$ $T_j = 125\text{ °C}_{chiplev.}$		2 1,8	2,5	V V
V_{F0}	$T_j = 25\text{ °C}$ $T_j = 125\text{ °C}$		1,1	1,2	V V
r_F	$T_j = 25\text{ °C}$ $T_j = 125\text{ °C}$		3	4,3	V V
I_{RRM} Q_{rr} E_{rr}	$I_F = 300\text{ A}$ $di/dt = 8300\text{ A/μs}$ $V_{GE} = 0\text{ V}; V_{CC} = 600\text{ V}$		350 45 16		A μC mJ
$R_{th(j-c)FD}$	per diode			0,125	K/W
Module					
L_{CE}			15	20	nH
$R_{CC'+EE'}$	res., terminal-chip $T_{case} = 25\text{ °C}$ $T_{case} = 125\text{ °C}$		0,35 0,5		mΩ mΩ
$R_{th(c-s)}$	per module			0,038	K/W
M_s	to heat sink M6	3		5	Nm
M_t	to terminals M6	2,5		5	Nm
w				325	g

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.




GB

GAL

GAR

SKM 400GB125D



SEMITRANS® 3

Ultra Fast IGBT Modules

SKM 400GB125D
SKM 400GAL125D
SKM 400GAR125D


Features







- Low inductance case
- Short tail current with low temperature dependence
- High short circuit capability, self limiting to $6 \times I_{cnom}$
- Fast & soft inverse CAL diodes
- Isolated copper baseplate using DBC Direct Copper Bonding Technology
- Large clearance (13 mm) and creepage distances (20 mm)







Typical Applications*


- Switched mode power supplies at $f_{sw} > 20\text{kHz}$
- Resonant inverters up to 100 kHz
- Inductive heating
- Electronic welders at $f_{sw} > 20\text{ kHz}$

Z_{th}			
Symbol	Conditions	Values	Units
$Z_{th(j-c)I}$			
R_i	$i = 1$	36	mk/W
R_i	$i = 2$	10,5	mk/W
R_i	$i = 3$	3	mk/W
R_i	$i = 4$	0,5	mk/W
τ_{ui}	$i = 1$	0,0744	s
τ_{ui}	$i = 2$	0,0078	s
τ_{ui}	$i = 3$	0,0016	s
τ_{ui}	$i = 4$	0,0002	s
$Z_{th(j-c)D}$			
R_i	$i = 1$	75	mk/W
R_i	$i = 2$	38	mk/W
R_i	$i = 3$	10,6	mk/W
R_i	$i = 4$	1,4	mk/W
τ_{ui}	$i = 1$	0,0386	s
τ_{ui}	$i = 2$	0,0201	s
τ_{ui}	$i = 3$	0,001	s
τ_{ui}	$i = 4$	0,003	s











Case D 56




GB

Case D 56



GAL

Case D 57 (→ D 56)



GAR

Case D 58 (→ D 56)