

SKYPER 42 R/02 (coated)



SKYPER®

IGBT Driver Core

Order Nr.: L5054305

SKYPER 42 R/02 (coated)

Features*

- Two output channels
- Integrated potential free power supply
- Under voltage protection
- Driver interlock top / bottom
- Dynamic short circuit protection
- Shut down input
- Failure management
- UL recognized, ROHS
- IEC 60068-1 (climate) 40/085/56, no condensation and no dripping water permitted, non-corrosive, climate class 3K3 acc. EN60721

Typical Applications

- Driver for IGBT modules in bridge circuits in industrial application
- DC bus voltage up to 1200V

Footnotes

Insulation test voltage with external high voltage diode


The insulation test is not performed as a series test at SEMIKRON

The driver power can be expanded to 50μC with external boost capacitors

Isolation coordination in compliance with EN50178 PD2

Operating temperature is real ambient temperature around the driver core

Degree of protection: IP00




Driver Core

Absolute Maximum Ratings			
Symbol	Conditions	Values	Unit
V_s	Supply voltage primary	16	V
V_{iH}	Input signal voltage (HIGH)	$V_s + 0.3$	V
V_{iL}	Input signal voltage (LOW)	GND - 0.3	V
$I_{outPEAK}$	Output peak current	30	A
$I_{outAVmax}$	Output average current	150	mA
f_{max}	Max. switching frequency	100	kHz
V_{CE}	Collector emitter voltage sense across the IGBT	1700	V
dv/dt	Rate of rise and fall of voltage secondary to primary side	100	kV/μs
V_{isolIO}	Insulation test voltage input - output (AC, rms, 2s)	4000	V
V_{isolPD}	Partial discharge extinction voltage, rms, $Q_{PD} \leq 10pC$	1500	V
V_{isol12}	Insulation test voltage output 1 - output 2 (AC, rms, 2s)	1500	V
$R_{Gon\ min}$	Minimum rating for external R_{Gon}	0.8	Ω
$R_{Goff\ min}$	Minimum rating for external R_{Goff}	0.8	Ω
$Q_{out/pulse}$	Max. rating for output charge per pulse	50	μC
T_{op}	Operating temperature	-40 ... 85	°C
T_{stg}	Storage temperature	-40 ... 85	°C

Characteristics					
Symbol	Conditions	min.	typ.	max.	Unit
V_s	Supply voltage primary side	14.4	15	15.6	V
I_{S0}	Supply current primary (no load)		125		mA
	Supply current primary side (max.)			800	mA
V_i	Input signal voltage on/off		15 / 0		V
V_{IT-}	Input threshold voltage (LOW)	4.6			V
R_{iN}	Input resistance (switching/HALT signal)		10		kΩ
$V_{G(on)}$	Turn-on output voltage		15		V
$V_{G(off)}$	Turn-off output voltage		-8		V
f_{ASIC}	Asic system switching frequency		8		MHz
$t_{d(on)IO}$	Input-output turn-on propagation time		1.1		μs
$t_{d(off)IO}$	Input-output turn-off propagation time		1.1		μs
$t_{d(terr)}$	Error input-output propagation time		2.3		μs
t_{pRESET}	Error reset time		0.009		ms
t_{TD}	Top-Bot interlock dead time		2		μs
C_{ps}	Coupling capacitance prim sec		3		pF
$I_{clear(PS)}$	Shortest distance in air, primary side to secondary side	12.2			mm
$I_{clear(SS)}$	Shortest distance in air, secondary sides	6.1			mm
$I_{creep(PS)}$	Shortest distance along the surface, primary side to secondary side (CTI ≥ 175)	12.2			mm
$I_{creep(SS)}$	Shortest distance along the surface, secondary sides (CTI ≥ 175)	6.1			mm
w	weight		40		g
MTBF	Mean Time Between Failure $T_a = 40^{\circ}C$		2.1		10 ⁶ h

SKYPER 42 R/02 (coated)



IGBT Driver Core

Order Nr.: L5054305

SKYPER 42 R/02 (coated)

Features*

- Two output channels
- Integrated potential free power supply
- Under voltage protection
- Driver interlock top / bottom
- Dynamic short circuit protection
- Shut down input
- Failure management
- UL recognized, ROHS
- IEC 60068-1 (climate) 40/085/56, no condensation and no dripping water permitted, non-corrosive, climate class 3K3 acc. EN60721

Typical Applications

- Driver for IGBT modules in bridge circuits in industrial application
- DC bus voltage up to 1200V

Footnotes

Insulation test voltage with external high voltage diode

The insulation test is not performed as a series test at SEMIKRON

The driver power can be expanded to 50μC with external boost capacitors

Isolation coordination in compliance with EN50178 PD2

Operating temperature is real ambient temperature around the driver core

Degree of protection: IP00

This is an electrostatic discharge sensitive device (ESDS) due to international standard IEC 61340.

*IMPORTANT INFORMATION AND WARNINGS

The specifications of SEMIKRON products may not be considered as guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of SEMIKRON products describe only the usual characteristics of products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.

