


SKM 400GB176D



SEMITRANS® 3

Trench IGBT Modules

SKM 400GB176D

SKM 400GAL176D


SKM 400GAR176D

Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability, self limiting to $6 \times I_C$

Typical Applications*

- AC inverter drives
- mains 575 - 750 V AC
- Public transport (auxiliary syst.)
- Wind power




GB

GAL

GAR

Absolute Maximum Ratings				$T_{case} = 25^\circ\text{C}$, unless otherwise specified	
Symbol	Conditions			Values	Units
IGBT					
V_{CES}	$T_j = 25^\circ\text{C}$			1700	V
I_C	$T_j = 150^\circ\text{C}$	$T_c = 25^\circ\text{C}$		430	A
		$T_c = 80^\circ\text{C}$		310	A
I_{CRM}	$I_{CRM} = 2 \times I_{Cnom}$			600	A
V_{GES}				± 20	V
t_{psc}	$V_{CC} = 1200\text{ V}; V_{GE} \leq 20\text{ V}; T_j = 125^\circ\text{C}$ $V_{CES} < 1700\text{ V}$			10	μs
Inverse Diode					
I_F	$T_j = 150^\circ\text{C}$	$T_c = 25^\circ\text{C}$		440	A
		$T_c = 80^\circ\text{C}$		300	A
I_{FRM}	$I_{FRM} = 2 \times I_{Fnom}$			600	A
I_{FSM}	$t_p = 10\text{ ms; sin.}$	$T_j = 150^\circ\text{C}$		2200	A
Freewheeling Diode					
I_F	$T_j = 150^\circ\text{C}$	$T_{case} = 25^\circ\text{C}$		440	A
		$T_{case} = 80^\circ\text{C}$		300	A
I_{FRM}	$I_{FRM} = 2 \times I_{Fnom}$			600	A
I_{FSM}	$t_p = 10\text{ ms; sin.}$	$T_j = 150^\circ\text{C}$		2200	A
Module					
$I_{t(RMS)}$				500	A
T_{vj}				- 40 ... + 150	$^\circ\text{C}$
T_{stg}				- 40 ... + 125	$^\circ\text{C}$
V_{isol}	AC, 1 min.			4000	V

Characteristics			T _{case} = 25°C, unless otherwise specified			
Symbol	Conditions		min.	typ.	max.	Units
IGBT						
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 12 mA		5,2	5,8	6,4	V
I _{CES}	V _{GE} = 0 V, V _{CE} = V _{CES}	T _j = 25 °C			4	mA
V _{CE0}		T _j = 25 °C		1	1,2	V
		T _j = 125 °C		0,9	1,1	V
r _{CE}	V _{GE} = 15 V	T _j = 25°C		3,3	4,2	mΩ
		T _j = 125°C		5,2	6	mΩ
V _{CE(sat)}	I _{Cnom} = 300 A, V _{GE} = 15 V	T _j = 25°C _{chiplev.}		2	2,4	V
		T _j = 125°C _{chiplev.}		2,45	2,9	V
C _{ies}	V _{CE} = 25, V _{GE} = 0 V	f = 1 MHz		19,8		nF
C _{oes}				1,1		nF
C _{res}				0,88		nF
Q _G	V _{GE} = -8V...+15V			2500		nC
t _{d(on)}	R _{Gon} = 4 Ω	V _{CC} = 1200V I _C = 300A		330		ns
t _r				55		ns
E _{on}	R _{Goff} = 4 Ω	T _j = 125 °C V _{GE} = ± 15V		170		mJ
t _{d(off)}				880		ns
t _f				145		ns
E _{off}				118		mJ
R _{th(j-c)}	per IGBT				0,075	K/W



SEMITRANS® 3

Trench IGBT Modules

SKM 400GB176D

SKM 400GAL176D

SKM 400GAR176D

Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability, self limiting to $6 \times I_C$


Typical Applications*

- AC inverter drives
- mains 575 - 750 V AC
- Public transport (auxiliary syst.)
- Wind power


Characteristics					
Symbol	Conditions	min.	typ.	max.	Units
Inverse Diode					
$V_F = V_{EC}$	$I_{Fnom} = 300 \text{ A}; V_{GE} = 0 \text{ V}$				
	$T_j = 25 \text{ }^\circ\text{C}_{chiplev.}$		1,7	1,9	V
	$T_j = 125 \text{ }^\circ\text{C}_{chiplev.}$		1,8	2	V
V_{F0}	$T_j = 25 \text{ }^\circ\text{C}$		1,2	1,4	V
	$T_j = 125 \text{ }^\circ\text{C}$		0,9	1,1	V
r_F	$T_j = 25 \text{ }^\circ\text{C}$		1,7	1,7	mΩ
	$T_j = 125 \text{ }^\circ\text{C}$		3	3	mΩ
I_{RRM}	$I_F = 300 \text{ A}$		418		A
Q_{rr}	$di/dt = 5800 \text{ A}/\mu\text{s}$		117		μC
E_{rr}	$V_{GE} = -15 \text{ V}; V_{CC} = 1200 \text{ V}$		78		mJ
$R_{th(j-c)D}$	per diode			0,125	K/W
FWD					
$V_F = V_{EC}$	$I_{Fnom} = 300 \text{ A}; V_{GE} = 0 \text{ V}$				
	$T_j = 25 \text{ }^\circ\text{C}_{chiplev.}$		1,7	1,9	V
	$T_j = 125 \text{ }^\circ\text{C}_{chiplev.}$		1,8	2	V
V_{F0}	$T_j = 25 \text{ }^\circ\text{C}$		1,2	1,4	V
	$T_j = 125 \text{ }^\circ\text{C}$		0,9	1,1	V
r_F	$T_j = 25 \text{ }^\circ\text{C}$		1,7	1,7	V
	$T_j = 125 \text{ }^\circ\text{C}$		3	3	V
I_{RRM}	$I_F = 300 \text{ A}$		418		A
Q_{rr}	$di/dt = 5800 \text{ A}/\mu\text{s}$		117		μC
E_{rr}	$V_{GE} = -15 \text{ V}; V_{CC} = 1200 \text{ V}$		78		mJ
$R_{th(j-c)FD}$	per diode			0,125	K/W
Module					
L_{CE}			15	20	nH
$R_{CC'+EE'}$	res., terminal-chip	$T_{case} = 25 \text{ }^\circ\text{C}$	0,35		mΩ
		$T_{case} = 125 \text{ }^\circ\text{C}$	0,5		mΩ
$R_{th(c-s)}$	per module			0,038	K/W
M_s	to heat sink M6		3	5	Nm
M_t	to terminals M6		2,5	5	Nm
w				325	g

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our staff.



SKM 400GB176D



SEMITRANS® 3

Trench IGBT Modules

SKM 400GB176D
SKM 400GAL176D
SKM 400GAR176D


Features

- Homogeneous Si
- Trench = Trenchgate technology
- $V_{CE(sat)}$ with positive temperature coefficient
- High short circuit capability, self limiting to $6 \times I_C$

Typical Applications*

- AC inverter drives
- mains 575 - 750 V AC
- Public transport (auxiliary syst.)
- Wind power

Z_{th}	Symbol	Conditions	Values	Units
$Z_{th(j-c)I}$				
R_i		$i = 1$	52	mk/W
R_i		$i = 2$	18	mk/W
R_i		$i = 3$	4,6	mk/W
R_i		$i = 4$	0,4	mk/W
τ_{ui}		$i = 1$	0,0569	s
τ_{ui}		$i = 2$	0,0122	s
τ_{ui}		$i = 3$	0,002	s
τ_{ui}		$i = 4$	0,02	s
$Z_{th(j-c)D}$				
R_i		$i = 1$	85	mk/W
R_i		$i = 2$	28	mk/W
R_i		$i = 3$	10,5	mk/W
R_i		$i = 4$	1,5	mk/W
τ_{ui}		$i = 1$	0,054	s
τ_{ui}		$i = 2$	0,0075	s
τ_{ui}		$i = 3$	0,0018	s
τ_{ui}		$i = 4$	0,0002	s






Fig. 1 Typ. output characteristic, inclusive $R_{CC'+EE'}$




Fig. 2 Rated current vs. temperature $I_C = f(T_C)$




Fig. 3 Typ. turn-on /-off energy = $f(I_C)$




Fig. 4 Typ. turn-on /-off energy = $f(R_G)$




Fig. 5 Typ. transfer characteristic












Fig. 6 Typ. gate charge characteristic






Case D 56




GB

Case D56



GAL

Case D57



GAR

Case D58