


# DEVIfoil™ Mirror



Make it easy,  
make it DEVI



An effective system for keeping the mirror completely steam free.  
Fast and easy installation where the self-adhesive side of the heating foil is placed on the back of the mirror.

Low energy consumption and automatic activation when the light is switched on.

## Benefits:

- Fast and easy installation
- Low energy consumption
- Automatic activation

## Standard compliance:

- EN 60335-1 + EN 60335-2-30

## Compliance symbols:



| Type                     | Value                |
|--------------------------|----------------------|
| Nominal voltage          | 230 V~               |
| Output                   | 200 W/m <sup>2</sup> |
| Max. ambient temperature | 80 °C                |
| IP Class                 | IP 44                |
| Protection class         | Class II -           |
| Connection cable length  | 95 cm                |
| Connection muff          | 4 x 31 x 39 mm       |

## Types: DEVIfoil™ Mirror

| Item no. | Type                  | Dimensions   | Wattage | EAN no.       |
|----------|-----------------------|--------------|---------|---------------|
| 62000000 | DEVIfoil™ Mirror 17,5 | 274 x 358 mm | 17,5 W  | 5703466180686 |
| 62000001 | DEVIfoil™ Mirror 40   | 410 x 524 mm | 40,0 W  | 5703466180693 |
| 62000002 | DEVIfoil™ Mirror 70   | 708 x 524 mm | 70,0 W  | 5703466180709 |