

Installation guide

Pressure switch, KP 1, KP 1W, KP 1A, KP 2, KP 4, KP 5, KP 5A, KP 6W, KP 6B, KP 6S, KP 6AW, KP 6AB, KP 6AS, KP 7W, KP 7B, KP 7S



Refrigerants:

R22, R134a, R404A, R407A, R407C, R407F, R410A*) R422B, R422D, R448A, R449A, R452A, R507A, R513A, R717**)

For complete list of approved refrigerants, go to http://products.danfoss.com/all-products/

*) only for KP 6W, KP 6B, KP 6S, KP 6AW, KP 6AB, KP 6AS


**) only for KP 1A, KP 5A, KP 6AW, KP 6AB, KP6 AS

KP 1, KP 2, KP4 KP 5, KP 6, KP 7












Ambient temperatures / Mounting requirements

-25 - 65 °C (PED approved units)




Relative humidity RH: 30 - 98%


Vibrations resistance: 4 g (10 - 1000 Hz)

Connections Danfoss 60-572.11 =12 (¹⁵/₃₂in.) 7/₁₆₋₂₀UNF (1/₄ in SAE flare)



Mounting









P_{test}max.:

KP 1, KP 2: 20 bar p_e (285 psig) KP 2: 12 bar p_e (174 psig) KP 4: 24 bar pe (343 psig) KP 5, KP 7: 35 bar p_e (510 psig) KP 6: 46,5 bar p_e (675 psig)

Туре	Regulation range	PS/MWP	
KP 1	-0.2 – 7.5 bar	245 psig / 17 bar	
KP 1, reset	-0.9 – 7.0 bar	245 psig / 17 bar	
KP 1 W	0.5 – 3.0 bar	245 psig / 17 bar	
KP 2	-0.2 – 5.0 bar	245 psig / 17 bar	
KP 2	-0.2 – 3.5 bar	145 psig / 10 bar	
KP 4	-0.2 – 7.5 bar	312 psig / 21,5 bar	
KP 5	8 – 32 bar	510 psig / 35 bar	
KP 6	8 – 42 bar	675 psig / 46,5 bar	
KP 7	8 – 32 bar	510 psig / 35 bar	


PS/MWP (Maximum Working Pressure)






nfo for UK customers only: Danfoss Ltd., 22 Wycombe End, HP9 1NB, GB















CAUTION:

Disconnect power supply before wiring connections are made or service to avoid possible electrical shock or damage to equipment. Do never touch live parts with your fingers or with any tool.

Contact 1-4 opens on pressure drop



KP 1, KP 2, KP 4



AC 1: 16 A

AC 3: 16 A


AC 15: 10 A

DC 13


12 W
220 V

Short circuit protection: Fuse 16 Amp.

Contact 1-4 opens on pressure drop



KP 1W, KP 1 manual reset




When used acc. to UL regulations




Voltage		FL	LR	Resist.	Pilot
AC	DC	А	Α	load	duty
240	_	8	48	8 A	3A
120	_	16	96	16 A	3A
_	240	_	_	_	12 W

Contact 1-2 opens on pressure rise




KP 5, KP 5A, KP 6, KP 6A, KP 7




Use copper wire only Tightening torque 20 lb. in.

Manual trip function






Manual reset



Туре	Differential	
KP 1, KP 1A	0.7 bar (10 psi)	
KP 5, KP 5A	3 bar (43 psi)	
KP 6B, KP 6S, KP 6AB, KP 6AS, KP 7B, KP 7S	4 bar (58 psi)	

Adjustment







CAUTION:

Only for selected A2L refrigerants: R455A, R454C, R1234yf, R1234ze For complete list of approved A2L refrigerants, go to http://products.danfoss.com/all-products/

Electrical rating

AC-3: 16 A / 250 V AC AC-15: 10 A / 250 V AC

Voltage	Current range	Power factor (cos phi)	Frequency
250V AC	≤ 4.0 A	PF ≥ 0,400	50Hz/60Hz
250V AC	> 4.0 to 6.0 A	PF ≥ 0,594	50Hz/60Hz
250V AC	> 6.0 to 16,0 A	PF ≥ 0,780	50Hz/60Hz

IMPORTANT NOTICE



Safety requirements

- 1. KP pressure switches shall only be employed in the units/systems which comply with the requirements for charge limits and requirements for avoiding ignition sources of IEC 60335-2-24, IEC 60335-2-40, IEC 60335-2-89, ISO 5149, EN378-1 or equivalent.
- 2. Applying the overload on the KPs must be prevented. If by any chance it was damaged, the system / unit shall be stopped and KP shall be replaced as necessary.
- 3. Electrostatic discharge protection and Electrical leakage protection shall be surely implemented by grounding or other measures.
- 4. Only trained personnel are authorized to handle flammable refrigerants systems and may do the installation, maintenance and exchange of the switch by using appropriate tools.
- 5. It is recommended to regularly check the function of KP switch.
- 6. KP pressure switches must be installed in an area with a low risk of mechanical damage.
- 7. Corrosion protection of KP pressure switches must be taken into account when used in a corrosive environment.
- 8. Cables shall not be in contact with sharp edges. The cables shall be connected with adequate stress relieve in order to prevent that pulling forces can be carried thorough the cable to the terminal.
- 9. In the event of pressure pulsation in the system, where switch is connected, these must be effectively dumped to prevent failure of the bellows. The cycle frequency of KP switch shall be kept as low as possible.
- 10. The KP switches shall not be installed in places where high level of vibration is present.

Disclaimer

The user is responsible for ensuring that third parties also comply with this Notice, e.g. in case that the KP switches are supplied to third parties, and e.g. that all installation guides are available with the KP switches during installation. It is required that all conditions of this guide are being met and secured when using KP pressure switches.

Danfoss shall not be responsible for any kind of direct and indirect or consequential damage or loss, including, but not limited to, loss of property, production, loss of profit, human injury arising out of the explosion or fire caused by the flammable nature of refrigerant.

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues descriptions, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material.

Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the product.