


# Proportional load sensing valve - PVG 32

Maximize productivity and machine efficiency

- Pre-compensated design for proportional flow or pressure control with individual port pressure limitation
- Load independent flow up to 130 l/min [34.3 US gal/min] with 400 bar [5800 psi] pressure capability
- Widest range of analog and digital actuator options including mechanical and hydraulic control
- Plug and perform with PLUS+1® electronic components
- Compact, highly configurable ensuring fast time to market

System integration examples for optimized vehicle architecture

- Possible to combine with PVG 120, PVG 100, PVG 16 and HIC to meet application needs at lower system costs
- Options for integrating pilot-operated check valves for zero port leak functionality
- A range of advanced integrated application specific features and options



# 100%

modularity for easy  
and fast machine  
design