

# SKKT 72, SKKH 72, SKKT 72B



## SEMIPACK® 1

### Thyristor / Diode Modules

#### SKKT 72

#### SKKH 72

#### SKKT 72B

#### Features

- Heat transfer through aluminium oxide ceramic isolated metal baseplate
- Hard soldered joints for high reliability
- UL recognized, file no. E 63 532


#### Typical Applications\*

- DC motor control (e. g. for machine tools)
- AC motor soft starters
- Temperature control (e. g. for ovens, chemical processes)
- Professional light dimming (studios, theaters)

1) See the assembly instructions

$I_{TRMS} = 125 \text{ A}$ (maximum value for continuous operation) $I_{TAV} = 70 \text{ A}$ (sin. 180; $T_c = 85^\circ\text{C}$ )				
$V_{RSM}$ V	$V_{RRM}$ ; $V_{DRM}$ V		SKKT 72/12 E	SKKT 72B12 E
1300	1200		SKKT 72/16 E	SKKT 72B16 E
1700	1600		SKKT 72/18 E	SKKH 72/16 E
1900	1800			SKKH 72/18 E

Symbol	Conditions	Values	Units
$I_{TAV}$	sin. 180; $T_c = 85$ (100) $^\circ\text{C}$ ; P3/180; $T_a = 45^\circ\text{C}$ ; B2 / B6	70 (50)	A
$I_D$	P3/180F; $T_a = 35^\circ\text{C}$ ; B2 / B6	62 / 75	A
$I_{RMS}$	P3/180F; $T_a = 35^\circ\text{C}$ ; W1 / W3	115 / 145	A
$I_{TSM}$	$T_{vj} = 25^\circ\text{C}$ ; 10 ms	155 / 3 * 115	A
$i^2t$	$T_{vj} = 125^\circ\text{C}$ ; 10 ms	1600	A
	$T_{vj} = 25^\circ\text{C}$ ; 8,3 ... 10 ms	1450	A
	$T_{vj} = 125^\circ\text{C}$ ; 8,3 ... 10 ms	13000	A <sup>2</sup> s
	$T_{vj} = 125^\circ\text{C}$ ; 8,3 ... 10 ms	10500	A <sup>2</sup> s
$V_T$	$T_{vj} = 25^\circ\text{C}$ ; $I_T = 300 \text{ A}$	max. 1,9	V
$V_{T(TO)}$	$T_{vj} = 125^\circ\text{C}$	max. 0,9	V
$r_T$	$T_{vj} = 125^\circ\text{C}$	max. 3,5	m $\Omega$
$I_{DD}$ ; $I_{RD}$	$T_{vj} = 125^\circ\text{C}$ ; $V_{RD} = V_{RRM}$ ; $V_{DD} = V_{DRM}$	max. 20	mA
$t_{gd}$	$T_{vj} = 25^\circ\text{C}$ ; $I_G = 1 \text{ A}$ ; $dI_G/dt = 1 \text{ A}/\mu\text{s}$	1	$\mu\text{s}$
$t_{gr}$	$V_D = 0,67 * V_{DRM}$	1	$\mu\text{s}$
$(di/dt)_{cr}$	$T_{vj} = 125^\circ\text{C}$	max. 150	A/ $\mu\text{s}$
$(dv/dt)_{cr}$	$T_{vj} = 125^\circ\text{C}$	max. 1000	V/ $\mu\text{s}$
$t_q$	$T_{vj} = 125^\circ\text{C}$ ,	80	$\mu\text{s}$
$I_H$	$T_{vj} = 25^\circ\text{C}$ ; typ. / max.	150 / 250	mA
$I_L$	$T_{vj} = 25^\circ\text{C}$ ; $R_G = 33 \Omega$ ; typ. / max.	300 / 600	mA
$V_{GT}$	$T_{vj} = 25^\circ\text{C}$ ; d.c.	min. 3	V
$I_{GT}$	$T_{vj} = 25^\circ\text{C}$ ; d.c.	min. 150	mA
$V_{GD}$	$T_{vj} = 125^\circ\text{C}$ ; d.c.	max. 0,25	V
$I_{GD}$	$T_{vj} = 125^\circ\text{C}$ ; d.c.	max. 6	mA
$R_{th(j-c)}$	cont.; per thyristor / per module	0,35 / 0,18	K/W
$R_{th(j-c)}$	sin. 180; per thyristor / per module	0,37 / 0,19	K/W
$R_{th(j-c)}$	rec. 120; per thyristor / per module	0,39 / 0,2	K/W
$R_{th(c-s)}$	per thyristor / per module	0,2 / 0,1	K/W
$T_{vj}$		- 40 ... + 125	°C
$T_{stg}$		- 40 ... + 125	°C
$V_{isol}$	a. c. 50 Hz; r.m.s.; 1 s / 1 min.	3600 / 3000	V~
$M_s$	to heatsink	5 ± 15 % <sup>1)</sup>	Nm
$M_t$	to terminals	3 ± 15 %	Nm
$a$		5 * 9,81	m/s <sup>2</sup>
$m$	approx.	95	g
Case	SKKT SKKT ...B SKKH	A 46 A 48 A 47	



# SKKT 72, SKKH 72, SKKT 72B




Fig. 1L Power dissipation per thyristor vs. on-state current




Fig. 1R Power dissipation per thyristor vs. ambient temp.




Fig. 2L Power dissipation per module vs. rms current




Fig. 2R Power dissipation per module vs. case temp.




Fig. 3L Power dissipation of two modules vs. direct current




Fig. 3R Power dissipation of two modules vs. case temp.

# SKKT 72, SKKH 72, SKKT 72B




Fig. 4L Power dissipation of three modules vs. direct and rms current




Fig. 4R Power dissipation of three modules vs. case temp.




Fig. 5 Recovered charge vs. current decrease




Fig. 6 Transient thermal impedance vs. time




Fig. 7 On-state characteristics









Fig. 8 Surge overload current vs. time

# SKKT 72, SKKH 72, SKKT 72B



## IMPORTANT INFORMATION AND WARNINGS

This is an electrostatic discharge sensitive device (ESDS) according to international standard IEC 61340.

\*The specifications of Semikron Danfoss products may not be considered as any guarantee or assurance of product characteristics ("Beschaffenheitsgarantie"). The specifications of Semikron Danfoss products describe only the usual characteristics of Semikron Danfoss products to be expected in typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Resulting from this, application adjustments of any kind may be necessary. Any user of Semikron Danfoss products is responsible for the safety of their applications embedding Semikron Danfoss products and must take adequate safety measures to prevent the applications from causing any physical injury, fire or other problem, also if any Semikron Danfoss product becomes faulty. Any user is responsible for making sure that the application design and realization are compliant with all laws, regulations, norms and standards applicable to the scope of application. Unless otherwise explicitly approved by Semikron Danfoss in a written document signed by authorized representatives of Semikron Danfoss, Semikron Danfoss products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. Semikron Danfoss does not convey any license under its or a third party's patent rights, copyrights, trade secrets or other intellectual property rights, neither does it make any representation or warranty of non-infringement of intellectual property rights of any third party which may arise from a user's applications.