



Gas sensor

DST GS4B / DST GS32

For use in residential applications

Description

Introducing the all-new A2L Gas Sensor, expertly engineered with a sleek, compact design, perfect for residential applications and air conditioning units. This innovative sensor delivers top-tier performance without compromising on space or efficiency. Experience cutting-edge technology in a small package, tailored to meet the demands of modern living.

Our thermal conductivity technology offers rapid and accurate leak detection, min. 15-year lifetime, immunity to poisoning, automated self-calibration, and reliable self-diagnostics to avoid silent failures.

Our unique design is optimized to ensure performance over the lifetime even in harsh application environment as it is robust against condensation, dirt, dust, and UV light. Easy portability and seamless system integration with Modbus.

Our small and light design is compatible with all systems due to our customizable software.

Features & Benefits

- Designed for use with R454B, R32, R454A, R454C and R455A
- Flexible alarm threshold and customizable software
- Patented, robust design
- High IP rating (IP66)
- No field service required

Product details

General data

Sensor specifications (UL 60335-2-40)

Measuring range	0 – 100% LFL
Alarm threshold	9 – 20% LFL
Operating temperature	-40 – 175 °F (-40 – 80 °C)
Intermittent temperature	-40 – 203 °F (-40 – 95 °C)
Storage temperature	-67 – 203 °F (-55 – 95 °C)
Operating pressure	700 – 1200 mbar
Operating humidity	0 – 100% RH with condensation
Enclosure protection (EN 60529)	IP66
Connector protection (EN 60529)	IP69k
Flame rating	UL 94 V – 0

Performance specifications

Accuracy at ambient 15 – 25 °C, 30 – 70%	±2.5% LFL
Accuracy across operating range	±5.0% LFL
Response time	< 15 s
Sensor recovery time	< 5 minutes in clean air
Lifetime	Min. 15-year lifetime – self monitoring
Mitigation recovery timer	0 – 5 minutes (others upon request)
Alarm reset	2.5% LFL hysteresis

Electrical specifications

Output mode ⁽¹⁾	Modbus Specification
Supply voltage	5 V DC ± 10 %
Power consumption (estimated)	1.1 VA max
Digital output	RS485, 120 Ω termination resistor included


⁽¹⁾ Others upon request

Mechanical characteristics

Materials – Enclosure	PA66 25% GF
Materials – Electrical connection	PA66 25% GF
Net weight (depending on the format)	0.03 – 0.04 kg

Dimensions & weights

Dimensions




NOTE:
Dimensions are in mm, unless stated otherwise.

Disclaimer/Information:
Sensor stores diagnostic values for warranty analysis. Data can be provided by returning the product. A service fee may apply.

Connections

Electrical connections

Type code	Standard (5 PIN)
	
Electrical connection, Modbus	Pin1: Supply voltage Pin2: Mod A (Data +) Pin3: Mod B (Data -) Pin4: Earth/Ground Pin5: Not connected
Enclosure IP	IP66 for sensor IP69K for MCON connector

NOTE:
Please check store.danfoss.com to find the correct variant for your requirements.



Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the ‘Declaration of Conformity’. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
EU Declaration	Danfoss EU-UK 073R0000.01	Danfoss	UK RoHS

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.