Proportional Valves

PAR1-16

Proportional Relief Valve, Spool Type, Pilot Operated, Normally Open

210 bar [3000 psi] • 132 l/min [35 US gpm]

DESCRIPTION AND OPERATION

This is a pilot operated, spool type, normally open, proportional relief valve. In the de-energized condition, the pressure setting will be at a minimum. As current is applied to the coil, the pressure setting of the valve will increase proportionally. This valve is ideal for system pressure control where flows may vary.

SCHEMATIC



DIMENSIONS

mm [in]



PERFORMANCE DATA

Rated pressure*	**210 bar [3000 psi]**
Rated flow	**132 l/min [35 US gpm]**
Leakage	130 ml/min [8 in³/min] @ 80% of pressure setting
Pressure Range	7-210 bar [100-3000 psi]
Maximum Hysteresis	10%
Threshold current	0 A
Maximum control current	2.0 A [12 VDC coil] 1.0 A [24 VDC coil]
Coil Options	J series
Weight	0.44 kg [0.98 lb]
Cavity	SDC16-2

*Rated pressure based on NFPA fatigue test standards (at 1 million cycles)

PERFORMANCE CURVES





MODEL CODE

PAR1 - 16 - V - 10 - 0 - 12D - G - J

Seal Option

Code	Seal kit
Omit - Buna - N	565810
V - Viton	889609

Max Pressure Setting

Code x 100 - Pressure setting in psi [100 psi increments within specified Pressure Range]
Pressure Range: 7-210 bar [100-3000 psi]
Example:

Code	Bar	Psi
10	69	[1000 psi]

Housing

Code	Ports	Aluminum
0	No housing	
12T	#12 SAE	566149
4G	1/2" BSP	876716
6G	3/4" BSP	876718
10H	#10 SAE	876717
12H	#12 SAE	566113

* Aluminum bodies are to be used for pressures less than 210 bar [3000 psi].
* Additional housings available

Coil Voltage

00 - No coil, nut included (p/n 565559)
12D - 12 VDC
24D - 24 VDC

Connector Type

Omit - No coil
G - DIN 43650
W - Lead wires
N - Deutsch
Y - AMP JR.

Coil series

Omit- No coil
J- J Series, 23 W