Installation Guide

DEVIreg™ Display Connect

Intelligent electronic timer controlled thermostat with App control







Table of contents

1	Introduction	
2	Standard Compliance	
3	Safety instruction	
4	Installation Guidelines	1
5	User Guide	2
	DEVI Control App:	2
	DEVI Control App User Guide:	2
6	Ecodesign Sheet	3
7	Warranty	3
8	Disposal instruction	4



Introduction

The DEVIreg™ Display Connect is a thermostat for use with electric floor heating, the thermostat has multiple control modes; Floor, Room* and Combined, the thermostat has adaptive timer support, which provides an efficient way of controlling your electric floor heating system.

*reauires special action.

The thermostat is special designed for wall mounted installation in standard EU wall mount boxes, in and on wall, and can be used for controlling total heating as well as comfort heating of the room. The thermostat supports a selection of commonly used frame systems for 55x55 (inner geometry) framing systems.

Among others, the thermostat has the following features:

- Ecodesign LOT20 compliance
- In App setup for specific flooring and room types.
- Support for 55x55 like frame systems.
- Simple knob operation for temp, control and features.
- Bluetooth connectivity on 2.4GHz frequency at a maximum power of 10 dRm
- Access to thermostat via App for settings for easy access, setup, or remote troubleshooting. Firmware update via DEVI Control App.
- Works out of box with default parameters as thermostat.
- Ecodesian class TW(f4)



Make it easy, make it DEVI

2 Standard Compliance

Electrical safety, Electro-Magnetic Compatibility and Radio aspects for this product is covered by the compliance with the following relevant standards:

- EN/IEC 60730-1 (general)
- EN/IEC 60730-2-7 (timer)
- EN/IEC 60730-2-9 (thermostat)
- EN 301 489-1 and EN 301 489-17 (EMC standard for radio equipment operating in the 2,4 GHz band)
- EN 300 328 (Efficient use of radio spectrum for radio equipment operating in the 2,4 GHz band)

SIMPLIFIED EU DECLARATION OF CONFORMITY

Hereby, Danfoss A/S declares that the radio equipment

DEVIreg™ Display Connect is in compliance with Directive 2014/53/EU.

The full Declaration of conformity can be found on

https://assets.danfoss.com/approvals/latest/514081/ID528938029774-0101.pdf

The UK Product Security and Telecommunications Infrastructure (Product Security) Regime

The DEVIreg™ Display Connect thermostat is considered a **UK consumer connectable product** under the Product Security and Telecommunications Infrastructure (Product Security) regime, as it can be indirectly connected



to the internet via a smartphone application, and is intended for use by consumers in the UK

The product complies with the following minimum security requirements as specified in the Product Security and Telecommunications Infrastructure (Security Requirements for Relevant Connectable Products) Regulations 2023, which implement Part 1 of the Product Security and Telecommunications Infrastructure Act 2022:

https://www.legislation.gov.uk/ukpga/2022/46/part/1/enacted

- No universal default passwords: The product does not have any preset or hard-coded passwords.
- Implement a means to manage reports of vulnerabilities: You can report any vulnerabilities by visiting our website: https://www.danfoss.com/en/service-and-support/report-securityvulnerability/
- Provide transparency and support for firmware updates: The product supports firmware updates via the DEVI Control App, which may download updates from the internet and transfer them to the device over Bluetooth. Danfoss provides security updates for at least five years from the date of purchase.

Compliance with EN 18031-1 - Cybersecurity and Data Protection

The DEVIreq™ Display Connect Thermostat complies with EN 18031-1, the European harmonized standard that supports the Radio Equipment Directive (RED) by setting cybersecurity and data protection requirements for wireless communication devices.

To ensure compliance and protect both the device and its users, the following guidelines must be followed:

Make it easy.

make it DEVI

Standard Residential Installation

- Controlled Access: The thermostat is primarily designed for installation in private homes or areas with restricted physical access, where only authorized users (e.g., family members or building staff) can interact with it.
- Secure Mounting: Always install the device on a wall or in a flushmounted electrical box using the provided hardware. This reduces the risk of tampering with physical interfaces like the reset or Bluetooth pairing button.
- Bluetooth Use: Pairing via Bluetooth® Low Energy (BLE) does not require a PIN, but the device enters pairing mode only briefly and within a short range. To reduce risk, perform pairing promptly and in a secure setting.

Installation in Public or Semi-Public Spaces (e.g. Offices, Shared Buildings)

If the DEVIreg™ Display Connect Thermostat is to be installed in areas accessible to the public or multiple users, additional precautions must be taken:

- Enclosure or Housing: Install the thermostat inside a lockable protective cover or within a secure enclosure to prevent unauthorized physical access to the device's buttons and connectors.
- Limited Access to Pairing: Ensure that only authorized personnel can activate the Bluetooth pairing mode. This may require temporarily disabling access to the thermostat during setup or commissioning.



- Network Segmentation: If integrated with a building management or automation system, make sure that communication between devices follows recommended network security practices, such as using isolated VLANs or secured local gateways.
- User Responsibility: In multi-user environments, assign clear responsibility for managing the thermostat (e.g. building maintenance personnel). Ensure all users are aware of how to avoid unintentional changes or unauthorized access.

Ongoing Security Measures

- Firmware Updates: Regularly check for firmware updates via the DEVI Control app and apply them promptly to benefit from the latest security enhancements.
- Limit App Access: Avoid sharing the DEVI Control App login or access with unknown or unauthorized users. Only trusted individuals should be allowed to connect to and control the thermostat.

By following these recommendations, the DEVIreg[™] Display Connect Thermostat can be used securely in both private and shared environments while maintaining compliance with EN 18031-1.



3 Safety instruction

Make sure that the mains power supply to the thermostat is shut off before starting the installation.

Important: When the thermostat is used to control a floor heating element, always use a floor sensor, and never set the maximum floor temperature to more than the manufacturer recommends for the specific flooring type. The device is limited to 35 °C floor temperature, due to compliance requirements. In special cases the limit can be extended to 45 °C floor temperature after the unrecoverable breakout has been performed. Based on the setup in the app the thermostat has maximum temperature limitations imposed based on DEVI recommendations.

- Electrical heating thermostats must always be installed according to local building regulations and wiring rules. Installation must be carried out by an authorized and/or qualified installer.
- The thermostat must be used in a wall mounted installation supplied through an all-pole disconnection switch (fuse).
- Do not expose the thermostat/switch to moisture, water, dust, and excessive heat.
- This thermostat/switch can be used by children aged from 8 years and above and persons with reduced physical, sensory or mental capabilities or lack of experience and knowledge, if they have been given supervision or instruction concerning use of the appliance in a safe way and understand the hazards involved, by a person responsible for their safety.
- Children should be supervised to ensure that they do not play with the thermostat/switch.





- The device is designed for permanent operation.
- Please ensure that the device is protected from unauthorized access.

Instructional video material

To make it easy we show the features and functions of the product in videos that are present on our YouTube channel



4 Installation Guidelines

Follow these guidelines when placing the thermostat.



Install the thermostat in a suitable height on the wall (typical 80 – 170 cm)



Do not place the thermostat on the inner side of a poorly insulated exterior wall.



Install the thermostat more than 50 cm from window and door openings





Do not place the thermostat in a way that it will be exposed to direct sunlight.



The thermostat must not be installed in direct wet areas (Zones 0, 1 and 2). Always follow local regulations regarding IP classes, this doesn't mean that the thermostats can't be installed in bathrooms.



Do not position the floor sensor close to door openings or at places where the sunlight or other heat sources are located in the floor.



Installation steps

Description

- Unpack the thermostat. Make sure all parts are delivered (1 pc. thermostat unit, 1 pc. Power supply, 1 pc. Frame, 1 pc. Frame adapter, 1 pc. Spacer, and 1 pc. wire sensor) along with the instructions written in local official language.
- Place the floor sensor in the Flexpipe and make sure the sensor element is properly fixed inside a Flexpipe. The Flexpipe must guide the sensor cable all the way to the wall/ connection box. DEVI's mats have this product included. sold separately as (140F1114).

Illustration








Description

- The bending radius for the Flexpipe must be more than 50 mm.
- Make sure the floor sensor is located with equal distances between two heating cables (> 2 cm) located at a representative position.
 For thin floor constructions:
- the Flexpipe should be flush with the sub-floor surface, countersink the Flexpipe if possible. For thicker constructions: the Flexpipe including the sensor should be located such that the sensor is exposed to a representative heating level, DEVI recommends that the sensor must be located equidistant between the cables or mat runs.

Illustration







Description

- Ensure that the wiring circuit is disconnected and voltage free, turn off the all-pole disconnection switch (fuse).
- Connect the wires according to the wiring diagram on back of the power supply of the thermostat. Ensure that the terminals are properly fastened and wires are securely connected.
- The screen/PE wire from the electric heating element must be connected to the PE wire from the main power supply using a separate connector.

Illustration








Description

- Fasten the thermostat's power supply to the wall terminal box using screws in minimum 2 of the designated holes on the power supply unit. Notice: place the thermostat according to the "IP" - arrow
- Attach the frame and the Top frame to the thermostat. After that attach the thermostat to the Power supply unit by a softly press until all parts firmly connected.
- 11. Carefully attach the thermostat to the Power supply – take care that the connector pins are not bent.
- After electrical installation is completed, turn on the all-pole disconnect (fuse).
- The thermostat is now ready for use.

Illustration





The thermostat is now ready for use. For scheduling and advanced features, connect to the DEVI Control app.

14. Dism



flathead screwdriver.




Description	Illustration
I. Dismount thermostat front for	Perform steps 11 and 10 carefully in
replacement.	the mentioned order, detachment
	can be done without tools or with a



Connection scheme

DEVIreg™ Display Connect







Technical specifications

220 V- 240V~ 50/60 Hz
0,2 W
16A / 3680W @ 230V Cos Φ = 0.3 max. 1A
NTC 15 kΩ @ 25 °C, 3 m. (default), NTC 2 kΩ @ 25 °C NTC 6.8 kΩ @ 25 °C, NTC 10 kΩ @ 25 °C, NTC 12 kΩ @ 25 °C, NTC 33 kΩ @ 25 °C, NTC 37 kΩ @ 25 °C, NTC 47 kΩ @ 25 °C
PWM - Pulse Width Modulation
4°C - 14°C (default 5°C)
15°C to 35 $^{\circ}\text{C}$ (room) 5°C to 35 $^{\circ}\text{C}$ (45 $^{\circ}\text{C}$ with break out) (floor)
Max: 1 x 4 mm ² or 2 x 2.5 mm ²
75 °C
2 (domestic use)
A
1 B



Storage temperature and conditions	-25 °C to 60 °C, 90% RH non-condensing
Operating temperatures and conditions	0 °C to 35 °C, 90% RH non-condensing
IP class	21
Protection class	Class II - 🗆
Immunity against voltage surges	Over Voltage Category III
Transmission frequency (GHz)	2.400 – 2.4835 GHz
Transmission Power (dBm)	<10 dBm
Color	RAL9016 Polar white
Battery type or Name	Manganese Lithium or Super Capacitor
Dimensions (H/W/D):	85 mm x 85 mm x 20-24 mm (in-wall depth: 22mm)
Weight, net	204 g
Battery back-up time, min.	1 hour

^{*} standard DEVI sensor 140F1091 3m.





5 User Guide

Product interface



* When knob is in temp adjustment mode the thermostat will not run the time schedule program.



	Description
1	In this position the thermostat is not active.
ſΡ	In this position the thermostat is running in schedule mode.
	In this position the thermostat is ready for App configuration/modification.
*	In this position the thermostat is operating in frost protection mode.
	By turning the knob clockwise the temperature will increase.
	り 歩

User interface/ daily use

On the thermostat, the temperature can be directly adjusted using the knob/dial by setting the desired temperature which is shown on the segmented display. This action will disregard any schedule but will still adhere to any set minimum or maximum limitations, which can be configured in the app.

The positions Frost Protection (FP), Timer Schedule (SC), or OFF (Of) can be selected using the knob/dial. Selecting the Frost Protection mode ensures that the frost temperature is maintained; this value can be set between 4-14 °C (default 5 °C) in the app.



Selecting the Timer Schedule/App Communication mode makes the device connectable in the DEVI Control app via Bluetooth 4.2, where temperatures, settings, schedules, limits, and more can be adjusted. The thermostat is connected via Bluetooth to the app when the middle connection indicator is lighting blue.


Selecting the **OFF** mode will disable the thermostat completely. In **OFF** mode, both the app and thermostat will be completely off, with no indication or communication to the app.

To pair the thermostat with the Bluetooth app, DEVI Control, place the thermostat in the Timer Schedule/App Communication mode (SC) and start the pairing process as instructed in the app. After the app initiates communication with the thermostat, the user needs to turn the dial to the manual temperature setting and then back to the Timer Schedule/ App Communication mode (SC) to validate which thermostat the pairing is intended for. The middle connection indicator will blink blue when establishing the connection and will be solid blue once the pairing process is completed.



Indicators

The indicators are shine through and are within the knob of the product. these will light up when needed.



All indicators fade out after a duration (default 20 seconds) unless an error is present. Additionally, indicators will "wake up" upon manual interaction with the thermostat, heating state change, schedule event, app connection or errors/warnings appearing.

Heat indicator



- This indicator lights up and turns **red** when the thermostat switches **on** and delivers current to the electric heating element.

 After some seconds the indicator fades out.
- This indicator lights up and turns green when the thermostat is powered and OK.
 After some seconds the indicator fades out.
- The indicator flashes red when an error is present, this will persist until error is alleviated, heating will not be activated/ activatable.

Data communication



- This indicator flashes **Blue** or **Red** when initiating data communication between the thermostat and communication device unit.
- The indicator flashes as part of the paring process
- The indicator is constant lightning **Blue** or **Red**when communication between the thermostat
 and communication device is present.
- The indicator turns off when communication stops.
- The indicator is Blue when in Bluetooth mode and Red when in Zigbee mode



Schedule



- This indicator lights up white when the built in schedule changes from Non active to active and vice versa. After some seconds, the indicator fades out
- This indicator flashes white when a warning has occurred. The warning will be present until App communication is activated, however the indicator will only flash for a duration (default 20 seconds). Warnings will be displayed in the App.

Default settings and out of the box settings.

The DEVIrea™ Display Connect will have the following settings out of the hox:

Maximum Room temperature 35 °C

Maximum floor temperature: 28 °C

Minimum floor temperature 5 °C

If the thermostat is placed onto the schedule (clock) icon without having the app connected, the temperature is default 21 °C



Factory reset

To perform a factory reset the thermostat needs to be powered and correctly mounted, on the bottom of the device (circled below) is a pin hole, by pressing a sim card ejector tool or similar blunt tool into this pinhole a button will be activated, after 20-30 seconds of activation of this button the thermostat will perform a factory reset. All indicators will flash briefly to inform about successful factory reset.

The thermostat will briefly reboot, please allow for up to 10 seconds for the thermostat to be back to a responsive state.

Performing an factory reset will reset errors and warnings.

Alternatively, the front cover on the thermostat can be removed using the slot on the bottom of the thermostat and the button can be activated with a finger.

The factory reset can only be performed whilst the thermostat is powered.





Make it easy, make it DEVI

Bluetooth <-> Zigbee changeover

To change the communication of the thermostat from Bluetooth to Zigbee or vise versa, the reset button is utilized.

To change over the communication, press the reset button for approximately 5 seconds. Once the middle communication indicator starts blinking purple, release the reset button, after which the thermostat will briefly restart. Please allow up to 10 seconds for the restart. When connecting, the middle connection indicator will light blue if in Bluetooth mode and red when in Zigbee mode.

Zigbee join procedure:

To join the thermostat with the DEVI Connect Zigbee app, a Zigbee gateway is required (DEVI Connect 140F1166).

Follow the instructions in the app to pair the thermostat. When prompted to set the thermostat in pairing mode, briefly press the reset button. The middle connection indicator will start quickly blinking red.

Should the Zigbee system require install code this is placed on the back of the thermostat as a QR code



Breakout

To enable the thermostat to go up to a floor temperature of 45°C, or to use the room only control functionality, a permanent modification must be made, this can invalidate your warranty on the product and connected products.

The higher maximum temperature limit or alternative control mode needs to be set in the app after the action has been performed.

To best perform the action the thermostat unit needs to be dismounted from the power supply, on the back of the thermostat there is a hole as shown below, to perform the breakout the plastic seal in the hole needs to be broken and thereafter the PCB trace needs to be broken. The action is best performed with a flathead screwdriver or similar as shown below.

whilst doing the breakout please take care not to damage any other components on the circuit board.







DEVI Control App:



DEVI Control App User Guide:



REFERENCE TO APP MANUAL

To pair the thermostat with the app, initiate the app and follow the instructions provided in the app.

DEVI Connect App:







App enabled functions

- wizard assisted installation scheduling
 smart preheating (adaptive
- heating)
- thermostat limits adaptation
- control mode configuration
- child lock

- app lock
- warning and error readout
- information export
- help function
- complete overview of data and functions



Warnings and error messages

Warning table

Warning	Description	Reference
W1	Schedule overwritten due to manual dial setting	Set when Schedule is active (Set in App) but dial has been turned to set a manual setpoint
W2	Invalid clock	If time is invalid - less than 2021 or above 2050 or use production date or first time connected to App
W3	Child lock is enable	Will be active if child lock is enable and the user tries to change the setpoint or mode with the potentiometer (or encoder)
W5	Set temperature not achievable	Warning given when the room/floor temperature from schedule or manual setpoint can't be reached within a reasonable time.
W8	Maximum Floor Temperature Limit reached	Set if Maximum Floor Temperature is reached while in Combi Mode while Room Temperature is not at Set point
W10	Temperature set above maximum temperature limit	Set, if maximum temperature is lower than the current temperature knob/potentiometer is pointing at. Like Max set to 25°C and knob is set to 27°C





Error table

Error type	No	Description	Solution	Need restart
Floor Sensor disconnected	E1	Connection to sensor is lost	Contact installer or local Danfoss service	The thermostat requires a restart to operate again
Floor Sensor short- circuited	E2	Sensor Contact short- installer or circuited local Danfoss service		The thermostat requires a restart to operate again
Thermostat overheated	E3	Thermostat is overheat- ed, heating is turned off.	Wait until thermostat cools down	The thermostat needs no restart but will start heating when the temperature is lowered
Room sensor disconnected	E4	Room tem- perature sensor value too low.	Contact installer or local Danfoss service	
Room sensor short- circuited	E5	Room tem- perature sensor value too high.	Contact installer or local Danfoss service	



Error type	No	Description	Solution	Need restart
Unrecover- able error, Power supply	E6	Power supply is detected as defective	Contact installer or local Danfoss service	
Potentiom- eter / dial error	E9	Potenti- ometer is detected as defective	Contact installer or local Danfoss service	The potentiometer is reading a value that is outside of the given range
Invalid com- munication	E10	Bluetooth communi- cation error	Retry / Contact installer or local Danfoss service	Bluetooth communication has encountered an unexpected / faulty command
Unrecover- able error	E11	Unrecover- able error	Contact installer or local Danfoss service	

Factory reset will reset all errors and warnings.







6 **Ecodesign Sheet**

To comply with Ecodesign regulations for electric local space heaters 2024/1103 the following table is to be filled in with the specifics of the heating system. Herein the thermostat information for this specific product is prefilled. please fill any/all blank slots.

Information requirements for electric local space heaters

Danfoss A/S, Nordborgvej 81,	Danfoss A/S, Nordborgvej 81,
6430 Nordborg, Denmark	6430 Nordborg, Denmark

Model identifier(s): DEVIrea™ Display Connect

Woder definition(3). Deviney Display connect								
Item		Symbol	Value	Unit	Item			
Power consumpt			Type (select	one)				
In off mode	P _o	0,2	w		single stage heat output and no room temperature control			
In standby mode	P_{sm}	0,2	w	stages, no ro	two or more manual stages, no room temperature control			
In idle mode	P_{idle}	0,6	w	mechanic thermostat room temperature control		no		
In networked standby	P_{nsm}	0,21	w	electronic room temperature control		no		
Standby mode with display of information or status		no		electronic roo temperature day timer		no		

electronic room temperature control plus week timer	yes
Other control options (mu selections possible)	ltiple
presence detection	no
open window detection	no
distance control option	yes*
adaptive start control	yes
working time limitation	no
black bulb sensor	no
self-learning functionality	no
control accuracy	no

^{*}requires zigbee gateway (DEVI Connect 140F1166)





Control function codes

		Code of tem- perature control (TC)	Control functions								
	Single stage, no tempera- ture control	NC	f1	f2	f3	f4	f5	f6	f7	f8	
	Two or more manual stages, no room temperature control	TX									
Type of	Mechanic thermostat room temperature control	TM									
temperature control	Electronic room temperature control	TE									
	Electronic room temperature control plus day timer	TD									
	Electronic room temperature control plus week timer	TW									
	Presence detection		1								
	Open window detection			2							
	Distance control option				3						
	Adaptive start control					4					
Control	Working time limitation						5				
functions	Black bulb sensor							6			
	Self-learning functionality								7		
	Control accuracy with CA<2 Kelvin and CSD<2 Kelvin									8	

This product contains TW(f4) control functions

7 Warranty



A 5-year product warranty is valid for:

thermostats incl. DEVIreg[™] Display Connect.

Make it easy

make it DEVI

Should you, against all expectations, experience a problem with your DEVI product, you will find that Danfoss offers DEVIwarranty valid from the date of purchase that was no later than 5 years from production date on the following conditions:

During the warranty period Danfoss shall offer a new comparable product or repair the product if the product is found to be faulty by reason of defective design, materials or workmanship. The decision to either repair or replace will be solely at the discretion of Danfoss.

The decision to either repair or replace will be solely at the discretion of Danfoss. Danfoss shall not be liable for any consequential or incidental damages including, but not limited to, damages to property or extra utility expenses. No extension of the warranty period following repairs undertaken is granted.



The warranty shall be valid only if the WARRANTY CERTIFICATE is completed correctly and in accordance with the instructions, the fault is submitted to the installer or the seller without undue delay and proof of purchase is provided. Please note that the WARRANTY CERTIFICATE must be filled in, stamped and signed by the authorized installer performing the installation (Installation date must be indicated). After the installation is performed, store and keep the WARRANTY CERTIFICATE and purchase documents (invoice, receipt or similar) during the whole warranty period.

DEVIwarranty shall not cover any damage caused by incorrect conditions of use, incorrect installation or if installation has been carried out by non-authorized electricians. All work will be invoiced in full if Danfoss is required to inspect or repair faults that have arisen as a result of any of the above. The DEVIwarranty shall not extend to products which have not been paid in full. Danfoss will, at all times, provide a rapid and effective response to all complaints and inquiries from our customers.

The warranty explicitly excludes all claims exceeding the above conditions. For full warranty text visit www.devi.com. devi.danfoss.com/en/warranty/

Make it easy, make it DEVI

Stamp

WARRANTY CERTIFICATE

ted to:	
nty is grante	
JEVIwarra	ess
l e l	٩ddr

Purchase date

Serial number of the product Product Art. No.

*Connected output [W] Installation Date & Signature

Connection Date & Signature

*Not mandatory





8 Disposal instruction



This symbol on the product indicates that it may not be disposed of as household waste.

It must be handed over to the applicable take-back scheme for the recycling of electrical and electronic equipment.

- Dispose of the product through channels provided for this purpose.
- Comply with all local and currently applicable laws and regulations.







42 INSTALLATION GUIDE DEVIreg™ Display Connect Make it easy, make it DEVI





Danfoss A/S Nordborgvej 81 6430 Nordborg Denmark

Danfoss A/S

DEVI • devi.com • +45 7488 8500 • E-Mail: EH@danfoss.com

Danfoss can accept no responsibility for possible errors in catalogues, brochures and other printed material. Danfoss reserves the right to after its products without notice. This also applies to products already on order provided that such alterations can be made without subsequential changes being necessary in specifications already agreed. All trademarks in this material are property of the respective companies. DEVI and all DEVI logotypes are trademarks of Danfoss A/S. All rights reserved.

140F1162 DEVIregTM Display Connect

Connectable Room thermostat Load 16 A/3680 W 220-240V~

@ 230V ~ 50/60Hz 0T35°C

Danfoss Ltd. 22





