

SAFETY DATA SHEET



Date Prepared : 3/5/2015
SDS No : 0114

ZEROL® 150T

1. PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: ZEROL® 150T
PRODUCT DESCRIPTION: Synthetic Alkylate

MANUFACTURER

Shrieve Chemical Products
1755 Woodstead Ct
The Woodlands, TX 77380

Emergency Contact: Audris King
Emergency Phone: (800)424-9300
Customer Service: (800) 367-4226

24 HR. EMERGENCY TELEPHONE NUMBERS

CHEMTREC: 800-424-9300

2. HAZARDS IDENTIFICATION

GHS LABEL

This product is not classified as hazardous according to 29CFR 1910.1200.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Chemical Name	Wt.%	CAS
Synthetic Alkylate(s)	*	Proprietary
Lubricant Additive	*	Proprietary

COMMENTS: Ingredients and composition are withheld as trade secret in accordance with 29CFR1910.1200(i).

4. FIRST AID MEASURES

EYES: Immediately flush eyes with plenty of water. Get medical attention, if irritation persists.

SKIN: Immediately wash skin with soap and plenty of water. Remove contaminated clothing. Get medical attention if symptoms occur. Wash clothing before reuse.

INGESTION: Rinse mouth with water. Drink plenty of water. Do not induce vomiting. Get immediate medical attention if you feel unwell. Never give anything by mouth to an unconscious person.

INHALATION: Remove to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Get immediate medical attention.

SIGNS AND SYMPTOMS OF OVEREXPOSURE

EYES: May cause eye irritation.

SKIN: May cause skin irritation.

5. FIRE FIGHTING MEASURES

FLAMMABLE CLASS: Non-flammable.

GENERAL HAZARD: Do NOT use water stream or water jet.

EXTINGUISHING MEDIA: Dry Chemical, CO₂, Foam, Fog or Water Spray.

HAZARDOUS COMBUSTION PRODUCTS: Oxides of carbon.

OTHER CONSIDERATIONS: Keep adjacent containers cool with water spray.

FIRE FIGHTING PROCEDURES: As in any fire, wear self-contained breathing apparatus pressure-demand, (MSHA/NIOSH approved or equivalent) and full protective gear.

FIRE FIGHTING EQUIPMENT: In case of fire wear a full-face positive pressure self contained breathing apparatus and protective suit.

6. ACCIDENTAL RELEASE MEASURES

SMALL SPILL: Contain and soak up spill with non-combustible absorbent material. Dampen and scoop spilled material into suitable containers, seal and label. Avoid mixing spilled material with other chemicals or debris. Avoid runoff into storm sewers and ditches which lead to waterways.

LARGE SPILL: SHUT OFF LEAK IF SAFE TO DO SO. Remove all possible sources of ignition. Contain spill with inert, absorbent material. Reclaim into recovery or salvage drums or vacuum truck for proper disposal. Treat residues as small spills.

ENVIRONMENTAL PRECAUTIONS

WATER SPILL: Prevent material from entering drains or watercourses using sand, earth or other appropriate barriers.

LAND SPILL: Prevent contamination of the soil.

GENERAL PROCEDURES: Avoid contact with skin or eyes. Avoid contact with spilled materials. Use appropriate personal protective equipment. Ensure adequate ventilation.

SPECIAL PROTECTIVE EQUIPMENT: Use protective equipment recommended in Section 8.

7. HANDLING AND STORAGE

GENERAL PROCEDURES: Handle in accordance with good industrial hygiene and safety practices.

HANDLING: Avoid breathing (dust, vapor, mist, gas). Avoid contact with skin and eyes. Ground and bond containers when transferring material. Wash thoroughly after handling.

STORAGE: Keep container tightly closed in a dry, well-ventilated place away from heat, open flame, or sources of ignition. Store away from incompatible materials (see section 10).

STORAGE TEMPERATURE: Ambient.

LOADING TEMPERATURE: Ambient

ELECTROSTATIC ACCUMULATION HAZARD: Bond and ground during loading, unloading and transferring material to prevent electrostatic accumulation.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

ENGINEERING CONTROLS: Provide adequate ventilation. Eye washes and showers for emergency use.

PERSONAL PROTECTIVE EQUIPMENT

EYES AND FACE: Wear safety glasses with side shields (or goggles) or a face shield.

SKIN: Use protective clothing, sleeves, boots, face protection and chemical resistant gloves. Use extra precautions when working with heated materials.

RESPIRATORY: Use appropriate protection if there is risk of breathing the mists or vapors or heated materials. Use suitable respiratory equipment if risk of insufficient ventilation.

PROTECTIVE CLOTHING: Wear protective clothing appropriate to the risk of exposure.

WORK HYGIENIC PRACTICES: Wash hands, forearms and face before eating, drinking, smoking and using the restroom. Launder contaminated clothing before re-use.

9. PHYSICAL AND CHEMICAL PROPERTIES

PHYSICAL STATE: Liquid

APPEARANCE: Clear colorless liquid

PHYSICAL STATE COMMENTS: Clear, bright, viscous.

pH: Not Available

FLASH POINT AND METHOD: > 155°C COC-ASTM D-92

AUTOIGNITION TEMPERATURE: Not Available

VAPOR PRESSURE: Not Available

BOILING POINT: Not Available

POUR POINT: < -35°C

THERMAL DECOMPOSITION: Not Available

SPECIFIC GRAVITY: 0.87 at 15°C

VISCOSITY #1: 30 cSt at 40°C

10. STABILITY AND REACTIVITY

HAZARDOUS POLYMERIZATION: None

STABILITY: Stable under normal conditions.

CONDITIONS TO AVOID: Excessive heat, sparks or open flames.

POSSIBILITY OF HAZARDOUS REACTIONS: None Expected.

HAZARDOUS DECOMPOSITION PRODUCTS: Under normal conditions, no hazardous decomposition products should be produced.

INCOMPATIBLE MATERIALS: Strong oxidizers.

11. TOXICOLOGICAL INFORMATION

ACUTE

DERMAL LD₅₀: > 2000 mg/kg

ORAL LD₅₀: > 2000 mg/kg

EYE EFFECTS: Minimal irritation.

SKIN EFFECTS: Minimal irritation.

CARCINOGENICITY

Notes: Contains no ingredient listed as a carcinogen.

REPEATED DOSE EFFECTS: None Expected.

IRRITATION: Not a primary irritant.

SENSITIZATION: None Expected.

REPRODUCTIVE EFFECTS: None Expected.

MUTAGENICITY: None Expected.

12. ECOLOGICAL INFORMATION

ENVIRONMENTAL DATA: Not classified as an environmental hazard.

ECOTOXICOLOGICAL INFORMATION: This product is not expected to be toxic to aquatic life.

BIOACCUMULATION/ACCUMULATION: Expected to have a very slow rate of bioaccumulation.

DISTRIBUTION: Insoluble in water. Adsorbs to soil and has low mobility.

CHEMICAL FATE INFORMATION: Expected to be partially or slowly biodegradable.

13. DISPOSAL CONSIDERATIONS

DISPOSAL METHOD: Dispose of contents/container to a licensed contractor or facility in accordance with local, state and federal regulations.

PRODUCT DISPOSAL: Materials are suitable for burning or disposal at a supervised incineration facility.

EMPTY CONTAINER: Clean container thoroughly and dispose to licensed disposal contractor. Do not weld, cut, or braze empty containers, or allow product residue to come in contact with other sources of ignition as they may contain residue which could ignite.

14. TRANSPORT INFORMATION

DOT (DEPARTMENT OF TRANSPORTATION)

PROPER SHIPPING NAME: Not regulated for Transport

ROAD AND RAIL (ADR/RID)

PROPER SHIPPING NAME: Not regulated for Transport

AIR (ICAO/IATA)

SHIPPING NAME: Not regulated for Transport
VESSEL (IMO/IMDG)

SHIPPING NAME: Not regulated for Transport

15. REGULATORY INFORMATION

UNITED STATES

SARA TITLE III (SUPERFUND AMENDMENTS AND REAUTHORIZATION ACT)

311/312 HAZARD CATEGORIES: Not hazardous.

313 REPORTABLE INGREDIENTS: No ingredients at detectable levels.

TSCA (TOXIC SUBSTANCE CONTROL ACT)

TSCA STATUS: All components listed or exempt.

CANADA

DOMESTIC SUBSTANCE LIST (INVENTORY): All components are listed or exempt.

16. OTHER INFORMATION

REASON FOR ISSUE: Updated to GHS Format with GHS classification


APPROVED BY: Audris King **TITLE:** HS&E Manager

PREPARED BY: Britton Webb **Date Prepared:** 3/5/2015

HMIS RATING

HEALTH	<input type="text"/>	1
FLAMMABILITY	<input type="text"/>	1
PHYSICAL HAZARD	<input type="text"/>	0
PERSONAL PROTECTION	<input type="text"/>	

NFPA CODES



MANUFACTURER DISCLAIMER: The information is based on the data of which we are aware and is believed to be correct as of the data hereof. Since the information contained herein may be applied under conditions beyond our control and with which we may be unfamiliar and since data made available subsequent to the date hereof may suggest modification of the information, we do not assume any responsibility for the result of its use. This information is furnished upon condition that the person receiving it shall make his own determination of the suitability of the material for his particular purpose.