



Energy meter EM530 (3-phase energy meter)

Danfoss EM530: Energy analyser for two and three phase systems

Description

Danfoss EM530 is an energy analyser connected through 5 A current transformers, for two and three phase systems up to 415 V LL. In addition to a digital input, the unit is equipped with Modbus RTU communication port.

Features & benefits

- System and phase variables (V L-L, V L-N, A, W/var, VA, PF, Hz)
- Displaying of the consumed active energy with a resolution of 0.001 kWh
- The frequency value is available via Modbus, with a resolution of 0.001 Hz
- Average value calculation (dmd) for current and power (kW/kVA)
- Streamlined user interface featuring 3 mechanical buttons
- Modbus RTU RS485 (data refresh every 100 ms) allowing integration into AK-SM 800A
- Continuous sampling of each voltage and current
- Backlit LCD display

Additional features:

- **AK-SM 800A** integrated
- **Enhanced readability:** The backlit display ensures perfect visibility even in low light. The different size of the digits preceding and following the dot makes the displayed values easier to read, while the essential style of the units of measure allows you to readily understand the available variables.
- **Easy browsing:** Page configuration and browsing are very intuitive, thanks to the user interface with 3 mechanical keys. The slideshow function automatically displays the desired measurements in sequence, without having to use the keyboard; the page filter allows you to hide the unnecessary information.
- **Quick configuration:** The configuration wizard which runs when the system is started up for the first time allows you to commission the unit without errors in a matter of seconds.
- **Accurate measuring:** Danfoss EM530 complies with the precision international standard IEC/EN62053-21.
- **Flexible installation:** It can be installed in two-phase, three-phase with neutral, three-phase without neutral, and wild-leg three-phase low-voltage systems.

Applications

Danfoss EM530 can be installed in any low-voltage switchboard, to monitor the energy consumption, the main electrical variables and the harmonic distortion. Compatible with any current transformer with 5 A secondary current, it can be installed in systems with rated current up to 10 kA, even in retrofit applications if used with openable transformers.

If used to monitor a single machine, it provides all the main electrical variables to identify any possible malfunction in its early stage and can correlate the energy consumption with the hours of operation, to plan maintenance and prevent failures. The partial meter reset function, easily implementable by means of a digital input, allows you to monitor each individual machine cycle.

Thanks to the measurement refresh time and to the high resolution of the variables available through a Modbus RTU communication module, it can also be used as data source for control actions, such as avoiding feeding energy into the electricity grid in a photovoltaic joint installation with energy storage.

In combination with energy monitoring it allows you to build a scalable and flexible system to monitor the energy efficiency of buildings and equipment.

Product code numbers

Product name	Type	Supply voltage [V] AC [min]	Supply voltage [V] AC [max]	Code number
Energy meter	Energy Meter	120	240	080Z2130

Accessories code numbers



080Z2136

Electron. control accessories, CTA-6X SPLIT CORE CURRENT TRANSFOR. 600A

CTA-6X SPLIT CORE CURRENT TRANSFOR.
600A, Packing format: Single pack, Quantity
per packing format: 1

Related products

080Z2130



080Z2134

Electron. control accessories, CTA-6X SPLIT CORE CURRENT TRANSFOR. 400A

CTA-6X SPLIT CORE CURRENT TRANSFOR.
400A, Packing format: Single pack, Quantity
per packing format: 1

Related products

080Z2130



080Z2132

Electron. control accessories, CTD-2X BUS-BAR CURRENT TRANSFORMER 100A

CTD-2X BUS-BAR CURRENT TRANSFORMER
100A, Packing format: Single pack, Quantity
per packing format: 1

Related products

080Z2130



080Z2133

Electron. control accessories, CTD-3X BUS-BAR CURRENT TRANSFORMER 200A

CTD-3X BUS-BAR CURRENT TRANSFORMER
200A, Packing format: Single pack, Quantity
per packing format: 1

Related products

080Z2130



080Z2135

Electron. control accessories, CTA-5X SPLIT CORE CURRENT TRANSFOR. 250A

CTA-5X SPLIT CORE CURRENT TRANSFOR.
250A, Packing format: Single pack, Quantity
per packing format: 1

Related products

080Z2130

Functions

- Measure active, reactive and apparent energy
- Measure the main electrical variables
- Measure the load run hours and of the analyser
- Measure the total harmonic distortion (THD) of current and voltages
- Transmit data to other systems through Modbus RTU
- Visualize the measured variables on the display

Data communication

Communication ports

Table: Modbus RTU

Feature	Description
Protocol	Modbus RTU
Devices on the same bus	Max. 247 (1/8 unit load)
Communication type	Multidrop, bidirectional
Connection type	2 wires
Configuration parameters	Modbus address (1 – 247) Baud rate (9.6/19.2/38.4/115.2 kbps) Parity (None/Even)
Refresh time	≤ 100 ms
Configuration mode	Via keypad

Communication

Figure: RS485 port






Figure: Last device on RS485



Note: In AK-SM 800A communication the Modbus levels are A+ and B-


The plus and minus symbols should be considered, not the letters A and B, that means within in the ADAP-KOOL® Refrigeration control systems, Modbus A+ of the AK-SM 800A must be connected to B+ of the energy meter and Modbus B- of the AK-SM 800A must be connected to A- of the energy meter (please refer to Communication Design Guide [AJ430138910308en-000101](#)).

Figure: Modbus

Product details

General data

Layout

Figure: Front and Back

A	Voltage inputs
B	Display
C	LED
D	Browsing and configuration buttons
E	Digital input and communication connections
F	Current inputs

A	DIN rail mounting bracket
----------	---------------------------

General specifications

Table: General specifications

Features	Description
Material	Housing: PBT Transparent cover: Polycarbonate
Protection degree	Front: IP40 Terminals: IP20
Terminals	Voltage inputs: min. 0.2 mm ² , max. 2.5 mm ² , 0.45 Nm max. Current inputs: min. 0.2 mm ² , max. 2.5 mm ² , 0.45 Nm max. Inputs, outputs and communication: min. 0.2 mm ² , max. 1.5 mm ² , 0.4 Nm max.
Overvoltage category	Cat. III
Pollution degree	2
Mounting	DIN rail
Weight	280 g (packaging included)
Dimensions	3-DIN modules

Table: Input and output insulation

Type	Measurement inputs	Digital input	RS485 serial port
Measurement inputs	–	Double/Reinforced	Double/Reinforced
Digital input	Double/Reinforced	–	None
RS485 serial port	Double/Reinforced	None	–

According to: EN 61010-1. Overvoltage category III. Pollution degree 2.

Table: Electrical specifications

Features	Description
Electrical system	
Managed electrical system	Two-phase (3-wire) Three-phase with neutral (4-wire) Three-phase without neutral (3-wire) Wild leg system (three-phase, four-wire delta)
Voltage inputs	
Voltage connection	Direct
Rated voltage L-N (from Un min. to Un max.)	120 – 240 V
Rated voltage L-L (from Un min. to Un max.)	208 – 415 V
Voltage tolerance	0.8 – 1.15 Un
Overload	Continuous: 1.5 Un max.
Input impedance	Refer to <i>Table: Power supply</i>
Frequency	45 – 65 Hz
Current inputs	
Current connection	Via CT
CT transformation ratio	2000 max.
Rated current (In)	5 A
Minimum current (Imin.)	0.05 A
Maximum current (Imax.)	6 A
Start-up current (Ist)	10 mA
Overload	For 500 ms: 20 Imax. (120 A)

Input impedance	< 0.9 VA
Crest factor	3
Measurement type	By means of internal shunts

Note: Danfoss EM530 can also be installed in a wild leg system (three phases, four delta wires), where one of the phase-neutral voltages is higher than the other two.

Figure: Wild leg system




Table: Power supply

Features	Description
Type	Self power supply
Consumption	< 1.3 W / 2.6 VA
Frequency	50/60 Hz

Table: Measurements

Features	Description
Method	TRMS measurements of distorted waveforms

Available measurements

Table: Active energy

Active energy	Unit	System	Phase
Imported (+) total	kWh+	■	■
Imported (+) partial	kWh+	■	-
Exported (-) total	kWh-	■	-
Exported (-) partial	kWh-	■	-
By tariff	kWh+	■	-

Table: Reactive energy

Reactive energy	Unit	System	Phase
Imported (+) total	kvarh+	■	-
Imported (+) partial	kvarh+	■	-
Exported (-) total	kvarh-	■	-
Exported (-) partial	kvarh-	■	-

Table: Apparent energy

Apparent energy	Unit	System	Phase
Total	kVAh	■	-
Partial	kVAh	■	-

Table: Run hour meter

Run hour meter	Unit	System	Phase
Total (kWh+)	hh:mm	■	-
Partial (kWh+)	hh:mm	■	-
Total (kWh-)	hh:mm-	■	-
Partial (kWh-)	hh:mm-	■	-
Total ON time	hh:mm	■	-

Table: Electrical variable

Electrical variable	Unit	System	Phase
Voltage L-N	V	■	■
Voltage L-L	V	■	■
Current	A	■	■
• DMD	A	-	■
• DMD max	A	-	■
Neutral current	A	■	-
Active power	W	■	■
• DMD	W	■	-
• DMD max	W	■	-
Apparent power	VA	■	■
• DMD	VA	■	-
• DMD max	VA	■	-
Reactive power	Var	■	■
Power factor	PF	■	■
Frequency	Hz	■	-
THD current ⁽¹⁾	THD A %	-	■
THD voltage L-N ⁽¹⁾	THD L-N %	-	■
THD voltage L-L ⁽¹⁾	THD L-L %	-	■

(1) Up to 15th harmonic

Note: The available variables depend on the type of system set. All the variables calculated by the meter are referred to the primary current of the current transformer.

Energy metering

Energy metering depends on the measurement type you choose.

A measurement

Easy connection function: irrespective of the current direction, the power always has a plus sign and contributes to increase the positive energy meter. The negative energy meter is not available.

B measurement

For each measuring time interval, the individual phase energies with a plus sign are summed to increase the positive energy meter (kWh+), while the others increase the negative one (kWh-).

Example:

P L1 = +2 kW, P L2 = +2 kW, P L3 = -3 kW

Integration time = 1 hour

kWh+ = $(2+2) \times 1 \text{ h} = 4 \text{ kWh}$

kWh- = $3 \times 1 \text{ h} = 3 \text{ kWh}$

C measurement

For every measuring interval time, the energies of the single phases are summed; according to the sign of the result, the positive (kWh+) or negative totalizer (kWh-) is increased.

Example:

P L1 = +2 kW, P L2 = +2 kW, P L3 = -3 kW

Integration time = 1 hour

+kWh = $(+2+2-3) \times 1 \text{ h} = (+1) \times 1 \text{ h} = 1 \text{ kWh}$

-kWh = 0 kWh

Measurement accuracy

Table: Current

From 0.05 In to I _{max} .	±0.3% rdg
From 0.01 In to 0.05 In	±0.6% rdg

Table: Phase-phase voltage

From U _n min. -20% to U _n max. +15%	±0.2% rdg
---	-----------

Table: Phase-neutral voltage

From U _n min. -20% to U _n max. +15%	±0.2% rdg
---	-----------

Table: Active and apparent power

From 0.05 In to I _{max} . (PF = 1)	±0.5% rdg
From 0.01 In to 0.05 In (PF = 1)	±1% rdg
From 0.1 In to I _{max} . (PF = 0.5 L – 0.8 C)	±0.6% rdg
From 0.02 In to 0.1 In (PF = 0.5 L – 0.8 C)	±1% rdg
Active energy	Class 0.5 S EN 62053-22
Reactive energy	Class 2 (EN62053-23)

Table: Reactive power

From 0.1 In to I _{max} . ($\sin\phi$ 0.5 L – 0.5 C)	±2% rdg
From 0.05 In to I _{max} . ($\sin\phi$ = 1)	
From 0.05 In to 0.1 In ($\sin\phi$ = 0.5 L – 0.5 C)	±2.5% rdg
From 0.02 In to 0.05 In (PF = 1)	
Active energy	Class 0.5 S EN 62053-22
Reactive energy	Class 2 (EN62053-23)

Table: Frequency

45 – 65 Hz	± 0.1% rdg
------------	------------

Measurement resolution

Table: Measurement resolution

Variable	Display resolution	Resolution by serial communication
Energy		0.001 kWh/kvarh/kVAh
Single phase and tariff energy	0.01 kWh	0.001 kWh
Power	0.01 kW/kvar/kVA	0.1 W/var/VA
Current ⁽¹⁾	0.01 A	0.001 A
Voltage		0.1 V
Frequency	0.01 Hz	0.001 Hz
THD		0.01 %
Power factor	0.01	0.001

(1) Value referred to CT ratio = 1

Display

Table: Display

Feature	Description
Type	Segments
Refresh time	500 ms
Description	Backlit LCD
Variable readout	Instantaneous: 5+1 dgt or 5+2 dgt Power factor: 1+2 dgt Energy: 8+3 dgt

Table: LED

Feature	Description	
Front	Red. pulse weight: proportional to energy consumption and depending on the CT ratio (16 Hz maximum frequency)	
	Weight (kWh per pulse)	CT ratio
	0.001	≤ 7
	0.01	7.1 – 70
	0.1	70.1 – 700
	1	700.1 – 2000

Digital inputs

Table: Digital inputs

Feature	Description
Connection type	Screw terminals
Number of inputs	1
Type	Free contact
Function	Remote status Tariff management Partial meter start/pause Partial meter reset
Features	Open contact voltage: 5 V DC +/- 5% Closed contact current: 5 mA max. Input impedance: 11.6 kΩ Open contact resistance: ≥ 25 kΩ Closed contact resistance: ≤ 840 Ω Maximum voltage applicable with no damages: 30 V AC
Configuration parameters	Input function
Configuration mode	Via keypad


Performance and environmental conditions

Table: Environmental specifications

Features	Description
Operating temperature	-25 – +55 °C / -13 – +131 °F
Storage temperature	-25 – +70 °C / -13 – +158 °F
Electromechanical environmental condition	E2
Mechanical environmental condition	M2


Note: R.H. < 90% non-condensing @ 40 °C / 104 °F.

Dimensions




Connections


Three-phase with neutral (4-wire)




Three-phase without neutral (3-wire)




Three-phase without neutral (3-wire)




Two-phase system with neutral (3-wire)



Solid core current transformer wiring diagram




Split core current transformer wiring diagram



Digital inputs

Figure: Input



Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Table: Certificates, declarations, and approvals

Directives	Standards	Mark	Country
<ul style="list-style-type: none"> 2014/35/EU (LVT - Low Voltage) 2014/30/EU (EMC - Electro Magnetic Compatibility) 2011/65/EU (Electric-electronic equipment hazardous substances) IEC/EN61557-12 PMD performance measuring and monitoring device compliant 	<ul style="list-style-type: none"> EN 62052-11: Electromagnetic Compatibility (EMC) - emissions and immunity Electrical safety: EN 61010-1 Metrology: EN62053-21, EN62053-23 	CE UKCA	EU UK
cULus UL 61010		UL listing	NAM (US and Canada)

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.