


DEVifoil™ Mirror

DEVI 
by Danfoss

Make it easy,
make it DEVI



An effective system for keeping the mirror completely steam free. Fast and easy installation where the self-adhesive side of the heating foil is placed on the back of the mirror.

Low energy consumption and automatic activation when the light is switched on.

Benefits:


- Fast and easy installation
- Low energy consumption
- Automatic activation

Standard compliance:

- EN 60335-1 + EN 60335-2-30

Compliance symbols:



Type	Value
Nominal voltage	230 V~
Output	200 W/m ²
Max. ambient temperature	80 °C
IP Class	IP 44
Protection class	Class II - 
Connection cable length	95 cm
Connection muff	4 x 31 x 39 mm

Types: DEVifoil™ Mirror

Item no.	Type	Dimensions	Wattage	EAN no.
62000000	DEVifoil™ Mirror 17,5	274 x 358 mm	17,5 W	5703466180686
62000001	DEVifoil™ Mirror 40	410 x 524 mm	40,0 W	5703466180693
62000002	DEVifoil™ Mirror 70	708 x 524 mm	70,0 W	5703466180709