



Manual balancing

PFM 1000

Description

Using the differential pressure measured by the measuring component in the system, PFM 1000 calculates the flow that runs through the component (balancing valve or measuring orifice). The application corrects the calculated flow also for anti-freeze mixes in cooling systems. The flow can be measured in all branches of the whole hydraulic system and the whole system can be balanced. The PFM 1000 has been designed to create hydraulic balance in heating, cooling and domestic hot water systems. It enables measuring of static pressure, differential pressure and flow. The main pressure sensor is extremely robust with a sturdy frame. Inside the pressure sensor is a differential pressure gauge with an integrated true differential pressure sensor for accurate digital data processing. Connectivity between measuring unit and smartphone is wireless via Bluetooth. PFM1000 can be connected to ANDROID and iOS devices using app downloaded from PLAY STORE (Android) or APPLE STORE (iOS).

Features & benefits

- Digital compensation of temperature effects and the pressure sensor nonlinearity
- Correction of flow calculation based on antifreeze liquid characteristics
- Compatible with Android (7,0+) and iOS devices
- User-friendly interface
- Easy balancing valve selection from a photographic menu
- A record of the measured values with the capacity of up to 2,000 recordings
- Can be used as data logger
- Very robust construction, can withstand fall from height of 2m
- Wireless data transfer from measuring unit to mobile Bluetooth Low Energy technology
- Accurate pressure measuring with true pressure sensor with 24 bit pressure processing

Applications

The PFM 1000 must be connected on the high side as well as on the low side of the valve using the appropriate needles, connectors and hoses. If you are to measure under high static pressure it is recommended to connect the red hose first in order to protect the membrane inside the pressure sensor. If you connect the blue hose first the pressure sensor may be damaged. You can read flow and pressure on the Android / iOS smartphone which is separate from the pressure sensor.

How to measure:

1. Select manufacturer
2. Select the type of valve
3. Select the dimension of the valve
4. Select pre-setting
5. Connect the valve to the pressure sensor
6. Zero adjust
7. Measure the flow

Ordering

Product code numbers

Type	Pressure [bar]	Code number
PFM 1000	10.00	003Z8260
PFM 1000	20.00	003Z8261

All versions are upgradable with additional pressure sensors and routers.

Accessories code numbers

Type	Set / pcs.	Code No.
Set of the hoses PFM1000 - 2x1,5m	1 set	003Z8262
Set of the filters PFM1000	2 pcs	003Z8263
Set of the needles PFM1000	2 pcs	003Z8264
Adapter R21	2 pcs	003Z8267

Product details

General data

Technical data

Type	Specification
Pressure range	0-1000 kPa ~ 0-10 bar 0-2000 kPa ~ 0-20 bar
Nominal pressure	10 or 20 bar
Max. over pressure	120% of nominal pressure: 1200kpa ~12 bar 2400kpa ~ 24 bar
Reliability, linearity and hysteresis error	0.15 % of range
Error for the pressure range 0 till 5 kPa after pressure zero setting	± 50 Pa for nominal pressure range 1 MPa ± 100 Pa for nominal pressure range 2 MPa
Temperature error	0.25 % of range
Medium temperature ¹⁾	-5 to 90 °C
Ambient temperature	-5 to 50 °C
Storage temperature	+5 to 50 °C
Ambient humidity	95% r.h., non-condensing
Power supply	AAA Alkaline batteries or NiMH rechargeable batteries
Operating time	Max. 45 hours
Power consumption	20mA
Wireless data transfer	Bluetooth Low Energy 5.0
Dimensions w x h x d	180 x 80 x 52 mm
Weight	440 g
IP rated enclosure	IP 65
Calibration validity	24 months

¹⁾ Measured at the end of measuring hoses, length 1.5m, Hot water flows thru PFM1000 hydraulic parts during Pressure zero procedure. Maximum time duration of zeroing when temperature of the medium exceeds 50°C is 10 seconds.

Certificates, declarations and approvals

The list contains all certificates, declarations, and approvals for this product type. Individual code number may have some or all of these approvals, and certain local approvals may not appear on the list.

When you click on the link you will be directed to the latest version of the 'Declaration of Conformity'. Products developed and sold before this date of issue conform to the directives/standards in force at the time of their sale.

Approval type	Title	Certification body	Approval topic
Manufacturer's Declaration	Danfoss BF01032022-en02.01	Danfoss	Similarity
Export Control Declaration	Measuring equipment, flow indicator, room controller	Danfoss	
Wireless Certificate	ACMA CF16070 AU-Rev.-00	ACMA - Australian Communication and Media Authority	Wireless
Wireless Certificate	RSM CF16070 NZ-Rev.00	RSM - Radio Spectrum Management	EMC, Wireless

Contact details

Online support

Danfoss offers a wide range of support along with our products, including digital information, software, mobile apps and expert guidance. See the possibilities below.



The Danfoss Design center

Discover the Design Center, our advanced digital platform that streamlines product selection. With integrated tools and enhanced type pages, it's simpler than ever to access product information and documentation, and to select the right products. Check the availability of Danfoss products at partner locations and enjoy seamless transitions from selection to purchase with our basket-to-basket functionality. Whether you're buying from our distributors or directly from the Product Store, the Design Center simplifies your experience. Learn more at: designcenter.danfoss.com.



The Danfoss product store

The Danfoss Product Store is a one-stop shop available 24/7 for our customers, no matter where you are in the world or what area of industry you work in. Browse our catalog, check product details and documentation, view your prices and product availability, and quickly finalize your purchase. Start browsing at: store.danfoss.com.



Danfoss Partner Portal/Product Data tool

Designed to support you with easy access to product data extracts, essential resources, tools, and information. The Partner Portal provides a centralized hub for product documentation, training materials, marketing assets, and technical support, ensuring you have everything you need to succeed and grow your business with Danfoss. The Partner Portal is available 24/7 at: partner.danfoss.com and is ready to support your business.



Find technical documentation

Find technical documentation you need to get your project up running. Get direct access to our official collection of data sheets, certificates and declarations, manuals and guides, 3D models and drawings, case stories, brochures, and much more. Start searching now at: documentation.danfoss.com.



Danfoss Learning

Danfoss Learning is a free online learning platform. It features courses and materials specifically designed to help engineers, installers, service technicians, and wholesalers better understand the products, applications industry topics, and trends that will help you do your job better. Find your local Danfoss website here: learning.danfoss.com.



Get local information and support

Local Danfoss websites are the main sources for help and information about our company and products. Find product availability, get the latest regional news, or connect with a nearby expert - all in your own language. Find your local Danfoss website here: danfoss.com.

Danfoss A/S

Climate Solutions . danfoss.com . +45 7488 2222

Any information, including, but not limited to information on selection of product, its application or use, product design, weight, dimensions, capacity or any other technical data in product manuals, catalogues description, advertisements, etc. and whether made available in writing, orally, electronically, online or via download, shall be considered informative, and is only binding if and to the extent, explicit reference is made in a quotation or order confirmation. Danfoss cannot accept any responsibility for possible errors in catalogues, brochures, videos and other material. Danfoss reserves the right to alter its products without notice. This also applies to products ordered but not delivered provided that such alterations can be made without changes to form, fit or function of the products. All trademarks in this material are property of Danfoss A/S or Danfoss group companies. Danfoss and the Danfoss logo are trademarks of Danfoss A/S. All rights reserved.
